

SEL-C280 EIA-232 Serial Cable

Male to Female Cable for connecting a DTE device to a DTE device.

Part Number:

C 2 8 0 -

Length⁽³⁾

Specify in feet with leading zeros (Example: 5 Feet = 005) Max length 100 Feet

⁽¹⁾ To verify your cable application, use the Cable Selector at <https://www.selinc.com/CableSelector/>.

⁽²⁾ Indoor Use Only, CM-Rated

⁽³⁾ The performance of EIA-232 cable lengths greater than 50 feet cannot be guaranteed. As cable lengths increase, so does the risk of interference and equipment damage due to ground potential rise and induced voltages. For lengths longer than 50 feet, we recommend the fiber-optic C280FZ/FD cable.



9-PIN MALE
"D" SUB CONNECTOR
DB-9-P

9-PIN FEMALE
"D" SUB CONNECTOR
DB-9-S

CABLE: 8 Conductor 22 AWG 7/30 Tinned Copper with PVC Jacket
(Shielded: Alpha 1298C or equal)

RXD	2	ORANGE	3	TXD
TXD	3	RED	2	RXD
GND	5	BLUE	5	GND
RTS	7		1	DCD
CTS	8		7	RTS
			8	CTS
SHELL		SHIELD		NO CONNECTION

Making Electric Power Safer, More Reliable, and More Economical®

SEL SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA
Phone: +1.509.332.1890 - Fax: +1.509.332.7990