





Energy and Power Monitoring Bundle o SEL-5705 Synchrowave Reports - Power Quality o SEL-5703 Synchrowave Monitoring - Power Monitoring (With Continuous Waveform Streaming Support) o SEL-5045 acSELeator TEAM Profile for billing and Team Events for waveform data (single or additional device license)*	
--	--

## Accessories

SEL-735 Getting Started Kit (includes communication cables, electrical connectors, screwdriver, and more)*	9 1 5 9 0 0 4 3 1
SEL-9321 Low-Voltage DC Power Supply*	Please see Online MOT or contact SEL REP or CSR for ordering information.
SEL-2401 Satellite-Synchronized Clock	2 4 0 1
Rear-Panel Connector Kit	
Rear-Panel Connector Kit*	9 1 5 9 0 0 0 1 4
90 Degree Connector Kit*	9 1 5 9 0 0 2 2 3
Rear Connector Kit for SEL-735 (Barrier Style)*	9 1 5 9 0 0 5 3 2
Self-Shorting Current Connectors	
Self-Shorting Current Connector, 20 feet (with 6 position male)*	9 1 5 9 0 0 2 6 4
Self-Shorting Current Connector, 8 feet (with 8 position male)*	9 1 5 9 0 0 0 4 8
FT Test Switch	
FT-1 Test Switch*	2 4 0 - 1 0 1 0
Communication Cables	
6 kV Ethernet Surge Suppressor Kit*	9 1 5 9 0 0 5 1 8
SEL-C287R Serial Cable (RS-232, DTE-DTE, DB9 M/DB9 F, Hardware Flow Control)	C 2 8 7 R
SEL-C662 USB Cable for Computer Terminal (USB, DB9 M/USB A-Type M, Pin 1 Power)*	Please see Online MOT or contact SEL REP or CSR for ordering information.
Dust Protection and Sealing Cover	
Dust-Protection Assembly*	9 1 5 9 0 0 1 7 0
7xx/24xx Vertical Dust Protection Assembly, Transparent Rear Cover*	9 1 5 9 0 0 4 5 2
Front-Panel Sealing Cover Kit for SEL-734*	9 1 5 9 0 0 1 7 6

Configurable Labels		
	Configurable Label Kit for SEL-735 (LDM, 3 Sheets)*	9 2 6 0 1 4 3
Socket Adapters		
	Socket Adapter Form 5*	9 1 5 9 0 0 2 5 6
	Socket Adapter Form 9*	9 1 5 9 0 0 2 5 7
	Form 5 EXM Test-Socket Adapter*	9 1 5 9 0 0 2 5 8
	Form 9 EXM Test-Socket Adapter*	9 1 5 9 0 0 2 5 9
Rack Mount Brackets		
	Single Horizontal Meter Bracket*	9 1 5 9 0 0 0 0 7
	Two Horizontal Meter Bracket*	9 1 5 9 0 0 0 0 8
	Horizontal Meter and FT-1 Test Switch Bracket*	9 1 5 9 0 0 0 0 9
	Meter and Two FT-1 Test Switch Bracket*	9 1 5 9 0 0 0 3 5
	Single Vertical Meter Bracket*	9 1 5 9 0 0 0 5 0
	Two Vertical Meter Bracket*	9 1 5 9 0 0 0 5 1
	Three Vertical Meter Bracket*	9 1 5 9 0 0 2 4 3
	Vertical Meter and two FT-1 Test Switch Bracket*	9 1 5 9 0 0 1 5 8
	Rack Mount Kit, 7xx/24xx Vertical and 7xx/24xx Horizontal Retrofit*	9 1 5 9 0 0 1 4 1
	Rack Mount Kit, 7xx/24xx Vertical*	9 1 5 9 0 0 1 6 9
	19" Rack Mount Bezel for 7xx/24xx Vertical (centered)*	9 1 5 9 0 0 2 2 8
	Vertical Meter and FT-1 Test Switch Bracket*	9 1 5 9 0 0 0 5 2
Wall Mount Brackets		
	Low-Profile, Hinged, Contains 2 Ribbon Cables*	9 1 5 9 0 0 2 5 5
	Low-Profile, Hinged, Contains CT/PT Wiring and 1 Serial Cable*	9 1 5 9 0 0 3 1 7
	Low-Profile, Hinged, Contains CT/PT Wiring and 2 Serial Cables*	9 1 5 9 0 0 3 1 8
	Low-Profile, Hinged, Contains CT/PT Wiring and 3 Serial Cables*	9 1 5 9 0 0 3 1 9
	Hinged Wall-Mount Bracket, Vertical*	9 1 5 9 0 0 1 3 6

	Vertical Hinged Wall-Mount Bracket for SEL-700 Series EXM and SEL-2400 Series EXM*	9 1 5 9 0 0 5 2 9
	Universal CT/PT Wiring Harness*	9 1 5 9 0 0 4 9 3
Retrofit Bezels		
	Single Vertical Meter Retrofit Bezel*	9 1 5 9 0 0 0 5 3
	Vertical Appearance Bezel *	9 1 5 9 0 0 0 5 8
	Vertical Retrofit (GE kV) Bezel*	9 1 5 9 0 0 0 6 8
	Vertical Retrofit (JEM 1 SB) Bezel*	9 1 5 9 0 0 0 6 9
	Vertical Retrofit (JEM 1 Panel Mount) Bezel*	9 1 5 9 0 0 0 7 0
	Vertical Retrofit (JEMStar SB/TransData MK-5 SB) Bezel*	9 1 5 9 0 0 0 7 2
	Vertical Retrofit (Nexus 1260/1270 SB) Bezel*	9 1 5 9 0 0 0 7 3
	Vertical Retrofit (PML ION 8000 SB) Bezel*	9 1 5 9 0 0 0 7 4
	Vertical Retrofit (Schlumberger Q1000 SB) Bezel*	9 1 5 9 0 0 0 7 5
	Vertical Retrofit (Siemens Q4 Tall SB) Bezel*	9 1 5 9 0 0 0 7 6
	Vertical Retrofit (Siemens Q4 Short SB) Bezel*	9 1 5 9 0 0 0 7 7
	Vertical Retrofit (Siemens Q4 Tall SB with FT-1 Test Switch Cutout)*	9 1 5 9 0 0 1 4 0
	Vertical Retrofit (Square-D Power Logic 2000)*	9 1 5 9 0 0 2 7 5
	Vertical Retrofit (GE 169/269/369 and Eaton FP5000)*	9 1 5 9 0 0 0 5 4
	Vertical Retrofit(GE 469)*	9 1 5 9 0 0 0 5 5
	Vertical Retrofit(Cutler-Hammer MP-3000)*	9 1 5 9 0 0 0 5 7
	Bezel, CO (FT-2) to 7XX Vertical*	9 1 5 9 0 0 0 7 8
	Bezel, GE F650 to 7XX Vertical*	9 1 5 9 0 0 0 7 9
	Bezel, GE 700 Series to 7XX Vertical*	9 1 5 9 0 0 0 8 0
	Bezel, Basler 851/951 to 7XX Vertical*	9 1 5 9 0 0 0 8 1

	ABB 500 Series to 7xx/24xx Vertical Retrofit*	9 1 5 9 0 0 0 8 2
	Bezel, Siemens 7SJ61 (1/3 Rack Case) to 7XX Vertical*	9 1 5 9 0 0 0 8 3
	Bezel, ABB 500 Series (1/2 Rack Case) to 7XX Vertical*	9 1 5 9 0 0 0 8 6
	GE ML 269 Plus With Drawout Case Option to 7xx/24xx Vertical Retrofit*	9 1 5 9 0 0 0 9 9
	ABB-FT 31/32 (CO FT-3) to 7xx/24xx Vertical Retrofit with 2 FT-1 Switch Cutouts*	9 1 5 9 0 0 1 3 0
	GE MDP/S2 to 7xx/24xx Vertical Retrofit*	9 1 5 9 0 0 1 3 2
	GE M1 to 7xx/24xx Vertical Retrofit*	9 1 5 9 0 0 1 3 3
	GE M2 to 7xx/24xx Vertical Retrofit*	9 1 5 9 0 0 1 3 4
	GE 565 to 7xx/24xx Vertical Retrofit*	9 1 5 9 0 0 1 4 5
	ABB-FT 41/42 (CO FT-4) to 7xx/24xx Vertical Retrofit with 2 FT-1 Switch Cutouts*	9 1 5 9 0 0 1 5 6
	ABB DPU to 7xx/24xx Vertical Retrofit*	9 1 5 9 0 0 1 5 7
	GE S1 (IAC S1) to 2 FT-1 Switch Cutouts*	9 1 5 9 0 0 1 5 9
	GE 269/369 to 7xx/24xx Vertical Retrofit with FT-1 Switch Cutout*	9 1 5 9 0 0 1 6 5
	GE DGP to 7xx Vertical Retrofit*	9 1 5 9 0 0 3 5 5
	EXM Retrofit Bezel, JEMStar SB/TransData MK-5 SB*	9 1 5 9 0 0 1 9 6
	701/Simpro Retrofit Bezel*	9 1 5 9 0 0 1 9 7
Indoor Enclosure Brackets		
	7xx Indoor Enclosure Mounting Bracket + FT-1 Cutout Test Switch, Vertical*	9 1 5 9 0 0 0 6 5
	7xx Indoor Enclosure Mounting Bracket, No FT-1 Cutout, Vertical*	9 1 5 9 0 0 0 9 1

Outdoor Enclosure Kits		
	7xx Outdoor Enclosure Kit + FT-1 cutout, Swing Door, Vertical*	9 1 5 9 0 0 0 6 6
	7xx Outdoor Enclosure, No FT-1 Cutout, Vertical*	9 1 5 9 0 0 0 9 3
Mounting Accessories		
	Mounting Gasket*	9 1 5 9 0 0 0 9 7
	Mounting Brackets for 16" x 18" x 8" Enclosure*	9 1 5 9 0 0 2 9 7
Current Transformers Clamp-On		
	Three 200:1 Clamp-On CTs, 0.6" Window, +-1% Accuracy*	9 1 5 9 0 0 2 0 9
	Three 1000:5 Clamp-On CTs, 2.0" Window, +-1% Accuracy*	9 1 5 9 0 0 2 1 0
Current Transformers Split-Core		
	Three 1000:5 Split-Core CTs, 4.5" Window, +-3% Accuracy*	9 1 5 9 0 0 2 1 1
	Three 2000:5 Split-Core CTs, 6.0" Window, +-3% Accuracy*	9 1 5 9 0 0 2 1 2
	Three 3000:5 Split-Core CTs, 8.0" Window, +-3% Accuracy*	9 1 5 9 0 0 2 1 3
Projection Mounting Collar		
	Projection Mounting Collar, 45mm*	9 1 5 9 0 0 0 2 8
	Projection Mounting Collar, 90mm*	9 1 5 9 0 0 0 2 9
Blank Cover Plates		
	ABB-FT 21/22 (CO FT-2) Blank Cover Plate*	9 1 5 9 0 0 0 8 4
	GE S1 (IAC S1) Blank Cover Plate*	9 1 5 9 0 0 0 8 5
	GE M1 Blank Cover Plate*	9 1 5 9 0 0 1 4 2
	ABB-FT 31/32 (CO FT-3) Blank Cover Plate*	9 1 5 9 0 0 1 4 3
	ABB-FT 11 (CO FT-1) Blank Cover Plate*	9 1 5 9 0 0 1 4 4
	GE MDP/S2 Blank Cover Plate*	9 1 5 9 0 0 2 3 0
	241X / 7XX Blanker Plate*	9 1 5 9 0 0 3 8 7
Literature		
	Printed Instruction Manual for SEL-735*	P M 7 3 5 - 0 1

\* Additional Cost

- (1) Conformal coat is included free of charge with NEMA 4 enclosure and portable case options.
- (2) Portable Case includes voltage clips. Order an optional current transformer kit for current sensing.
- (3) Requires Ethernet.

***Making Electric Power Safer, More Reliable, and More Economical®***

---

**SEL** SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA  
Phone: +1.509.332.1890 - Fax: +1.509.332.7990