




SCHWEITZER ENGINEERING LABORATORIES
2350 NE Hopkins Court Pullman, WA 99163-5603 USA
Phone:(509) 332-1890 Fax:(509) 332-7990
Internet:www.selinc.com E-mail:info@selinc.com

CABLE C552



32-PIN MALE
CIRCULAR CONNECTOR

42-PIN FEMALE
RECTANGULAR CONNECTOR

CABLE: 33 Conductor 20 AWG Tinned copper,
polyurethane jacket

I1	A	BLACK	21	I1
I2	B	BROWN	28	I2
I3	C	RED	35	I3
IN	D	ORANGE	27	IN
12VDC Whet	F	VIOLET	29	12VDC Whet
GND	G	SHIELD WIRE	25	GND
GND	H	SHIELD WIRE	19	GND
V1Y	J	WHT/BLK/ORG	36	V1Y
V2Y	K	WHT/BLK/YEL	37	V2Y
V3Y	L	WHT/BLK/GRE	38	V3Y
NY	M	WHT/BLK/BLU	30	N1Y
V1Z	N	WHT/BRO/RED	40	V1Z
V2Z	P	WHT/BRO/ORG	41	V2Z
V3Z	R	WHT/BRO/YEL	42	V3Z
NZ	S	WHT/BRO/GRE	39	N1Z
GND	T	SHIELD WIRE	20	GND
52a1	U	GRAY	9	52a1
52a2	V	WHITE	8	52a2
52a3	W	WHITE/BLACK	1	52a3
69	X	WHITE/BROWN	15	69
Close 1	Y	WHITE/YELLOW	2	Close 1
Trip 1	Z	WHITE/GREEN	3	Trip 1
Close 2	f	WHITE/BLUE	4	Close 2
Trip 2	g	WHITE/VIOLET	5	Trip 2
Close 3	h	WHITE/GRAY	6	Close 3
Trip 3	j	WHT/BLK/BRO	7	Trip 3

Comments: *Maximum length 100 feet