




SCHWEITZER ENGINEERING LABORATORIES
2350 NE Hopkins Court Pullman, WA 99163-5603 USA
Phone:(509) 332-1890 Fax:(509) 332-7990
Internet:www.selinc.com E-mail:info@selinc.com

CABLE C524



32-PIN MALE
CIRCULAR CONNECTOR

32-PIN FEMALE
CIRCULAR CONNECTOR

CABLE: Shielded 24 Conductor, 20 AWG Tinned Copper
Polyurethane jacket

I1	A	WHT	A	I1
I2	B	WHT/BLK	B	I2
I3	C	WHT/BRN	C	I3
IN	D	WHT/RED	D	IN
12Vdc Whet	F	WHT/GRY	F	12 Vdc Whet
GND	G	SHIELD /WIRE	G	GND
GND	H	SHIELD/WIRE	H	GND
V1Y	J	GRN	J	V1Y
V2Y	K	BLU	K	V2Y
V3Y	L	VIOL	L	V3Y
NY	M	YEL	M	NY
V1Z	N	BRN	N	V1Z
V2Z	P	RED	P	V2Z
V3Z	R	ORG	R	V3Z
NZ	S	BLK	S	NZ
GND	T	SHIELD/ WIRE	T	GND
52a1	U	WHT/BLK/BRN	U	52a1
52a2	V	WHT/BLK/RED	V	52a2
52a3	W	WHT/BLK/ORG	W	52a3
69	X	WHT/BLK/YEL	X	69
Close 1	Y	WHT/ORG	Y	Close 1
Trip 1	Z	WHT/YEL	Z	Trip 1
Close 2	f	WHT/GRN	f	Close 2
Trip 2	g	GRY	g	Trip 2
Close 3	h	WHT/BLU	h	Close 3
Trip 3	j	WHT/VIOL	j	Trip 3

2-17-2011

Comments: * Maximum length 100 feet