




SCHWEITZER ENGINEERING LABORATORIES
2350 NE Hopkins Court Pullman, WA 99163-5603 USA
Phone:(509) 332-1890 Fax:(509) 332-7990
Internet:www.selinc.com E-mail:info@selinc.com

CABLE C584



#10
RING TERMINALS

3-PIN FEMALE
CIRCULAR CONNECTOR

CABLE: 3 Conductor 16AWG Tinned Copper with Thermoset jacket

LINE	A	BLACK	A	LINE
NEUTRAL	B	WHITE	B	NEUTRAL
GND	C	GREEN	C	GND

Comments: * Base cable is unarmored, available up to 100 ft. Partially armored cable option is also available up to 100 ft. and includes 10 ft. armor (at control end). Fully armored option is available up to a max length of 65 ft. The armoring consists of flexible liquid-tight steel with a UV resistant, flame-retardant PVC Jacket. Tranformer side includes a weather proof boot.

All three cable options (unarmored, partial armor, and fully armored) are rated to IPX6.