




SCHWEITZER ENGINEERING LABORATORIES
2350 NE Hopkins Court Pullman, WA 99163-5603 USA
Phone:(509) 332-1890 Fax:(509) 332-7990
Internet:www.selinc.com E-mail:info@selinc.com

CABLE C525



10-PIN MALE
CIRCULAR CONNECTOR

10-PIN FEMALE
CIRCULAR CONNECTOR

CABLE: Shielded 9 Conductor, 20 AWG Tinned Copper
Polyurethane jacket

52a	A	RED	A	52a
69	B	ORANGE	B	69
I (1000:1)	C	YELLOW	C	I (1000:1)
I Ret (1000:1)	D	GREEN	D	I Ret (1000:1)
I (500:1)	E	BLUE	E	I (500:1)
I Ret (500:1)	F	VIOLET	F	I Ret (500:1)
GND	G	GROUND WIRE	G	GND
12 Vdc Whet	H	GREY	H	12 Vdc Whet
TRIP	J	BLACK	J	TRIP
CLOSE	K	BROWN	K	CLOSE

Comments: * Base cable is unarmored, available up to 100 ft. Partially armored cable option is also available up to 100 ft. and includes 10 ft. armor (at control end). Fully armored option is available up to a max length of 65 ft. The armoring consists of flexible liquid-tight steel with a UV resistant, flame-retardant PVC Jacket.