




SCHWEITZER ENGINEERING LABORATORIES
2350 NE Hopkins Court Pullman, WA 99163-5603 USA
Phone:(509) 332-1890 Fax:(509) 332-7990
Internet:www.selinc.com E-mail:info@selinc.com

CABLE C541



5-POSITION
SOCKET CONTACT CIRCULAR

3-POSITION
SOCKET CONTACT CIRCULAR

CABLE: Shielded, 2 conductor, 16 AWG tinned copper, chlorinated polyethylene jacket

LINE	A	BLACK	A	LINE
NEUTRAL	E	WHITE	B	NEUTRAL
		SHIELD		

Comments: Base mode (unarmored): max 100 ft
Partially armored (10 ft on controller end): max 100 ft
Fully armored: max 65 ft.
The armoring consists of flexible liquid-tight steel with UV resistant, flame-retardant PVC Jacket.