

SEL-2244-5 Fast High-Current Digital Output Module

Digital Output Module for the SEL-2240 Axion System

Part Number:

2	2	4	4						X	
---	---	---	---	--	--	--	--	--	---	--

10 Fast High-Current Digital Outputs

Form A Control Outputs					5	1	5	1		
5 Form A, 5 Form B Control Outputs					5	1	5	2		
Form B Control Outputs					5	2	5	2		

Conformal Coat

None										0
Conformal Coated Circuit Boards*										1

Accessories

32 Conductor Wiring Harness With Two Pre-Installed I/O Board Terminal Plugs - 8 ft*	9	1	5	9	0	1	8	5	
32 Conductor Wiring Harness With Two Pre-Installed I/O Board Terminal Plugs - 12 ft*	9	1	5	9	0	1	8	6	
32 Conductor Wiring Harness With Two Pre-Installed I/O Board Terminal Plugs - 20 ft*	9	1	5	9	0	1	8	7	
Strain Relief Connectors (2 Pieces, 16 Pin)*	9	1	5	9	0	0	4	0	2

* Additional Cost

Note: The SEL-2244 is used with an SEL-2242 Chassis/Backplane. The SEL-2244 comes standard with a printed module datasheet.

Making Electric Power Safer, More Reliable, and More Economical®

SEL SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA
 Phone: +1.509.332.1890 - Fax: +1.509.332.7990