

SEL-3306 Synchrophasor Processor

Standard With 16 Serial Ports, 2 Ethernet Connections

Full part number must be configured online.

Part Number:

3	3	0	6					X					X	X		X	X
---	---	---	---	--	--	--	--	---	--	--	--	--	---	---	--	---	---

Processor

Pentium® M 1.1 GHz CPU w/ 512 MB DDR SDRAM						0	3										
--	--	--	--	--	--	---	---	--	--	--	--	--	--	--	--	--	--

Power Supply

24/48 Vdc								2									
48/125 Vdc or 120 Vac								3									
125/250 Vdc or 120/240 Vac								4									

Serial Ports

16 Ports RS232													5				
----------------	--	--	--	--	--	--	--	--	--	--	--	--	---	--	--	--	--

Ethernet Network Connections

Port 1 10/100BASE-T + 100BASE-FX ⁽¹⁾ + Port 2 100BASE-FX														6			
---	--	--	--	--	--	--	--	--	--	--	--	--	--	---	--	--	--

Compact Flash Primary

512 MB																1	
--------	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	---	--

Mounting

Horizontal Rack Mount																	H
Horizontal Panel Mount																	3

⁽¹⁾ Port 1 Ethernet jumper selectable between copper and fiber interfaces.

Note: The SEL-3306 comes standard with a CD manual. A printed instruction manual is available upon request.

Making Electric Power Safer, More Reliable, and More Economical®
An Employee Owned Company



2350 NE Hopkins Court - Pullman, WA 99163
 Phone: (509) 332-1890 - Fax: (509) 332-7990