

SEL-C807 Multimode Fiber-Optic Cable

62.5/200 Micrometer Core Diameter⁽¹⁾

Part Number:

C	8	0	7					0											
---	---	---	---	--	--	--	--	---	--	--	--	--	--	--	--	--	--	--	--

Cable Construction

Simplex 1 Fiber*					Z	0	1												
Zipcord 2 Fibers*					Z	0	2												
Waterproof Heavy Duty Jacketed 2 Fibers*					G	0	2												
Waterproof Heavy Duty Jacketed 4 Fibers*					G	0	4												

Jacket Marking

Standard								0											
----------	--	--	--	--	--	--	--	---	--	--	--	--	--	--	--	--	--	--	--

Termination

Bulk Cable: No Terminations								0	0										
ST [®] Connector on Both Ends								S	S										
LC Connector on Both Ends					Z	0	2	L	L	X									
LC Connector to ST Connector					Z	0	2	L	S	X									

Other Options

No Options																		X	
Pulling Loop*					G													1	

Length

Specify length Enter length in meters with leading zeros.
(Example: 15 meters = 0015)

--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--

Accessories

ST Connector Termination Kit*	2	4	0	-	1	4	9	9											
ST Connector*	0	9	0	-	5	0	0	1											
ST Connector Splice Bushing*	0	9	0	-	5	0	1	2											
Fiber Stripper - Replacement Blade Kit*	9	1	5	9	0	0	2	5	2										
Magnetic Cable Guides*	M	C	G																

* Additional Cost

⁽¹⁾ Cables are priced per options selected.

Making Electric Power Safer, More Reliable, and More Economical[®]

SEL SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA
Phone: +1.509.332.1890 - Fax: +1.509.332.7990