















|  |   |
|--|---|
| SEL-C805 200 $\mu$ m Multimode Fiber-Optic Cable (configurable length)*                                      | Please see Online MOT or contact SEL REP or CSR for ordering information. |
| SEL-C807 62.5/200 $\mu$ m Multimode Fiber-Optic Cable (configurable length)*                                 | Please see Online MOT or contact SEL REP or CSR for ordering information. |
| SEL-C808 62.5/125 $\mu$ m Multimode Fiber-Optic Cable*   | Please see Online MOT or contact SEL REP or CSR for ordering information. |
| SEL-C814 Arc-Flash Detection (AFD) Fiber Cables and Accessories (configurable length and number of splices)* | Please see Online MOT or contact SEL REP or CSR for ordering information. |
| SEL-CA605 CAT 5e, Shielded Twisted Pair(STP) Ethernet Cable (configurable length)*                           | Please see Online MOT or contact SEL REP or CSR for ordering information. |

#### Additional Information

- Base unit includes slots A, B (EIA-232), Z, HMI, and Front EIA-232 Port.
- The protocols SNTP, IEEE 1588-2008 firmware-based PTP and Modbus TCP are included in the standard offering with Single Ethernet option.
- The protocols SNTP, IEEE 1588-2008 firmware-based PTP, PRP and Modbus TCP are included in the standard offering with Dual Ethernet option.
- DNP3 LAN/WAN are included with DNP3 and Ethernet options.
- Download ACSELERATOR QuickSet SEL-5030 software for free at <https://www.selinc.com/software/solutions/>. ACSELERATOR QuickSet on CD (503001WX4) is available upon request.
- The SEL-710-5 comes standard with a CD manual. One complimentary printed instruction manual is available upon request with each product purchased.
- SEL-710- 5 when ordered with synchronous motor option will include a Synchronous Motor Voltage Divider Module (SEL part number 915900294). Additional modules if desired, can be ordered using the part number provided. Synchronous Motor Option will require an external DCCT with (0-10 Vdc) or (4-20 mA) output for DC field current measurement.
- A configuration kit is provided for the front panel configurable labels (packaged in the shipping box). For additional kits, order SEL part number 9260136 (2 Sheet Kit) or 9260137 (25 Sheet Kit).
- For additional remote I/O capability, order SEL-2505 Remote I/O Module that is SEL-2812 compatible (ST option only).
- Order external AC powered RTD module SEL-2600A or external DC powered RTD module SEL-2600D using WI-5997 to interface remote external resistive temperature devices (RTD) or use internal RTD inputs option in Slot D.
- The SEL-710-5 option cards are orderable separately for field installation. Use WI-11297 and contact your SEL representative to order option cards.
- For relay wire termination kits, please see Application Note AN2014-08 on the SEL website or contact SEL REP or CSR for ordering information.
- For SEL-710-5 Mounting Accessories including adapter plates, dust protectors, etc go to <https://selinc.com/applications/mountingselector/>.
- ACSELERATOR Bay Screen Builder SEL-5036 software is available with touchscreen models.
- All Digital Outputs are Form-A unless noted otherwise

**Making Electric Power Safer, More Reliable, and More Economical®**

**SEL SCHWEITZER ENGINEERING LABORATORIES, INC.**

2350 NE Hopkins Court - Pullman, WA 99163 USA  
Phone: +1.509.332.1890 - Fax: +1.509.332.7990