



SEL-2245-22 Analog Input Extended Range Module

The SEL-2245-22 provides extended range dc analog inputs or ac voltage inputs for the SEL Axion[®]. Within an Axion system, install as many as sixteen SEL-2245-22 modules in any combination you want.

Front Panel



Figure 1 SEL-2245-22 Analog Input Extended Range Module

Mechanical Installation

Each SEL-2242 chassis/backplane has four or ten slots, labeled A–J. Slots B–J support the SEL-2245-22 modules.

To install an SEL-2245-22 module, tip the top of the module away from the chassis, align the notch on the bottom of the module with the slot you want on the chassis, and place the module on the bottom lip of the chassis as *Figure 2* illustrates. The module is aligned properly when it rests entirely on the lip of the chassis.



Figure 2 Proper Module Placement

Next, carefully rotate the module into the chassis, making sure that the alignment tab fits into the corresponding slot at the top of the chassis (refer to *Figure 3*). Finally, press the module firmly into the chassis and tighten the chassis retaining screw.



Figure 3 Final Module Alignment

Input Connections

The SEL-2245-22 analog inputs include a plus sign to indicate the positive convention. Refer to *Specifications* for analog input ratings and to *Figure 1* for terminal assignments. Input range is 0–300 Vdc. Configure inputs by adding a Fieldbus I/O connection for each module in ACCELERATOR RTAC® SEL-5033 Software. See the EtherCAT® portion in *Section 2: Communications* in the SEL-5033 software manual for details.

LED Indicators

The LEDs labeled **ENABLED** and **ALARM** are related to EtherCAT network operation. The green **ENABLED** LED illuminates when the module is operating normally on the network. The **ALARM** LED illuminates during network initialization or when there is a problem with the network. Refer to *Section 3: Testing and Troubleshooting* in the *SEL-2240 Instruction Manual* for more information.

Specifications

Compliance

Designed and manufactured under an ISO 9001 certified quality management system

Product Standards

IEC 60255-26:2013 - Relays and Protection Equipment: EMC
 IEC 60255-27:2014 - Relays and Protection Equipment: Safety
 IEC 60825-2:2004 +A1:2007 +A2:2010 for fiber-optic communications
 IEC 61850-3:2013 - Comm Systems for Power Utility Automation

General

Operating and Storage Temperature Range

-40° to +85°C (-40° to +185°F)

Units should be stored and transported in their original packaging.

Note: Operating temperature evaluated for UL ambient 0° to 40°C.

Operating Environment

Pollution Degree:	2
Overtoltage Category:	II
Insulation Class:	1
Relative Humidity:	5%–95%, noncondensing
Maximum Altitude:	2000 m
Vibration, Earth Tremors:	Class 1

Type Test Acceptance Criteria

Level B: Allows temporary degradation or loss of performance during transient events that are self-recovering.

DC Transducer (Analog) Inputs (SEL-2245-22) (DC Mode)

Input Impedance:	> 7 MΩ
Input Range (Maximum):	0–300 V
Sampling Rate:	24 ksp/s

Anti-Alias Filter

Corner Frequency:	5 kHz
Rolloff:	20 dB per decade

Digital Filter

Corner Frequency:	Filter A: 16 Hz Filter B: 10 Hz Filter C: 0.2 Hz
50 Hz Rejection:	Filter A: > 30 dB Filter B: > 50 dB Filter C: > 70 dB
60 Hz Rejection:	Filter A: > 60 dB Filter B: > 70 dB Filter C: > 70 dB

Step Response

Group Delay (Pre-Filter):	5.3 ms
No Filter:	3 ms (10–90% response)
Filter A:	23 ms (10–90% response)
Filter B:	35 ms (10–90% response)
Filter C:	700 ms (10–90% response)

AC Voltage Inputs (SEL-2245-22) (AC Mode)

Voltage Inputs

V_{NOM} :	300 V
Measurement Range:	5–400 L-N, 9–693 L-L Vac Fundamental/RMS 5–300 L-N, 9–520 L-L Vac Fundamental/RMS (UL)
Maximum:	600 L-N, 1039 L-L Vac Fundamental/RMS for 10 s
Typical Accuracy:	±0.1% Fundamental@ f_{NOM} and > 20V ±0.1% RMS@ f_{NOM}
Worst Case Accuracy:	±2% Fundamental@ f_{NOM} ±1% RMS ±0.05 V

Angle

Range:	±180°
Typical Accuracy:	±0.1° @ f_{NOM} and > 20 V
Worst Case Accuracy:	±2° @ f_{NOM}
Burden:	< 0.1 VA

Sequence Components

Values:	V0, V1, V2
Typical Accuracy	
Magnitude:	±0.2% @ f_{NOM} and $V > 6.7 V, I > 0.6 A$
Angle:	±0.2% @ f_{NOM} and $V > 6.7 V, I > 0.6 A$
Worst Case Accuracy	
Magnitude:	±3% @ f_{NOM} and $V > 6.7 V, I > 0.6 A$
Angle:	±0.2% @ f_{NOM} and $V > 6.7 V, I > 0.6 A$

Synchrophasor

Conformance:	IEEE C37.118.1-2011 as amended by IEEE C37.118.1a-2014 IEEE C37.118.2-2011
Accuracy:	Level 1 as specified by IEEE C37.118
Measurements:	Software selectable
Voltage:	VA, VB, VC, VS
Positive-Sequence:	V1
Periodic:	Frequency and df/dt
Processing Rate:	120 Hz

AC and DC Inputs (SEL-2245-22)

Common Mode Range

±250 Vdc between inputs
±250 Vac all inputs to chassis

Isolation

2500 Vrms between separate inputs
2500 Vrms all inputs to chassis

Accuracy at 25°C

ADC:	16 bit
Inputs:	0.25% of full-scale typical 3% of full scale worst case

Accuracy Variation With Temperature

Inputs:	±0.015% per °C of full scale
---------	------------------------------

Triggered Waveform Recording

Sampling Rate:	1, 2, 4, 8, 24 kHz
Record Duration:	0.1 second increments from 0.5 s to 144 s
Record Pretrigger:	0.05 s minimum to a maximum of (record length minus 0.05) s
Waveform File Format:	COMTRADE (IEEE C37.111-1999 compliant)

Type Tests**Environmental Tests**

Enclosure Protection:	IEC 60529:2001 + CRGD:2003 IP3X excluding the terminal blocks
Vibration Resistance:	IEC 60255-21-1:1988 Vibration Endurance, Severity: Class 2 Vibration Response, Severity: Class 2
Shock Resistance:	IEC 60255-21-2:1988 Bump Withstand, Severity: Class 1 Shock Withstand, Severity: Class 1 Shock Response, Severity: Class 2
Seismic:	IEC 60255-21-3:1993 Quake Response, Severity: Class 2
Cold, Operational and Cold, Storage:	IEC 60068-2-1:2007 -40°C, 16 hours
Dry Heat, Operational and Dry Heat, Storage:	IEC 60068-2-2:2007 +85°C, 16 hours
Damp Heat, Cyclic:	IEC 60068-2-30:2005 25° to 55°C, 6 cycles, 95% relative humidity
Damp Heat, Steady State:	IEC 60068-2-78:2012 93% RH and 55°C for 10 days
Change of Temperature:	IEC 60068-2-14:2009 1 deg. per minute, -40° and +85°C, 5 cycles

Dielectric Strength and Impulse Tests

Impulse:	IEC 60255-5:2000 IEEE C37.90-2005 Severity Level: 0.5 Joule, 5 kV
Dielectric (HiPot):	IEC 60255-5:2000 IEEE C37.90-2005 Severity Level: 2500 Vac channel to chassis for 1 minute

RFI and Interference Tests**EMC Immunity**

Slow Damped Oscillatory Waves:	IEC 61000-4-18:2006 + A1:2010 Severity Level: 2.5 kV common mode 1 kV differential mode
--------------------------------	---

Electrostatic Discharge Immunity:	IEEE C37.90.3-2001 IEC 60255-22-2:2008 IEC 61000-4-2:2008 Severity Level: 8 kV contact discharge 15 kV air discharge
Radiated RF Immunity:	IEEE C37.90.2-2004 Severity Level: 35 V/m IEC 61000-4-3:2008 IEC 60255-22-3:2007 Severity Level: 10 V/m
Digital Radio Telephone RF Immunity:	ENV 50204:1995 Severity Level: 10 V/m at 900 MHz and 1.89 GHz
Conducted RF Immunity:	IEC 60255-22-6:2001 IEC 61000-4-6:2008 Severity Level: 10 Vrms
Surge Immunity:	IEC 60255-22-5:2008 IEC 61000-4-5:2005 Severity Level: 1 kV Line to Line, 2 kV Line to Earth
Fast Transient, Burst Immunity:	IEC 60255-22-4:2008 IEC 61000-4-4:2011 Severity Level: Class A: 4 kV, 5 kHz; 2 kV, 5 kHz on communications ports
Magnetic Field Immunity:	IEC 61000-4-8:2009 Severity Level: 1000 A/m for 3 seconds, 100 A/m for 1 minute IEC 61000-4-9:2001 Severity Level: 1000 A/m IEC 61000-4-10:2001 Severity Level: 100 A/m
Surge Withstand Capability Immunity:	IEEE C37.90.1-2002 Severity Level: 2.5 kV Oscillatory 4.0 kV Fast Transient
Oscillatory Waves Immunity:	IEC 61000-4-12:2006 Severity Level: Ring Wave: 2 kV common, 1.0 kV differential Oscillatory: 2.5 kV common, 1.0 kV differential
Common Mode Disturbance Immunity:	IEC 61000-4-16:2002 Frequency: 0 to 150 Hz Severity Level: Level 4, Segment 4: 30 Vrms open-circuit, 15 to 150 kHz
Emissions	
Radiated and Conducted Emissions:	IEC 60255-25:2000 Severity Level: Class A Canada ICES-001 (A) / NMB-001 (A)

© 2014-2022 by Schweitzer Engineering Laboratories, Inc. All rights reserved.

All brand or product names appearing in this document are the trademark or registered trademark of their respective holders. No SEL trademarks may be used without written permission. SEL products appearing in this document may be covered by U.S. and Foreign patents.

Schweitzer Engineering Laboratories, Inc. reserves all rights and benefits afforded under federal and international copyright and patent laws in its products, including without limitation software, firmware, and documentation.

The information in this document is provided for informational use only and is subject to change without notice. Schweitzer Engineering Laboratories, Inc. has approved only the English language document.

This product is covered by the standard SEL 10-year warranty. For warranty details, visit selinc.com or contact your customer service representative.

SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court • Pullman, WA 99163-5603 U.S.A.
Tel: +1.509.332.1890 • Fax: +1.509.332.7990
selinc.com • info@selinc.com

