

## SEL-C322R EIA-232 Serial Cable

Cable with PVC jacket and double-shielding for enhanced RFI/EMI protection<sup>(1)</sup> for connecting a DTE device to another DTE device with 9-pin female connectors<sup>(2)</sup>

Part Number:

**C 3 2 2 R -**

### Length<sup>(3)</sup>

Specify in feet with leading zeros (Example: 5 Feet = 005) Max length 100 Feet

\* Additional Cost

<sup>(1)</sup> Indoor Use Only, CM-Rated.

<sup>(2)</sup> To verify your cable application, use the Cable Selector at <https://www.selinc.com/CableSelector/>

<sup>(3)</sup> The performance of EIA-232 cable lengths greater than 50 feet cannot be guaranteed. As cable lengths increase, so does the risk of interference and equipment damage due to ground potential rise and induced voltages. For lengths longer than 50 feet, we recommend the Fiber-Optic C272AFZ/FD



9-PIN MALE  
"D" SUB CONNECTOR  
DB-9-P

9-PIN MALE  
"D" SUB CONNECTOR  
DB-9-P

**CABLE:** 8 Conductor 24 AWG 7/32 Tinned Copper with PVC Jacket

RXD	2	ORANGE	3	TXD
TXD	3	RED	2	RXD
GND	5	BLACK	5	GND
RTS	7		7	RTS
CTS	8		8	CTS
SHELL		SHIELD		SHELL

**Comments:** This cable uses metal connector shells for improved shielding.

*Making Electric Power Safer, More Reliable, and More Economical®*

**SEL** SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA  
Phone: +1.509.332.1890 - Fax: +1.509.332.7990