

IEC 61850 Certificate Level A¹

No. 10078062-INC 18-2339

Issued to: Schweitzer Engineering Laboratories, Inc 2350 NE Hopkins Court Pullman, WA 99163-5603 USA

For the server product:

SEL-2440 Discrete Programmable Automation Controller Firmware version: SEL-2440-R215-V0-Z007004-D20180131 IEC 61850 library ID: 5FEA494D S/N: 1172080316

The server product has not been shown to be non-conforming to:

IEC 61850 Edition 2 Parts 6, 7-1, 7-2, 7-3, 7-4 and 8-1

Communication networks and systems for power utility automation

The conformance test has been performed according to IEC 61850-10 Edition 2, the UCA International Users Group Edition 2 Server Test Procedures version 1.0 with TPCL² 1.2.4 with product's protocol, model and technical issue implementation conformance statements: "Protocol Implementation Conformance Statement for the IEC 61850 interface in SEL-2440, January 10, 2018, "Model Implementation Conformance Statement for the IEC 61850 interface in SEL-2440, January 10, 2018" and "TISSUES Implementation Conformance Statement for the IEC 61850 interface in SEL-2440, January 22, 2018" and the extra information for testing: "Protocol Implementation eXtra Information for Testing (PIXIT) for the IEC 61850 interface in SEL-2440, January 22, 2018".

The following IEC 61850 conformance blocks have been tested with a positive result (number of relevant and executed test cases / total number of test cases):

| 2 5 | Basic Exchange (18/26) Data Sets (4/7) Unbuffered Reporting (17/21) Buffered Reporting (25/30) | 9b 12a 12c | GOOSE Publish (9/13) GOOSE Subscribe (13/14) Direct Control (5/18) Enhanced Direct Control (5/20) Enhanced SBO Control (13/28) |
|--------|---|------------------|--|
| | | | Enhanced SBO Control (13/28) Time Synchronization (3/7) |

This certificate includes a summary of the test results as carried out at DNV GL in The Netherlands with UniGrid SA Simulator 1.4 with test suite 1.0.55 and UniCA 61850 Analyzer 5.31.02. This document has been issued for information purposes only, and the original paper copy of the DNV GL verification report No. 10076082-INC 18-2338 will prevail.

The test has been carried out on one single specimen of the product as referred above and submitted to DNV GL by Schweitzer Engineering Laboratories. The manufacturer's production process has not been assessed. This certificate does not imply that DNV GL has approved any product other than the specimen tested.

Arnhem, April 5, 2018

> MS.

E. Henriquez Business leader Interoperability of Smart Power Systems

Issued by:





 1 Level A - Independent test lab with certified ISO 9001 Quality System 2 TPCL - Test procedures change list

Copyright © DNV GL Netherlands B.V. Arnhem, the Netherlands. All rights reserved. It is prohibited to update or change this certificate in any manner whatsoever, including but not limited to dividing it into parts.



IEC 61850 Certificate Level A No. 10078062-INC 18-2339

Applicable Test Procedures from the UCA International Users Group Edition 2 Server Test Procedures version 1.0 with TPCL 1.2.4

| Conformance Block | | Mandatory | Conditional |
|-------------------|----------------------------|--|--------------------------------|
| 1: | Basic Exchange | sAss1, sAss2, sAss3, sAssN2, sAssN3, sAssN4, sAssN5, sSrv1, sSrv2, sSrv3, sSrv4, sSrv5, sSrvN1abcd, sSrvN4 | sAssN6, sSrv8, sSrv10, sSrvN1f |
| 2: | Data Sets | sDs1, sDs10a, sDsN1ae | sDs15 |
| 5: | Unbuffered Reporting | sRp1, sRp2, sRp3, sRp4, sRp5, sRp9, sRp14, sRp15, sRpN1, sRpN2, sRpN3, sRpN4, sRpN8 | sRp8, sRp10, sRp11, sRp12 |
| 6: | Buffered Reporting | sBr1, sBr2, sBr3, sBr4, sBr5, sBr9, sBr14, sBr15, sBr20, sBr21, sBr22, sBr25, sBr26, sBr27, sBr28, sBrN1, sBrN2, sBrN3, sBrN4, sBrN5, sBrN8 | sBr8, sBr10, sBr11, sBr12 |
| 9a: | GOOSE publish | sGop2a, sGop3, sGop4, sGop9, sGop10, sGop11 | sGop1, sGop5, sGop7 |
| 9b: | GOOSE subscribe | sGos1, sGos2, sGos3, sGos5, sGos6a, sGos7, sGosN1, sGosN2, sGosN3, sGosN4, sGosN5, sGosN6 | sGos6b |
| 12a: | Direct control | sCtl5, sCtl10, sDOns1, sDOns2 | sCtl16 |
| 12c: | Enhanced Direct Control | sCtl5, sCtl10, sDOes1, sDOes2 | sCtl16 |
| 12d: | Enhanced SBO Control | sCtl5, sCtl8, sCtl9, sCtl10, sCtl11, sCtl25, sSBOes1, sSBOes2, sSBOes6, sSBOes8 | sCtl6, sCtl16, sCtl26 |
| 13: | Time sync | sTm1, sTm2, sTmN1 | |