


SEL-3061

Cellular Router



Confidently apply secure cellular wireless communications to critical infrastructure applications

- Cellular wireless connectivity provides access to remote equipment and installations.
- Comprehensive security methods ensure the confidentiality and integrity of data.
- A web interface simplifies configuration and provides device management and diagnostic information.
- Multicarrier support enables fast deployment across the United States, including AT&T, FirstNet, Verizon, T-Mobile, and other roaming partners.
- Design and testing to protective relay standards ensures electromagnetic compatibility and surge immunity.



Applications


Communications to Substations

Use the SEL-3061 to communicate with substation equipment over secure cellular networks. The SEL-3061 is certified to operate across a broad range of cellular network operators. With LTE technology, which has as much as 150 Mbps downlink and 50 Mbps uplink, the SEL-3061 can be the primary communications link or it can be a redundant link to a fiber cable.




Backhaul for SEL Fault and Load Transmitter and Receiver Systems

Use the SEL-3061 to communicate with fault indicators and transmitters, including LINAM® FLT Fault and Load Transmitters. The LINAM FLR Fault and Load Receiver collects fault and load data from LINAM FLT transmitters, and then the SEL-3061 backhauls that information to a centralized location.




Distribution Network Automation

Provide communications for distribution automation with the SEL-3061. You can implement cost-effective radio links for collecting SCADA, metering, and synchrophasor data from field devices and for engineering access to devices.



Industrial Oil and Gas Systems

Provide real-time data collection for analysis and alarm detection. Radios create communications links to tanks, wellheads, Lease Automatic Custody Transfer (LACT) units, flow lines, pumps, valves, and test stations for improved safety and cost savings through efficiency gains.



SEL-3061 Specifications

General

Operating Temperature Range	−40° to +75°C (−40° to +167°F)
Relative Humidity Range	15–93%, noncondensing
Antenna Connector Type	SMA
Ports	1 Ethernet, 1 serial
Dimensions	5.96" × 4.08" × 1.73" (151 mm × 104 mm × 44 mm)
Communications	4G LTE with AT&T, FirstNet, Verizon, T-Mobile, and other roaming partners
Bands	4G LTE: B2, B4, B5, B12, B13, B14, B66, B71 3G fallback (AT&T and T-Mobile only): B2, B4, B5
Power	12–30 Vdc, <5 W
Security	IPsec data encryption Secure VPN connections (5 concurrent VPN tunnels) SPI firewall User-set Destination Network Address Translation (DNAT), Source Network Address Translation (SNAT), and filter rules for accepting, rejecting, dropping, and logging packets Transport Layer Security (TLS) for Serial-IP connections MAC address filtering Syslog
Management	SNMP-based network monitoring HTTPS web interface Over-the-air settings changes and firmware upgrades Centralized user management using RADIUS
Warranty	10 years

SCHWEITZER ENGINEERING LABORATORIES

Making Electric Power Safer, More Reliable, and More Economical
+1.509.332.1890 | info@selinc.com | selinc.com

© 2026 by Schweitzer Engineering Laboratories, Inc.
PF00555 • 20260331

