




SCHWEITZER ENGINEERING LABORATORIES
2350 NE Hopkins Court Pullman, WA 99163-5603 USA
Phone:(509) 332-1890 Fax:(509) 332-7990
Internet:www.selinc.com E-mail:info@selinc.com

CABLE C553



32-POSITION
SOCKET CONTACT CIRCULAR

32-POSITION
SOCKET CONTACT CIRCULAR

CABLE: Shielded, 24 Conductor, 20 AWG Tinned Copper, polyurethane jacket

12 VDC WHET	I1	A	WHT	A	I1
	I2	B	WHT/BLK	B	I2
	I3	C	WHT/BRN	C	I3
	IN	D	WHT/RED	D	IN
	F	F	WHT/GRY	F	12 VDC WHET
	GND	G	SHIELD WIRE	G	GND
	GND	H	SHIELD WIRE	H	GND
	V1Y	J	GRN	J	V1Y
	V2Y	K	BLU	K	V2Y
	V3Y	L	VIO	L	V3Y
	NY	M	YEL	M	NY
	V1Z	N	BRN	N	V1Z
	V2Z	P	RED	P	V2Z
	V3Z	R	ORG	R	V3Z
	NZ	S	BLK	S	NZ
	GND	T	SHIELD WIRE	T	GND
	52a1	U	WHT/BLK/BRN	U	52a1
	52a2	V	WHT/BLK/RED	V	52a2
	52a3	W	WHT/BLK/ORG	W	52a3
	69	X	WHT/BLK/YEL	X	69
	CLOSE1	Y	WHT/ORG	Y	CLOSE1
	TRIP1	Z	WHT/YEL	Z	TRIP1
	CLOSE2	f	WHT/GRN	f	CLOSE2
	TRIP2	g	GRY	g	TRIP2
	CLOSE3	h	WHT/BLU	h	CLOSE3
	TRIP3	j	WHT/VIO	j	TRIP3

Comments: Base mode (unarmored): max 100 ft

8/4/2026

Partially armored (10 ft on controller end): max 100 ft

Fully armored: max 65 ft.

The armoring consists of flexible liquid-tight steel with UV resistant, flame-retardant PVC Jacket.