




SCHWEITZER ENGINEERING LABORATORIES
2350 NE Hopkins Court Pullman, WA 99163-5603 USA
Phone:(509) 332-1890 Fax:(509) 332-7990
Internet:www.selinc.com E-mail:info@selinc.com

CABLE C551



32-POSITION
PIN CONTACT CIRCULAR

42-POSITION
SOCKET CONTACT RECTANGULAR

CABLE: Shielded, 33 conductor, 20 AWG tinned copper, polyurethane jacket

12 VDC WHET	I1	A	BLK	21	I1
	I2	B	BRN	28	I2
	I3	C	RED	35	I3
	IN	D	ORG	27	IN
	F		VIO	29	12 VDC WHET
	GND	G	SHIELD WIRE	25	GND
	GND	H	SHIELD WIRE	19	GND
	V1Y	J	WHT/BLK/ORG	36	V1Y
	V2Y	K	WHT/BLK/YEL	37	V2Y
	V3Y	L	WHT/BLK/GRN	38	V3Y
	NY	M	WHT/BLK/BLU	30	NY
	V1Z	N	WHT/BRN/RED	40	V1Z
	V2Z	P	WHT/BRN/ORG	41	V2Z
	V3Z	R	WHT/BRN/YEL	42	V3Z
	NZ	S	WHT/BRN/GRN	39	NZ
	GND	T	SHIELD WIRE	20	GND
	52a1	U	GRY	9	52a1
	52a2	V	WHT	8	52a2
	52a3	W	WHT/BLK	1	52a3
	69	X	WHT/BRN	15	69
CLOSE1	Y		WHT/YEL	2	CLOSE1
TRIP1	Z		WHT/GRN	3	TRIP1
CLOSE2	f		WHT/BLU	4	CLOSE2
TRIP2	g		WHT/VIO	5	TRIP2
CLOSE3	h		WHT/GRY	6	CLOSE3
TRIP3	j		WHT/BLK/BRN	7	TRIP3

Comments: Base mode (unarmored): max 100 ft

Partially armored (10 ft on controller end): max 100 ft

Fully armored: max 65 ft.

The armoring consists of flexible liquid-tight steel with UV resistant, flame-retardant PVC Jacket.

8/4/2026