

SEL-2595

Teleprotection Terminal, IEEE C37.94 Compliant, Communications Device

Part Number:

2	5	9	5	0					X
---	---	---	---	---	--	--	--	--	---

Mounting

Horizontal Rack Mount					0				
-----------------------	--	--	--	--	---	--	--	--	--

Power Supply

48/125 Vdc or 120 Vac						3			
125/250 Vdc or 120/230 Vac						4			

Fiber Optic Options

820nm IEEE C37.94, Multimode Fiber							C		
1300nm (IEEE C37.94 Modulation), Single-mode Fiber*							H		

Control Input Voltage

24 Vdc								1	
48 Vdc								2	
110 Vdc								3	
125 Vdc								4	
220 Vdc								5	
250 Vdc								6	


I/O Board Configuration

I/O Board with 8 Standard Outputs, 8 Inputs									1
I/O Board with 8 High-Speed High-Current Outputs, 8 Inputs*							C		5

* Additional Cost

Note: Order part number 9260023 for additional SEL-2595 Label Kits.

For ST[®]-terminated 62.5-µm core fiber-optic patchcords, use SEL-C807 Multimode Fiber-Optic Patchcord (WI-4132).
 For ST-terminated 9-µm core fiber-optic patchcords, use SEL-C809 Single-Mode Fiber-Optic Patchcord (WI-4133).



The SEL-2595 applied with IEEE C37.94 Compliant Digital Multiplexers

All brand or product names appearing in this document are the trademark or registered trademark of their respective holders.

Making Electric Power Safer, More Reliable, and More Economical[®]

SEL SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA
 Phone: +1.509.332.1890 - Fax: +1.509.332.7990