

SEL-C809 Singlemode Fiber-Optic Cable

9 Micrometer Core Diameter

Part Number:

C	8	0	9					0				X				
---	---	---	---	--	--	--	--	---	--	--	--	---	--	--	--	--

Cable Construction⁽¹⁾

Simplex 1 Fiber ^{(2)*}					Z	0	1									
Zipcord 2 Fibers ^{(2)*}					Z	0	2									
Heavy-Duty Waterproof 2 Fibers ^{(2)*}					G	0	2									
Simplex 1 Fiber (Plenum) ^{(3)*}					P	0	1									
Zipcord 2 Fibers (Plenum) ^{(3)*}					P	0	2									

Jacket Marking

Standard										0						
----------	--	--	--	--	--	--	--	--	--	---	--	--	--	--	--	--

Termination

Bulk Cable: No Terminations										0	0					
ST [®] Connector on Both Ends										S	S					
LC Connector on Both Ends										L	L					
LC Connector to ST Connector										L	S					
SC Connector on Both Ends										C	C					
SC Connector to ST Connector										C	S					
SC Connector to LC Connector										C	L					

Other Options

No Options													X			
------------	--	--	--	--	--	--	--	--	--	--	--	--	---	--	--	--

Length

Specify length Enter length in meters with leading zeros.
(Example: 15 meters = 0015)

--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--

Accessories

Field Termination Kit*	2	4	0	-	1	5	4	0
ST Connector*	2	4	0	-	1	5	4	6
LC Connector*	2	4	0	-	1	5	4	8
SC Connector*	2	4	0	-	1	5	4	7
ST Connector Splice Bushing*	0	9	0	-	5	0	1	2
LC Connector Splice Bushing*	2	4	0	-	1	8	1	0
SC Connector Splice Bushing *	2	4	0	-	1	8	1	1
Magnetic Cable Guide*	M	C	G					

* Additional Cost

⁽¹⁾ Cables are priced per options selected.

⁽²⁾ Riser (OFNR) rated cable, for use in riser and general purpose building applications.

⁽³⁾ Plenum (OFNP) rated cable, for use in plenum, riser and general purpose building applications.

SEL SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court - Pullman, WA 99163 USA
Phone: +1.509.332.1890 - Fax: +1.509.332.7990