



SEL-2242 Chassis/Backplane

The SEL-2242 Chassis/Backplane is a 10-slot chassis for SEL Axion[®] systems. This data sheet provides installation instructions and specifications.

Front and Rear View




Figure 1 SEL-2242 10-Slot Front Panel, Rack-Mount



Figure 2 SEL-2242 10-Slot Front Panel 7-Inch Touchscreen Display




Figure 3 SEL-2242 10-Slot Rear View, Panel-Mount



Figure 4 SEL-2242 4-Slot Front Panel, Rack-Mount




Figure 5 SEL-2242 4-Slot Rear View, Panel-Mount



Figure 6 SEL-2242 Dual 4-Slot Front Panel, Rack-Mount




Figure 7 SEL-2242 Dual 4-Slot Rear View, Panel-Mount

Device Placement

NOTE: For applications compliant with IEC 60255-26, surface-mount units must be installed in IP4X enclosures.

You can mount the Axion in a sheltered indoor environment (a building or an enclosed cabinet) that does not exceed the temperature and humidity ratings for the modules. Equipment must be installed in an enclosure

that protects against shock and fire to meet UL requirements. Configurations with an SEL-2245-42 as the right-most module in a backplane should have the backplane installed in a metal enclosure to meet Radiated RF Immunity type test requirements. The Axion must be mounted such that modules are vertical and have at least 0.5 inches to the nearest solid surface above and below.









Figure 8 SEL-2242 10-Slot Rack- and Surface-Mount Dimensions

Note: The 10-slot backplane equipped with LDM is not compatible with surface mount.








i9285b

Figure 13 SEL-2242 Dual 4-Slot Rack- and Surface-Mount Dimensions



i9408a

Figure 14 SEL-2242 for Dual 4-Slot Panel-Mount Dimensions

Protective Connector Covers

The SEL-2242 is shipped with protective covers installed in each backplane connector. Prior to installing any Axion modules, grasp either side of the connector cover and pull it straight out of the connector. We suggest that you leave the covers inserted in any unused slots in order to provide dust and mechanical protection.




Figure 15 Protective Connector Cover

Specifications

Compliance

Designed and manufactured under an ISO 9001 certified quality management system
 UL Listed to U.S. and Canadian safety standards (File E220228; NRAQ, NRAQ7)
 CE Mark
 UKCA Mark

Product Standards

IEC 60255-26:2013 - Relays and Protection Equipment: EMC
 IEC 60255-27:2014 - Relays and Protection Equipment: Safety
 IEC 60825-2:2004 +A1:2007 +A2:2010 for fiber-optic communications
 IEC 61850-3:2013 - Comm Systems for Power Utility Automation

General

Operating and Storage Temperature Range

−40° to +85°C (−40° to +185°F)
 Units should be stored and transported in their original packaging.

Note: Operating temperature evaluated for UL ambient 0° to 40°C.
Note: The optional front-panel LCD is impaired for temperatures below −20°C and above +70°C.

Operating Environment

Pollution Degree: 2
 Overvoltage Category: II
 Insulation Class: 1
 Relative Humidity: 5–95%, noncondensing
 Maximum Altitude: 2000 m
 Vibration, Earth Tremors: Class 1

Backplane (SEL-2242)

Ethernet Port

Port: 1
 Data Rate: 10/100 Mbps
 Connector: RJ45 Female
 Protocol: Engineering Access

Note: SEL-2242 Ethernet port is included with the optional touchscreen, 10-slot model only.

Fuse Rating
 Non-Serviceable: 2.5 A, 125 V, time lag T

Type Tests

Note: To ensure protection-level EMI and EMC performance, type tests were performed using shielded Ethernet cables with the shield grounded at both ends of the cable.

Electromagnetic Compatibility Emissions

Conducted and Radiated Emissions (Class A): CISPR 11:2009+A1:2010
 CISPR 22:2008
 FCC 15.107:2014
 FCC 15.109:2014
 47 CFR Part 15.109
 47 CFR Part 15.107
 ICES-003, Issue 6
 Canada ICES-001 (A) / NMB-001 (A)

Electromagnetic Compatibility Immunity

Conducted RF Immunity: IEC 61000-4-6:2013
 Severity Level: 10 Vrms
 Electrostatic Discharge Immunity: IEC 61000-4-2:2008
 IEEE C37.90.3-2001
 Severity Level:
 2, 4, 6, 8 kV contact discharge
 2, 4, 8, 15 kV air discharge

Fast Transient/Burst Immunity:	IEC 61000-4-4:2012 Severity Level: 2 kV, 5 kHz on communications lines
Magnetic Field Immunity:	IEC 61000-4-8:2009 Severity Level: 1,000 A/m for 3 s 100 A/m for 60 s IEC 61000-4-9:2016 Severity Level: 1,000 A/m IEC 61000-4-10:2016 Severity Level: 100 A/m for 2 s at 100 kHz and 1 MHz
Power Supply Immunity:	IEC 61000-4-11:2004 IEC 61000-4-17:1999+ A1:2001+A2:2008 IEC 61000-4-29:2000
Radiated Radio Frequency:	IEC 61000-4-3:2006+A1:2007+A2:2010 Severity Level: 10 V/m IEEE C37.90.2-2004 Severity Level: 20 V/m
Slow Damped Oscillatory Waves:	IEC 61000-4-18:2006+A1:2010 Severity Level: Communications ports 1.0 kV peak common mode
Surge Withstand Capability:	IEEE C37.90.1-2012 Severity Level: 2.5 kV oscillatory 4 kV fast transient
Surge Immunity:	IEC 61000-4-5:2005 Severity Level per IEC 60255-26:2013*: Zone A: 2 kV line-to-line 4 kV line-to-earth

Environmental

Change of Temperature:	IEC 60068-2-14:2009 Severity Level: 5 cycles, 1°C per minute ramp -40° to +85°C
Cold, Operational and Cold, Storage:	IEC 60068-2-1:2007 Severity Level: 16 hours at -40°C

Damp Heat, Cyclic:	IEC 60068-2-30:2005 Severity Level: 12 + 12-hour cycle 25° to 55°C, 6 cycles, >93% RH
Damp Heat, Steady:	IEC 60068-2-78:2001 Severity Level: 40°C, 240 hours, >93% RH
Dry Heat, Operational and Dry Heat, Storage:	IEC 60255-1:2009 IEC 61850-3:2013 IEC 60068-2-2:2007 Severity Level: 16 hours at 85°C
Change of Temperature:	IEC 60068-2-14:2009 1 deg. per minute, -40° and +85°C, 5 cycles
Free Fall:	IEEE 1613-2009 Severity Level: 100 mm
Vibration:	IEC 60255-21-1:1988 Severity Level: Endurance Class 2 Response Class 2 IEC 60255-21-2:1988 Severity Level: Shock Withstand, Bump Class 1 Shock Response Class 2 IEC 60255-21-3:1993 Severity Level: Quake Response Class 2

Safety

Enclosure Protection*:	IEC 60529:1989+A1:1999+A2:2013 Severity Level: IP4X on all sides
------------------------	--

* Self declared rating.

Technical Support

We appreciate your interest in SEL products and services. If you have questions or comments, please contact us at:

Schweitzer Engineering Laboratories, Inc.
2350 NE Hopkins Court
Pullman, WA 99163-5603 U.S.A.
Tel: +1.509.338.3838
Fax: +1.509.332.7990
Internet: selinc.com/support
Email: info@selinc.com

Notes

© 2021–2025 by Schweitzer Engineering Laboratories, Inc.

Content subject to change without notice.

Unless otherwise agreed in writing, all SEL product sales are subject to SEL's terms and conditions located here: <https://selinc.com/company/termsandconditions/>.

SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court • Pullman, WA 99163-5603 U.S.A.

Tel: +1.509.332.1890 • Fax: +1.509.332.7990

selinc.com • info@selinc.com



* P D S 2 2 4 2 - 0 1 *