



SEL-487B-2 Bus Differential and Breaker Failure Relay

Bus Differential and Breaker Failure Relay With Sampled Values or TiDL Technology




Key Features and Benefits

The SEL-487B-2 Bus Differential and Breaker Failure Relay with Sampled Values (SV) or TiDL[®] Technology provides bus-current differential protection, circuit-breaker failure protection, and backup overcurrent protection.

- ▶ **High-Speed Differential Protection.** Busbar differential protection operates in less than one cycle, which increases system stability margins and reduces equipment damage.
- ▶ **Six Differential Zones.** Flexible zone selection and six differential zones provide protection for multiple busbar applications.
- ▶ **Failed CT Detection.** The SEL-487B reliably indicates open and shorted CTs for alarming and/or blocking.
- ▶ **CT Ratio Mismatch.** Differential protection accommodates as high as 10:1 CT ratio mismatch without auxiliary CTs.
- ▶ **External Fault Security.** External fault detection logic secures differential protection for external faults with minimal CT requirements.
- ▶ **Overcurrent Elements.** Instantaneous and inverse time-overcurrent elements can provide backup protection for each terminal.
- ▶ **Voltage Elements.** Negative- and zero-sequence, over- and undervoltage elements can supervise the differential element.
- ▶ **Three Check Zones.** Three dedicated check zones in each relay can supervise complex bus differential schemes.
- ▶ **Breaker Failure.** Apply the relay to supply breaker failure protection for all supported breakers. Logic for breaker failure retrip and initiation of transfer tripping is included.
- ▶ **Ethernet Access.** The Ethernet card grants access to all relay functions. Use IEC 61850 Manufacturing Message Specification (MMS) or DNP3 protocol directly to interconnect with automation systems. You can also connect to DNP3 networks through a communications processor. Use File Transfer Protocol (FTP) for high-speed data collection.
- ▶ **Serial Data Communication.** The relay can communicate serial data through SEL ASCII, SEL Fast Message, SEL Fast Operate, MIRRORING BITS[®], and DNP3 protocols.

- ▶ **Automation.** The enhanced automation features include programmable elements for local control, remote control, protection latching, and automation latching. Local metering on the large front-panel LCD eliminates the need for separate panel meters. Serial and Ethernet links efficiently transmit key information, including metering data, protection element and control I/O status, IEC 61850 Edition 2 GOOSE messages, Sequential Events Recorder (SER) reports, relay summary event reports, and time synchronization. Apply expanded SELOGIC[®] control equations with math and comparison functions in control applications. Incorporate as many as 1000 lines of automation logic to accelerate and improve control actions.
- ▶ **Battery Monitoring.** An alarm contact provides notification of substation battery voltage problems even if voltage is low only during trip or close operations.
- ▶ **Digital Secondary Systems (DSS) Technologies.** You can order the relay as either an SV subscriber relay or a TiDL relay. DSS capable relays receive current and voltage information that is published by remote merging units instead of standard PT and CT inputs. DSS technologies reduce copper cable lengths and associated installation labor costs and improve the overall safety of the substation.
- ▶ **IEC 61850-9-2LE SV Relay.** The SV subscriber relay can subscribe to current and voltage information that is published by as many as seven SV merging units that are compliant with the IEC 61850-9-2LE guideline.
- ▶ **TiDL Relay.** The TiDL relay can receive current and voltage information from as many as eight SEL-TMUs (TiDL Merging Units) over direct point-to-point fiber-optic connections. The TiDL relay automatically synchronizes data collection, alleviating the need or impact of an external clock on protection.
- ▶ **Selective Protection Disabling.** The subscriber or TiDL relay provides selective disabling of protection functions by using hard-coded logic or available torque-control equations in case of a loss of communications between your merging unit and relay that results in the loss of relevant analog data.
- ▶ **Current Summation.** The relay can combine multiple SV stream currents to simplify external wiring.
- ▶ **Six Independent Settings Groups.** The relay includes group logic to adjust settings for different operating conditions, such as station maintenance, seasonal operations, emergency contingencies, loading, source changes, and adjacent relay settings changes. Select the active group settings by control input, command, or other programmable conditions.
- ▶ **Parallel Redundancy Protocol (PRP).** PRP provides seamless recovery from any single Ethernet network failure. The Ethernet network and all traffic are fully duplicated with both copies operating in parallel.
- ▶ **IEC 61850 Operating Modes.** The relay supports IEC 61850 standard operating modes such as Test, Blocked, On, and Off.
- ▶ **IEEE 1588, Precision Time Protocol (PTP).** PTP provides high-accuracy timing over an Ethernet network.
- ▶ **Digital Relay-to-Relay Communications.** MIRRORING BITS communications can monitor internal element conditions between bays within a station, or between stations, using SEL fiber-optic transceivers. Send digital, analog, and virtual terminal data over the same MIRRORING BITS channel.
- ▶ **Sequential Events Recorder (SER).** The SER records the last 1000 events, including setting changes, startups, and selectable logic elements.
- ▶ **Oscillography and Event Reporting.** The relay records voltages, currents, and internal logic points at a sampling rate as fast as 8 kHz. Offline phasor and harmonic-analysis features allow investigation of bay and system performance. Time-tag binary COMTRADE event reports with high-accuracy time stamping for accuracy better than 10 μ s.
- ▶ **Digitally Signed Upgrades.** The relay supports upgrading the relay firmware with a digitally signed upgrade file. The digitally signed portion of the upgrade file helps ensure firmware and device authenticity after it is sent over a serial or Ethernet connection.
- ▶ **Increased Security.** The relay divides control and settings into seven relay access levels; the relay has separate breaker, protection, automation, and output access levels, among others. Set unique passwords for each access level.
- ▶ **Rules-Based Settings Editor.** You can communicate with and set the relay by using an ASCII terminal or use Grid Configurator to configure the relay and analyze fault records with relay element response. Use as many as 200 aliases to rename any digital or analog quantity in the relay.

Functional Overview



ANSI NUMBERS/ACRONYMS AND FUNCTIONS	
27/59	Over- and Undervoltage
50	Overcurrent (Phase)
50BF	Breaker Failure Overcurrent
51	Time-Overcurrent (Phase)
87	Current Differential

ADDITIONAL FUNCTIONS	
16 SEC	Access Security (Serial, Ethernet)
85 RIO	SEL MIRRORBITS Communications
DFR	Event Reports
LGC	SELLogic Control Equations
MET	High-Accuracy Metering
RTU	Remote Terminal Unit
SBM	Station Battery Monitor
SER	Sequential Events Recorder

ADDITIONAL FEATURES	
Open CT Detection	
Three Independent Check Zones	
Disconnect Status and Monitoring Logic for 60 Disconnects	
Single-Relay Application: 2 Three-Phase Zones for as many as 7 Terminals	
Two-Relay Application: 3 Three-Phase Zones for as many as 10 Terminals	
Three-Relay Application: 6 Single-Phase Zones for as many as 21 Terminals	

Five-port Ethernet card ordering option depicted.

Figure 1 SEL-487B Functional Overview

SV

The SEL-487B subscribes to data streams that are published by merging units, such as the SEL-421-7 SV Publisher or SEL-401 Protection, Automation, and Control Merging Unit. The SEL-421-7 SV Publisher provides full backup protection while the SEL-401 can provide basic phase overcurrent and breaker-failure protection in the absence of communication. The data may be synchronized using Precision Time Protocol (PTP).




Figure 2 SV Network

TiDL

The SEL-487B-2 TiDL receives and automatically synchronizes data streams from connected and commissioned SEL-TMUs. The TiDL technology does not require an external time source for local relay protection functions.




Figure 3 SEL TiDL System

Protection Features

Differential Protection

The SEL-487B includes six independent current differential elements. Operating time for internal faults, including high-speed output contact closure, is less than one cycle. *Figure 4* shows an example of an internal fault and differential element operation.




Figure 4 Differential Element Operation in Less Than One Cycle for Internal Faults

Each of the differential elements provides the following:

- Fast operating times for all busbar faults
- Security for external faults with heavy CT saturation
- Security with subsidence current present
- High sensitivity for busbar faults
- Minimum delay for faults evolving from external to internal faults

Figure 5 shows a block diagram of one of the six differential protection elements.




Figure 5 External Fault Detection Logic Increases Differential Element Security

CT saturation is one of the main factors to address when considering relay security. Because of the high sampling rate, the fault detection logic detects external faults in less than 2 ms by comparing the rate of change of the restraint and operating currents. Following the detection of an external fault, the relay enters a high-security mode, during which it dynamically selects a higher slope for the differential elements (see *Figure 5*). *Figure 6* shows an external fault with heavy CT saturation, without differential element operation.




Figure 6 Differential Element Does Not Operate for External Fault With Heavy CT Saturation

Dynamic Zone Configuration

The SEL-487B dynamically assigns the input currents to the correct differential elements without the need for auxiliary relays. Connect the digital inputs from the busbar disconnect auxiliary contacts directly to the relay. SELGIC control equations and zone selection logic will correctly assign the currents to the differential elements, even for complex bus arrangements such as the one in *Figure 7*.

Busbar configuration information, as a function of the disconnect status, is readily available. *Figure 8* depicts the response of the relay to the **ZONE** command, showing the terminals and bus zones assigned to each protection zone.




Figure 7 Bus-Zone Protection Based on Disconnect Switch Positions

```

=>>ZONE <Enter>
BUS PROTECTION
Rinadel Station
Terminals in Protection Zone 1
HELIUM SILICON
Bus-Zones in Protection Zone 1
NORTH
Terminals in Protection Zone 2
BORON ARGON LITHIUM
Bus-Zones in Protection Zone 2
EAST
Terminals in Protection Zone 3
SILICON KRYPTON
Bus-Zones in Protection Zone 3
SOUTH
Terminals in Protection Zone 4
SODIUM NEON
Bus-Zones in Protection Zone 4
WEST
=>>
    
```

Figure 8 Result of ZONE Command, Indicating the Protection Zone Configuration According to Disconnect Switch Positions




Figure 9 Bus Arrangement With Disconnect DS2 Closed; the New Zone 1 That Includes Bus Zones North and East

```

=>>ZONE <Enter>
BUS PROTECTION
Rinadel Station
Terminals in Protection Zone 1
HELIUM SILICON BORON ARGON
LITHIUM
Bus-Zones in Protection Zone 1
NORTH EAST
Terminals in Protection Zone 3
SILICON KRYPTON
Bus-Zones in Protection Zone 3
SOUTH
Terminals in Protection Zone 4
SODIUM NEON
Bus-Zones in Protection Zone 4
WEST
=>>
    
```

Figure 10 Result of ZONE Command, Showing the Protection Zone Configuration After Zone 1 Merges With Zone 2

Closing disconnect DS2 combines Zone 1 and Zone 2, resulting in a single zone. *Figure 9* shows the new protection zone configuration. In this combination, Zone 1 includes North and East bus-zones. *Figure 10* shows the new Zone 1 that includes bus-zones North and East.

Zone Selection Logic

Busbar protection requires assignment of the correct current values to the appropriate differential elements as a function of user-defined conditions. To achieve this, the SEL-487B employs a two-step process:

- Evaluates the user-defined conditions.
- Assigns the currents to the differential element of the appropriate zone.

Current assignment conditions vary from simple to complex. A simple condition would be a statement such as “always include this terminal in the differential calcula-

tions.” A more complex condition statement could be “when Disconnect 2 is closed, and the transfer disconnect is open.”

SELOGIC control equations provide the mechanism by which the user enters the conditions for assigning the currents to the differential elements when these conditions are met. When a SELOGIC control equation becomes true (e.g., the disconnect is closed), the relay dynamically assigns the current to the differential elements. Conversely, when the SELOGIC control equation is false (the disconnect is open), the relay dynamically removes the currents from the differential elements. This is also true for the trip output. When the SELOGIC control equation of a terminal is false, the relay issues no trip signal to that terminal. *Table 1* shows a simple case where the disconnect status is the only condition for the relay to consider.

Table 1 Conditions for Automatic Terminal Assignment

Example of Condition	SELOGIC Control Equation Result	Consider Terminal in Protection Calculations?	Issue Trip?
Disconnect is open	False	No	No
Disconnect is closed	True	Yes	Yes

End-Zone Protection

To illustrate the flexibility of use of SELOGIC control equations for user-defined conditions, consider the ease of achieving end-zone protection with the SEL-487B.

Figure 11 shows fault F1 between an open circuit breaker and CT of a feeder at a substation. This area is a dead zone because neither busbar protection nor local line protection can clear this fault; the remote end of the feeder must clear this fault. Because the feeder circuit breaker is already open, operation of the busbar protection serves no purpose. The busbar protection must not operate for this fault.




Figure 11 Fault Between Breaker and CT

By including the circuit breaker auxiliary contact in one of the SELOGIC control equations (*Figure 12*), we can cause the value of the SELOGIC control equation to be false when the circuit breaker is open, removing the current from the differential element calculations. This capability ensures stability of the busbar protection. By

our use of SELOGIC control equations and normal communications channels to configure the protection system, the relay sends a trip signal to the remote end of the feeder.




Figure 12 Bus Protection Is Not Affected by Fault, F1; Use Transfer Trip to Clear the Fault

Check Zones

The SEL-487B provides three completely independent check zones, each with its own adaptive differential element. Supervise zone differential elements by using the independent check zones to monitor all incoming sources and outgoing feeders on a per-phase basis. During an internal fault, the check zone differential element will assert. During an external fault, the check zone element will remain deasserted.

CT Supervision

Open or shorted current transformers produce equal and opposite changes in restraint and operate current. The advanced CT supervision in the SEL-487B monitors differential zone restraint and operating current for these changes, to provide rapid and dependable detection of open or shorted CT conditions. Use the CT supervision logic in zone trip equations.

Disconnect Status Monitor

Figure 13 shows the disconnect open and close contact relationship. During the open-to-close operation, the 89b contact must open (disconnect is CLOSED) during the transition zone before the main contact arcing starts. The 89a contact must close in this transition zone.

During the close-to-open operation, the 89b contact must close during the transition zone after the main contact arcing is extinguished (disconnect is OPEN), as shown in *Figure 13*. The 89a contact must open in this transition zone.

Table 2 shows the four possible disconnect auxiliary contact combinations and how the relay interprets each combination.

Table 2 Disconnect Status as a Function of the Auxiliary Contacts

89a	89b	Relay 89 Status Interpretation
0	0	Closed
0	1	Open
1	0	Closed
1	1	Closed




Figure 13 Disconnect Switch Auxiliary Contact Requirements for the Zone Selection Logic; No CT Switching Required

Tie-Breaker Configurations

Figure 14, Figure 15, and Figure 16 show three tie-breaker schemes:

- Two CTs configured in overlap (Figure 14)
- A single CT with two cores configured in overlap (Figure 15)
- Two CTs configured with a differential element across the breaker (Figure 16)

Configure any one of these schemes without using external auxiliary relays. Figure 14 and Figure 15 also show the tie breaker closing onto an existing fault, F1. The SEL-487B includes tie-breaker logic to prevent the loss of both zones for this fault.




Figure 14 Two CTs Configured in Overlap




Figure 15 A Single CT With Two CT Cores Configured in Overlap

Configure one of the differential zones as a differential across the tie breaker. This arrangement has the following advantages:

- Both main zones are secure for a fault between the tie breaker and the CT.
- Only one main zone is tripped for a fault between the tie breaker and the CT (as opposed to both main zones with an overlapping tie-breaker arrangement).




Figure 16 Two CTs Configured With a Differential Element Across the Breaker

Applications

Figure 17 and Figure 18 show a station with a double bus configuration in both a SV installation (Figure 17) and a TiDL installation (Figure 18).




Figure 17 Double-Breaker Double-Bus Application (SV)




Figure 18 Double-Breaker Double-Bus Application (TiDL)

Additional Features

Front-Panel Display

The LCD shows event, metering, setting, and relay self-test status information.

The LCD is controlled by the navigation pushbuttons (Figure 20), automatic messages the relay generates, and programmable display points. The rotating display scrolls through any active, nonblank display points. If none are active, the relay scrolls through displays of the differential operating and restraint quantities, the terminals in each enabled zone, and the primary current and voltage values. Each display remains for 5 seconds

Figure 19 and Figure 20 show close-up views of the front panel of the SEL-487B. The front panel includes a 128 x 128 pixel, 3" x 3" LCD screen; 24 LED target indicators; and 12 direct-action control pushbuttons with indicating LEDs for local control functions. You can use easily changed slide-in labels to custom configure target and pushbutton identification. Use the capabilities of the SEL-487B front panel to integrate a wide range of control and system annunciation functions.




Figure 19 Front Panel With 24 Tricolor Target LEDs and 12 Pushbuttons




Figure 20 Front-Panel Display and Pushbuttons

before the display continues scrolling. Any message the relay generates because of an alarm condition takes precedence over the rotating display.

Status and Trip Target LEDs

The SEL-487B includes programmable target LEDs, as well as programmable direct-action control pushbuttons/LEDs on the front panel. *Figure 19* shows these targets.

The SEL-487B features a versatile front panel that you can customize to fit your needs. Use SELOGIC control equations and slide-in configurable front-panel labels to change the function and identification of target LEDs and operator control pushbuttons and LEDs. The blank slide-in label set is included with the SEL-487B. You can use templates supplied with the relay or hand label supplied blank labels and print label sets from a printer.

Communications Features

See *Specifications on page 18* for specific supported protocols.




Figure 21 System Functional Overview

The relay offers the following communications features:

- Four independent EIA-232 serial ports.
- Access to event history, relay status, and meter information from the communications ports.
- Password-controlled settings management and automation features.
- SCADA interface capability, including FTP, IEC 61850, DNP3 LAN/WAN (via Ethernet), and DNP3 (via serial port). The relay does not require special communications software. You only need ASCII terminals, printing terminals, or a computer supplied with terminal emulation and a serial communications port.

Ethernet Card

The Ethernet card has five small form-factor pluggable (SFP) ports.^a **PORT 5A** and **PORT 5B** are reserved for the process bus network. **PORT 5C** and **PORT 5D** are reserved for the station bus network. The process and station bus networks support PRP and fast failover redundancy modes. **PORT 5E** operates on an isolated network with a unique IP address making it ideal for engineering and

data access. All ports support 100 Mbps speeds. **PORT 5A** and **PORT 5B** also support 1 Gbps speeds to satisfy potentially large traffic requirements on the process bus. The process bus, station bus, and engineering access networks use separate MAC addresses and are logically delineated, including in the Configured IED Description (CID) file.^b

Use popular Telnet applications for easy terminal communications with SEL relays and other devices. Transfer data at high speeds for fast file uploads. The Ethernet card communicates using FTP applications for easy and fast file transfers.

Communicate with SCADA by DNP3 and other substation IEDs by using IEC 61850 Manufacturing Message Specification (MMS) and GOOSE messaging.

Choose Ethernet connection media options for primary and standby connections:

- 10/100BASE-T twisted pair network^c
- 100BASE FX fiber-optic network
- 1000BASE-X fiber-optic network^d

^b This paragraph describes the five-port Ethernet card ordering option. It does not apply to the four-port Ethernet card ordering option.

^c Four-port Ethernet card ordering option only.

^d Gigabit speeds are only available on **PORT 5A** and **PORT 5B** of the five-port Ethernet card ordering option.

^a SFP transceivers are not included with the card and must be ordered separately. See selinc.com/products/sfp for a list of compatible SFP transceivers.

Telnet and FTP

Use Telnet to access relay settings, metering, and event reports remotely by using the ASCII interface. Use FTP to transfer settings files to and from the relay via the high-speed Ethernet port.

DNP3 LAN/WAN

DNP3 LAN/WAN provides the relay with DNP3 Level 2 Outstation functionality over Ethernet. Configure DNP3 data maps for use with specific DNP3 masters.

PTP

The Ethernet card provides the ability for the relay to accept IEEE 1588 PTPv2 for data time synchronization. PTP support includes the Default, Power System, and Power Utility Automation Profiles. When connected directly to a grandmaster clock providing PTP at 1-second synchronization intervals, the relay can be synchronized to an accuracy of ± 100 ns in the PTP time scale.




Figure 22 Example PTP Network

SNTP Time Synchronization

Use SNTP to cost-effectively synchronize relays to as little as ± 1 ms with no time source delay. Use SNTP as a primary time source, or as a backup to a higher accuracy time input to the relay.

PRP

Use PRP to provide seamless recovery from any single Ethernet network failure, in accordance with IEC 62439-3. The Ethernet network and all traffic are fully duplicated with both copies operating in parallel.

HTTP Web Server

The relay can serve read-only webpages displaying certain settings, metering, and status reports. The web server also allows quick and secure firmware upgrades over Ethernet. As many as four users can access the embedded HTTP server simultaneously.

IEC 61850 Ethernet Communications

IEC 61850 Ethernet-based communication protocols provide interoperability between intelligent devices within the substation. Standardized logical nodes allow interconnection of intelligent devices from different manufacturers for monitoring and control of the substation.

Eliminate system RTUs by streaming monitor and control information from the intelligent devices directly to remote SCADA client devices.

You can order the relay with IEC 61850 protocol for relay monitor and control functions, including:

- As many as 128 incoming GOOSE messages. You can use the incoming GOOSE messages to control as many as 256 control bits in the relay with < 3 ms latency from device to device depending on network design. These messages provide binary control inputs to the relay for high-speed control functions and monitoring.
- As many as eight outgoing GOOSE messages. Configure outgoing GOOSE messages for Boolean or analog data such as high-speed control and monitoring of external breakers, switches, and other devices. Boolean data are provided with < 3 ms latency from device to device depending on network design.
- IEC 61850 Data Server. The relay equipped with embedded IEC 61850 Ethernet protocol provides data according to predefined logical node objects. Each relay supports as many as seven unbuffered MMS report client associations. Relevant Relay Word bits are available within the logical node data, so status of relay elements, inputs, outputs, or SELOGIC control equations can be monitored.
- As many as 256 virtual bits. Configure the virtual bits within GOOSE messaging to represent a variety of Boolean values available within the relay. These bits that the relay receives are available for use in SELOGIC control equations.
- As many as 64 remote analog outputs. Assign the remote analog outputs to virtually any analog quantity available in the relay. You can also use SELOGIC math variables to develop custom analog quantities for assignment as remote analog outputs. Remote

analog outputs that use GOOSE messages provide peer-to-peer transmission of analog data. Each relay can receive as many as 256 remote analog inputs and use those inputs as analog quantities within SELOGIC control equations.

- IEC 61850 standard operating modes. The relay supports Test, Blocked, On, and Off. The relay also supports Simulation mode for added flexibility.

MMS File Services

This service of IEC 61850 MMS provides support for file transfers completely within an MMS session. All relay files that can be transferred via FTP can also be transferred via MMS file services.

MMS Authentication

When enabled via a setting in the Configured IED Description (CID) file, the relay requires authentication from any client requesting to initiate an MMS session.

Architect Software

Use ACCELERATOR Architect SEL-5032 Software to manage the IEC 61850 configuration for devices on the network. This Windows-based software provides easy-

to-use displays for identifying and binding IEC 61850 network data among logical nodes that use IEC 61850-compliant CID files. Architect uses CID files to describe the data available in each relay.

Serial Communications MIRRORED BITS Communications

The SEL patented MIRRORED BITS technology provides bidirectional relay-to-relay digital communication.

Figure 23 shows two relays with SEL-2815 Fiber-Optic Transceivers that use MIRRORED BITS communications. MIRRORED BITS communications can operate simultaneously on any two serial ports. This bidirectional digital communication creates additional outputs (transmitted MIRRORED BITS) and additional inputs (received MIRRORED BITS) for each serial port operating in the MIRRORED BITS communications mode.

Communicated information can include digital, analog, and virtual terminal data. Virtual terminal allows operator access to remote relays through the local relay. You can use this MIRRORED BITS protocol to transfer information between stations to enhance coordination and achieve faster tripping.




Figure 23 Integral Communication Provides Secure Protection, Monitoring, and Control as Well as Terminal Access to Both Relays Through One Connection

Open Communications Protocols

The relay does not require special communications software. ASCII terminals, printing terminals, or a computer supplied with terminal emulation and a serial communications port are all that is required. Table 3 lists a brief description of the terminal protocols.

Table 3 Open Communications Protocol

Type	Description
ASCII	Plain-language commands for human and simple machine communications. Use for metering, setting, self-test status, event reporting, and other functions.
Compressed ASCII	Comma-delimited ASCII data reports. Allows external devices to obtain bay data in an appropriate format for direct import into spreadsheets and database programs. Data are checksum protected.
Extended Fast Meter, Fast Operate, and Fast SER	Binary protocol for machine-to-machine communications. Quickly updates communications processors, RTUs, and other substation devices with metering information, bay element, I/O status, time-tags, open and close commands, and summary event reports. Data are checksum protected. Binary and ASCII protocols operate simultaneously over the same communications lines so that control operator metering information is not lost while a technician is transferring an event report.
Ymodem	Support for reading event, settings, and oscillography files.
DNP3 Level 2 Outstation	DNP with point remapping. Includes access to metering data, protection elements, contact I/O, targets, SER, relay summary event reports, and settings groups.
MIRRORED BITS	SEL protocol for exchanging digital and analog information among SEL relays and for use as low-speed terminal connection.
IEC 61850	Ethernet-based international standard for interoperability between intelligent devices in a substation.
PRP	PRP provides redundant Ethernet network capabilities for seamless operation in the event of loss to one network.
SNTP	Ethernet-based SNTP for time synchronization among relays.
FTP and Telnet	Use Telnet to establish a terminal-to-relay connection over Ethernet. Use FTP to move files in and out of the relay over Ethernet.

Automation

Flexible Control Logic and Integration Features

Use the control logic to perform the following:

- Replace traditional panel control switches
- Eliminate remote terminal unit (RTU)-to-bay wiring
- Replace traditional latching relays
- Replace traditional indicating panel lights

Eliminate traditional panel control switches with 64 local control points. Set, clear, or pulse local control points with the front-panel pushbuttons and display. Program the local control points to implement your control scheme via SELOGIC control equations. Use the local control points for such functions as trip testing, enabling/disabling reclosing, and tripping/closing circuit breakers.

Eliminate RTU-to-bay wiring with 96 remote control points per relay. Set, clear, or pulse remote control points via serial port commands. Incorporate the remote control points into your control scheme via SELOGIC control equations. Use remote control points for SCADA-type control operations (e.g., trip, close, settings group selection).

Replace traditional latching relays for such functions as remote control enable with 64 latching control points. Program latch set and latch reset conditions with SELOGIC control equations. Set or reset the latch control points via

control inputs, remote control points, local control points, or any programmable logic condition. The relay retains the states of the latch control points after turning on following a power interruption.

Replace traditional indicating panel lights and switches with as many as 24 latching target LEDs and as many as 12 programmable pushbuttons with LEDs. Define custom messages (i.e., BREAKER OPEN) to report power system or relay conditions on the large format LCD. Control displayed messages with SELOGIC control equations by driving the LCD via any logic point in the relay.

SELOGIC Control Equations With Expanded Capabilities and Aliases

Expanded SELOGIC control equations put relay logic in the hands of the engineer. Assign inputs to suit your application, logically combine selected bay elements for various control functions, and assign outputs to your logic functions.

Programming SELOGIC control equations consists of combining relay elements, inputs, and outputs with SELOGIC control equation operators (*Table 4*). Any element in the Relay Word can be used in these equations. For complex or unique applications, these expanded SELOGIC functions allow superior flexibility.

Table 4 SELogic Control Equation Operators

Operator Type	Operators	Comments
Boolean	AND, OR, NOT	Allows combination of measuring units.
Edge Detection	F_TRIG, R_TRIG	Operates at the change of state of an internal function.
Comparison	>, >=, =, <=, <, <>	
Arithmetic	+, -, *, /	Uses traditional math functions for analog quantities in an easily programmable equation.
Numerical	ABS, SIN, COS, LN, EXP, SQRT, LOG	
Precedence Control	()	Allows multiple and nested sets of parentheses.
Comment	#, (* *)	Provides for easy documentation of control and protection logic.

Use the relay alias capability to assign more meaningful names to analog and Boolean quantities. This improves the readability of customized programming. Use as many as 200 aliases to rename any digital or analog quantity. The following is an example of possible applications of SELOGIC control equations that use aliases.

```

=>>SET T <Enter>
1: PMV01, THETA
(assign the alias "THETA" to math variable PMV01)

2: PMV02, TAN
(assign the alias "TAN" to math variable PMV02)

=>>SET L <Enter>
1: # CALCULATE THE TANGENT OF THETA
2: TAN:=SIN(THETA)/COS(THETA)
(use the aliases in an equation)

```

Add programmable control functions to your relay and automation systems. New functions and capabilities enable using analog values in conditional logic statements. The following are examples of possible applications of SELOGIC control equations with expanded capabilities.

- ▶ Emulate a motor-driven reclose timer, including stall, reset, and drive-to-lockout conditions.
- ▶ Scale analog values for SCADA retrieval.
- ▶ Initiate remedial action sequence based on load flow before fault conditions.
- ▶ Interlock breakers and disconnect switches.
- ▶ Restrict breaker tripping in excessive duty situations without additional relays.
- ▶ Hold momentary change-of-state conditions for SCADA polling.

Metering and Monitoring

Access a range of useful information in the relay with the metering function. Metered quantities include fundamental primary and secondary current and voltage magnitudes and angles for each terminal. Secondary quantities also include the PT ratio and CT ratio of each terminal. Zone information displays primary current and voltage magnitudes and angles for each terminal and also includes the polarity of each CT and the bus-zones in each of the protective zones at the station. The same information is available in secondary quantities and includes both the CT ratio and polarity. Differential metering shows the operating and restraint currents, as well as the reference current, for each zone.

Table 5 Flexible Metering Capabilities and Large Screen Display Eliminate Need for Panel Instruments (Sheet 1 of 2)

Capabilities	Description
V01, V02, V03	Fundamental phase voltage magnitude and angle in primary and secondary values
I01, I02, . . . , I21	Fundamental phase current magnitude and angle in primary and secondary values

Table 5 Flexible Metering Capabilities and Large Screen Display Eliminate Need for Panel Instruments (Sheet 2 of 2)

Capabilities	Description
IOP, IRT, IREF	Operating and restraint currents for each zone, check zone, and the reference current
Bus Zones in Protection Zone <i>n</i>	Names of the bus-zones in Protection Zone <i>n</i> (where <i>n</i> = 1 to 6)
PTR, CTR	PT ratio and CT ratio for each terminal
POL	Polarity of each CT

Event Reporting and SER

Event reports and SER features simplify post-fault analysis and help improve your understanding of both simple and complex protective scheme operations. These features also aid in testing and troubleshooting relay settings and protective schemes.

Oscillography and Event Reporting

In response to a user-selected internal or external trigger, the voltage, current, and element status information contained in each event report confirms relay, scheme, and system performance for every fault. The relay provides sampling rates as fast as 8 kHz for analog quantities in a COMTRADE file format, as well as eight-sample-per-cycle and four-sample-per-cycle event reports. The relay stores as much as 3 seconds of 8 kHz event data. The relay supports inclusion of user-configurable analogs in the events. Reports are stored in nonvolatile memory. Relay settings operational in the relay at the time of the event are appended to each event report.

Each relay provides event reports for analysis with software such as SEL-5601-2 SYNCHROWAVE[®] Event Software. With SYNCHROWAVE Event, you can display events from several relays to make the fault analysis easier and more meaningful. Because the different relays time-stamp the events with values from their individual clocks, be sure to time synchronize the relay with an IRIG-B clock input or PTP source to use this feature.

Event Summary

Each time the relay generates a standard event report, it also generates a corresponding event summary. This is a concise description of an event that includes the following information:

- Relay/terminal identification
- Event date and time
- Event type
- Event number
- Time source
- Active settings group
- Targets asserted during the fault
- Current magnitudes and angles for each terminal
- Voltage magnitudes and angles
- Terminals tripped for this fault
- Breaker Status (open/close)
- Bus-zones in Protection Zone n ($n = 1-6$)

With an appropriate setting, the relay sends an event summary in ASCII text automatically to one or more serial ports each time an event report is triggered.

SV Reporting

The SV Subscriber includes a comprehensive report of the SV communication stream. The ASCII command **COM SV** displays statistics information from the sample values stream to aid in troubleshooting.

SER

Use this feature to gain a broad perspective of relay element operation. Items that trigger an SER entry are selectable and can include as many as 250 monitoring points, such as I/O change-of-state and element pickup/dropout. The relay SER stores the latest 1000 events.

Analog Signal Profiling

The relay provides analog signal profiling for as many as 20 analog quantities. Select any analog quantity measured or calculated by the relay for analog signal profiling. You can select signal sampling rates of 1, 5, 15, 30, and 60 minutes through settings. The analog signal profile report provides a comma-separated variable (CSV) list that you can load into any spreadsheet or database for analysis and graphical display.

SELOGIC enable/disable functions can start and stop signal profiling based on Boolean or analog comparison conditions.

Substation Battery Monitor for DC Quality Assurance

The relay measures and reports the substation battery voltage for one battery system. The battery monitor supports programmable threshold comparators and associated logic provides alarm and control for one battery and charger. The relay also provides dual ground detection. Monitor dc system status alarms with an SEL communications processor and trigger messages, telephone calls, or other actions.

The measured dc voltage is reported in the METER display via serial port communications and in the event report. Use the event report data to see an oscillographic display of the battery voltage. Monitor the substation battery voltage drops during trip, close, and other control operations.

Diagrams and Dimensions






Figure 24 Rack-Mount Front Panel



Five-port Ethernet card ordering option depicted.

Figure 25 SEL-487B-2 SV Subscriber Rear Panel



Five-port Ethernet card ordering option depicted.

Figure 26 SEL-487B-2 TiDL Rear Panel




Figure 27 Dimensions for Rack- and Panel-Mount Models

Models and Options

Consider the following options when ordering and configuring the SEL-487B.

- DSS connector type
 - IEC 61850-9-2LE-compliant SV subscriber relay
 - SEL TiDL relay with T-Protocol

- Chassis size
 - 4U (U is one rack unit—1.75 in or 44.45 mm)

Table 6 Interface Board Information

Board Name	Inputs	Description	Outputs	Description
INT2	8	Optoisolated, independent, level-sensitive	13	Standard Form A
			2	Standard Form C
INT4	18	Two sets of 9 common optoisolated, level-sensitive	6	High-speed, high-current interrupting, Form A
	6	Optoisolated, independent, level-sensitive	2	Standard Form A

- Chassis orientation and type
 - Horizontal rack mount
 - Horizontal panel mount
 - Vertical rack mount
 - Vertical panel mount
- Power supply
 - 24–48 Vdc
 - 48–125 Vdc or 110–120 Vac
 - 125–250 Vdc or 110–240 Vac

- Ethernet card options
 - Four-port Ethernet card with port combinations of:
 - Four copper (10BASE-T/100BASE-TX)
 - Four fiber (100BASE-FX)
 - Two copper (10BASE-T/100BASE-TX) and two fiber (100BASE-FX)
 - Five-port Ethernet card with small form-factor pluggable (SFP) ports (100BASE-FX and 1000BASE-X)^e

^e All ports support 100 Mbps speeds. **PORT 5A** and **PORT 5B** also support 1 Gbps speeds.

- Communications protocols
 - Complete group of protocols (SEL ASCII, SEL Compressed ASCII, SEL Settings File Transfer, SEL Fast Meter, SEL Fast Operate, SEL Fast SER, MIRRORING BITS Communications), and DNP3
 - Above protocols plus IEC 61850 Edition 2

Contact the SEL factory or your local Technical Service Center for ordering information (see *Technical Support on page 24*). You can also view the latest ordering information on the SEL website at selinc.com.

Specifications

Note: Because the SEL-487B-2 uses DSS, the relay operating times are delayed. For SV applications, operating times are delayed by the configured channel delay, CH_DLY. See <CrossRefBook>SV Network Delays on page 17.25 in the SEL-400 Series Relays Instruction Manual for more details. For TiDL applications, the operating times are delayed by a fixed 1 ms. Use caution when setting relay coordination to account for this added delay.

Note: The metering and protection element accuracies specified for the SEL-487B SV Subscriber Relay are valid only when using SEL merging units. For SV applications, third-party SV publisher devices are supported, but hardware accuracies and analog filtering need to be considered to determine the effect on SEL-487B-2 SV Subscriber performance.

Compliance

Designed and manufactured under an ISO 9001 certified quality management system

FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class A digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference when the equipment is operated in a commercial environment. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instruction manual, may cause harmful interference in which case the user will be required to correct the interference at his own expense.

UL Listed to U.S. and Canadian safety standards (File E212775; NRGU, NRGU7)

CE Mark

RCM Mark

General

Frequency and Rotation

System Frequency: 50/60 Hz
Phase Rotation: ABC

Power Supply

24–48 Vdc

Rated Voltage: 24–48 Vdc
Operational Voltage Range: 18–60 Vdc
Vdc Input Ripple: 15% per IEC 60255-26:2013
Interruption: 20 ms at 24 Vdc, 100 ms at 48 Vdc per IEC 60255-26:2013

Burden

SV Relay: <35 W
TiDL Relay: <40 W

48–125 Vdc or 110–120 Vac

Rated Voltage: 48–125 Vdc, 110–120 Vac
Operational Voltage Range: 38–140 Vdc
85–140 Vac
Rated Frequency: 50/60 Hz
Operational Frequency Range: 30–120 Hz
Vdc Input Ripple: 15% per IEC 60255-26:2013
Interruption: 14 ms @ 48 Vdc, 160 ms @ 125 Vdc per IEC 60255-26:2013

Burden

SV Relay: <35 W, <90 VA
TiDL Relay: <40 W, <90 VA

125–250 Vdc or 110–240 Vac

Rated Voltage: 125–250 Vdc, 110–240 Vac
Operational Voltage Range: 85–300 Vdc
85–264 Vac
Rated Frequency: 50/60 Hz
Operational Frequency Range: 30–120 Hz
Vdc Input Ripple: 15% per IEC 60255-26:2013
Interruption: 46 ms @ 125 Vdc, 250 ms @ 250 Vdc per IEC 60255-26:2013

Burden

SV Relay: <35 W, <90 VA
TiDL Relay: <40 W, <90 VA

Control Outputs

Note: IEEE C37.90-2005 and IEC 60255-27:2013

Update Rate: 1/8 cycle
Make (Short Duration Contact Current): 30 Adc
1,000 operations at 250 Vdc
2,000 operations at 125 Vdc
Limiting Making Capacity: 1000 W at 250 Vdc (L/R = 40 ms)
Mechanical Endurance: 10,000 operations

Standard

Rated Voltage: 24–250 Vdc
110–240 Vrms
Operational Voltage Range: 0–300 Vdc
0–264 Vrms

Operating Time:	Pickup ≤ 6 ms (resistive load) Dropout ≤ 6 ms (resistive load)
Short-Time Thermal Withstand:	50 A for 1 s
Continuous Contact Current:	6 A at 70°C 4 A at 85°C
Contact Protection:	MOV protection across open contacts 264 Vrms continuous voltage 300 Vdc continuous voltage
Limiting Breaking Capacity/Electrical Endurance:	10,000 operations 10 operations in 4 seconds, followed by 2 minutes idle

Rated Voltage	Resistive Break	Inductive Break L/R = 40 ms (DC) PF = 0.4 (AC)
24 Vdc	0.75 Adc	0.75 Adc
48 Vdc	0.63 Adc	0.63 Adc
125 Vdc	0.30 Adc	0.30 Adc
250 Vdc	0.20 Adc	0.20 Adc
110 Vrms	0.30 Arms	0.30 Arms
240 Vrms	0.20 Arms	0.20 Arms

Fast Hybrid (High-Speed High-Current Interrupting)

Rated Voltage:	48–250 Vdc
Operational Voltage Range:	0–300 Vdc
Operating Time:	Pickup ≤ 10 μ s (resistive load) Dropout ≤ 8 ms (resistive load)
Short-Time Thermal Withstand:	50 Adc for 1 s
Continuous Contact Current:	6 Adc at 70°C 4 Adc at 85°C
Contact Protection:	MOV protection across open contacts 300 Vdc continuous voltage
Limiting Breaking Capacity/Electrical Endurance:	10,000 operations 4 operations in 1 second, followed by 2 minutes idle

Rated Voltage	Resistive Break	Inductive Break
24 Vdc	10 Adc	10 Adc (L/R = 40 ms)
48 Vdc	10 Adc	10 Adc (L/R = 40 ms)
125 Vdc	10 Adc	10 Adc (L/R = 40 ms)
250 Vdc	10 Adc	10 Adc (L/R = 20 ms)

Note: Do not use hybrid control outputs to switch ac control signals.

Control Inputs

Optoisolated (For Use With AC or DC Signals)

INT2 Interface Board:	8 inputs with no shared terminals
INT4 Interface Board:	6 inputs with no shared terminals 18 inputs with shared terminals (2 groups of 9 inputs with each group sharing one terminal)
Voltage Options:	24, 48, 110, 125, 220, 250 V
Current Draw:	< 5 mA at nominal voltage < 8 mA for 110 V option
Sampling Rate:	2 kHz
DC Thresholds (Dropout thresholds indicate level-sensitive option)	
24 Vdc:	Pickup 19.2–30.0 Vdc; Dropout < 14.4 Vdc

48 Vdc:	Pickup 38.4–60.0 Vdc; Dropout < 28.8 Vdc
110 Vdc:	Pickup 88.0–132.0 Vdc; Dropout < 66.0 Vdc
125 Vdc:	Pickup 105–150 Vdc; Dropout < 75 Vdc
220 Vdc:	Pickup 176–264 Vdc; Dropout < 132 Vdc
250 Vdc:	Pickup 200–300 Vdc; Dropout < 150 Vdc

AC Thresholds (Ratings met only when recommended control input settings are used)

24 Vac:	Pickup 16.4–30.0 Vac rms; Dropout < 10.1 Vac rms
48 Vac:	Pickup 32.8–60.0 Vac rms; Dropout < 20.3 Vac rms
110 Vac:	Pickup 75.1–132.0 Vac rms; Dropout < 46.6 Vac rms
125 Vac:	Pickup 89.6–150.0 Vac rms; Dropout < 53.0 Vac rms
220 Vac:	Pickup 150.3–264.0 Vac rms; Dropout < 93.2 Vac rms
250 Vac:	Pickup 170.6–264.0 Vac rms; Dropout < 106 Vac rms
Current Drawn:	< 5 mA at nominal voltage < 8 mA for 110 V option
Sampling Rate:	2 kHz

Communications Ports

EIA-232:	1 Front and 3 Rear
Serial Data Speed:	300–57600 bps

Ethernet Card Slot for Four-Port Ethernet Card

Ordering Option:	10/100BASE-T
Connector Type:	RJ45
Ordering Option:	100BASE-FX fiber-optic Ethernet
Mode:	Multi
Wavelength (nm):	1300
Source:	LED
Connector Type:	LC
Min. TX Pwr. (dBm):	-19
Max. TX Pwr. (dBm):	-14
RX Sens. (dBm):	-32
Sys. Gain (dB):	13

Ethernet Card Slot for the Five-Port Ethernet Card

Ordering Option:	100BASE-FX fiber-optic Ethernet SFP transceiver
Part Number:	8103-01 or 8109-01
Mode:	Multi
Wavelength (nm):	1310
Source:	LED
Connector Type:	LC
Min. TX Pwr. (dBm):	-24
Max. TX Pwr. (dBm):	-14
Min. RX Sens. (dBm):	-31
Max. RX Sens. (dBm):	-12
Approximate Range:	2 km
Transceiver Internal Temperature Accuracy:	$\pm 3.0^\circ\text{C}$

Transmitter Average
Optical Power Accuracy: ± 3.0 dB

Received Average Optical
Input Power Accuracy: ± 3.0 dB

Ordering Option: 1000BASE-LX fiber-optic Ethernet SFP
transceiver

Part Number: 8130-01, 8130-02, 8130-03, or 8130-04

Mode: Single

Wavelength (nm): 1310

Source: LED

Connector Type: LC

	Part Number			
	8130-01	8130-02	8130-03	8130-04
Min. TX Pwr. (dBm)	-9.5	-6	-5	-2
Max. TX Pwr. (dBm)	-3	-1	0	3
Min. RX Sens. (dBm)	-21	-22	-24	-24
Max. RX Sens. (dBm)	-3	-3	-3	-3
Approximate Range (km)	10	20	30	40

Transceiver Internal
Temperature Accuracy: $\pm 3.0^{\circ}\text{C}$

Transmitter Average
Optical Power Accuracy: ± 3.0 dB

Received Average Optical
Input Power Accuracy: ± 3.0 dB

Ordering Option: 1000BASE-XD fiber-optic Ethernet SFP
transceiver

Part Number: 8130-05

Mode: Single

Wavelength (nm): 1550

Source: LED

Connector Type: LC

Min. TX Pwr. (dBm): -5

Max. TX Pwr. (dBm): 0

Min. RX Sens. (dBm): -24

Max. RX Sens. (dBm): -3

Approximate Range: 50 km

Transceiver Internal
Temperature Accuracy: $\pm 3.0^{\circ}\text{C}$

Transmitter Average
Optical Power Accuracy: ± 3.0 dB

Received Average Optical
Input Power Accuracy: ± 3.0 dB

Ordering Option: 1000BASE-ZX fiber-optic Ethernet SFP
transceiver

Part Number: 8130-06, 8130-08, or 8130-10

Mode: Single

Wavelength (nm): 1550

Source: LED

Connector Type: LC

	Part Number		
	8130-06	8130-08	8130-10
Min. TX Pwr. (dBm)	0	1	5
Max. TX Pwr. (dBm)	5	5	8
Min. RX Sens. (dBm)	-24	-36	-36
Max. RX Sens. (dBm)	-3	-10	-10
Approximate Range (km)	80	160	200

Transceiver Internal
Temperature Accuracy: $\pm 3.0^{\circ}\text{C}$

Transmitter Average
Optical Power Accuracy: ± 3.0 dB

Received Average Optical
Input Power Accuracy: ± 3.0 dB

Ordering Option: 1000BASE-SX fiber-optic Ethernet SFP
transceiver

Part Number: 8131-01

Mode: Multi

Wavelength (nm): 850

Source: LED

Connector Type: LC

Min. TX Pwr. (dBm): -9

Max. TX Pwr. (dBm): -2.5

Min. RX Sens. (dBm): -18

Max. RX Sens. (dBm): 0

Approximate Range: 300 m for 62.5/125 μm ; 550 m for 50/125 μm

Transceiver Internal
Temperature Accuracy: $\pm 3.0^{\circ}\text{C}$

Transmitter Average
Optical Power Accuracy: ± 3.0 dB

Received Average Optical
Input Power Accuracy: ± 3.0 dB

Optional TiDL Communication Ports

Number of Ports: 8

Protocol: T-Protocol

Supported SFP
Transceivers: 8103-01 or 8109-01

Note: For SFP Transceiver specification, see *Ethernet Card Slot for the Five-Port Ethernet Card* on page 19.

Time Inputs

IRIG Time Input-Serial PORT 1

Input: Demodulated IRIG-B

Rated I/O Voltage: 5 Vdc

Operational Voltage Range: 0-8 Vdc

Logic High Threshold: ≥ 2.8 Vdc

Logic Low Threshold: ≤ 0.8 Vdc

Input Impedance: 2.5 k Ω

IRIG-B Input-BNC Connector

Input: Demodulated IRIG-B

Rated I/O Voltage: 5 Vdc

Operational Voltage Range: 0-8 Vdc

Logic High Threshold: ≥ 2.2 Vdc

Logic Low Threshold: ≤ 0.8 Vdc

Input Impedance: 50 Ω or >1 k Ω

Dielectric Test Voltage: 0.5 kVac

PTP

Input:	IEEE 1588 PTPv2
Profiles:	Default, IEEE C37.238-2011 (Power Profile), IEC/IEEE 61850-9-3-2016 (Power Utility Automation Profile)
Synchronization Accuracy:	±100 ns @ 1-second synchronization intervals when communicating directly with master clock

Operating Temperature

−40° to +85°C (−40° to +185°F)

Note: LCD contrast impaired for temperatures below −20° and above +70°C.

Humidity

5% to 95% without condensation

Weight (Maximum)

TiDL Relay:	6.74 kg (14.87 lb)
SV Relay:	6.57 kg (14.47 lb)

Terminal Connections

Rear Screw-Terminal Tightening Torque, #8 Ring Lug

Minimum:	1.0 Nm (9 in-lb)
Maximum:	2.0 Nm (18 in-lb)

User terminals and stranded copper wire should have a minimum temperature rating of 105°C. Ring terminals are recommended.

Wire Sizes and Insulation

Wire sizes for grounding (earthing) and contact connections are dictated by the terminal blocks and expected load currents. You can use the following table as a guide in selecting wire sizes:

Connection Type	Min. Wire Size	Max. Wire Size
Grounding (Earthing) Connection	14 AWG (2.5 mm ²)	N/A
Contact I/O	18 AWG (0.8 mm ²)	10 AWG (5.3 mm ²)
Other Connection	18 AWG (0.8 mm ²)	10 AWG (5.3 mm ²)

Type Tests

Installation Requirements

Overvoltage Category:	2
Pollution Degree:	2

Safety

Product Standards:	IEC 60255-27:2013 IEEE C37.90-2005 21 CFR 1040.10
Dielectric Strength:	IEC 60255-27:2013, Section 10.6.4.3 2.5 kVac, 50/60 Hz for 1 min: Analog Inputs, Contact Outputs, Digital Inputs 3.6 kVdc for 1 min: Power Supply, Battery Monitors 2.5 kVdc for 1 min: IRIG-B 1.1 kVdc for 1 min: Ethernet
Impulse Withstand:	IEC 60255-27:2013, Section 10.6.4.2 IEEE C37.90-2005 Common Mode: ±1.0 kV: Ethernet ±2.5 kV: IRIG-B ±5.0 kV: All other ports Differential Mode: 0 kV: Analog Inputs, Ethernet, IRIG-B, Digital Inputs ±5.0 kV: Standard Contact Outputs, Power Supply Battery Monitors +5.0 kV: Hybrid Contact Outputs
Insulation Resistance:	IEC 60255-27:2013, Section 10.6.4.4 >100 MΩ @ 500 Vdc

Protective Bonding:	IEC 60255-27:2013, Section 10.6.4.5.2 <0.1 Ω @ 12 Vdc, 30 A for 1 min
Ingress Protection:	IEC 60529:2001 + CRGD:2003 IEC 60255-27:2013 IP30 for front and rear panel IP10 for rear terminals with installation of ring lug IP40 for front panel with installation of serial port cover

Max Temperature of Parts and Materials:	IEC 60255-27:2013, Section 7.3
Flammability of Insulating Materials:	IEC 60255-27:2013, Section 7.6 Compliant

Electromagnetic (EMC) Immunity

Product Standards:	IEC 60255-26:2013 IEC 60255-27:2013 IEEE C37.90-2005
Surge Withstand Capability (SWC):	IEC 61000-4-18:2006 + A:2010 IEEE C37.90.1-2012 Slow Damped Oscillatory, Common and Differential Mode: ±1.0 kV ±2.5 kV Fast Transient, Common and Differential Mode: ±4.0 kV
Electrostatic Discharge (ESD):	IEC 61000-4-2:2008 IEEE C37.90.3-2001 Contact: ±8 kV Air Discharge: ±15 kV
Radiated RF Immunity:	IEEE C37.90.2-2004 IEC 61000-4-3:2006 + A1:2007 + A2:2010 20 V/m (>35 V/m, 80% AM, 1 kHz) Sweep: 80 MHz to 1 GHz Spot: 80, 160, 450, 900 MHz 10 V/m (>15 V/m, 80% AM, 1 kHz) Sweep: 80 MHz to 1 GHz Sweep: 1.4 GHz to 2.7 GHz Spot: 80, 160, 380, 450, 900, 1850, 2150 MHz
Electrical Fast Transient Burst (EFTB):	IEC 61000-4-4:2012 Zone A: ±2 kV: Communication ports ±4 kV: All other ports
Surge Immunity:	IEC 61000-4-5:2005 Zone A: ±2 kV _{L-L} ±4 kV _{L-E} ±4 kV: Communication Ports Note: Cables connected to IRIG-B ports shall be less than 10 m in length for Zone A compliance. Zone B: ±2 kV: Communication Ports
Conducted Immunity:	IEC 61000-4-6:2013 20 V/m; (>35 V/m, 80% AM, 1 kHz) Sweep: 150 kHz–80 MHz Spot: 27, 68 MHz
Power Frequency Immunity (DC Inputs):	IEC 61000-4-16:2015 Zone A: Differential: 150 V _{RMS} Common Mode: 300 V _{RMS}
Power Frequency Magnetic Field:	IEC 61000-4-8:2009 Level 5: 100 A/m; ≥60 Seconds; 50/60 Hz 1000 A/m 1 to 3 Seconds; 50/60 Hz Note: 50G1P ≥0.05 (ESS = N, 1, 2) 50G1P ≥0.1 (ESS = 3, 4)

Power Supply Immunity:	IEC 61000-4-11:2004 IEC 61000-4-17:1999/A1:2001/A2:2008 IEC 61000-4-29:2000 AC Dips & Interruptions Ripple on DC Power Input DC Dips & Interruptions Gradual Shutdown/Startup (DC only) Discharge of Capacitors Slow Ramp Down/Up Reverse Polarity (DC only)
------------------------	---

Damped Oscillatory Magnetic Field:	IEC 61000-4-10:2016 Level 5: 100 A/m
---------------------------------------	--

EMC Compatibility

Product Standards:	IEC 60255-26:2013
Emissions:	IEC 60255-26:2013, Section 7.1 Class A 47 CFR Part 15B Class A Canada ICES-001 (A) / NMB-001 (A)

Environmental

Product Standards:	IEC 60255-27:2013
Cold, Operational:	IEC 60068-2-1:2007 Test Ad: 16 hours at -40°C
Cold, Storage:	IEC 60068-2-1:2007 Test Ad: 16 hours at -40°C
Dry Heat, Operational:	IEC 60068-2-2:2007 Test Bd: 16 hours at $+85^{\circ}\text{C}$
Dry Heat, Storage:	IEC 60068-2-2:2007 Test Bd: 16 hours at $+85^{\circ}\text{C}$
Damp Heat, Cyclic:	IEC 60068-2-30:2005 Test Db: $+25^{\circ}\text{C}$ to $+55^{\circ}\text{C}$, 6 cycles (12 + 12-hour cycle), 95% RH
Damp Heat, Steady State:	IEC 60068-2-78:2013 Severity: 93% RH, $+40^{\circ}\text{C}$, 10 days
Vibration Resistance:	EC 60255-21-1:1988 Class 2 Endurance, Class 2 Response
Shock Resistance:	IEC 60255-21-2:1988 Class 1 Shock Withstand, Class 1 Bump Withstand, Class 2 Shock Response
Seismic:	IEC 60255-21-3:1993 Class 2 Quake Response

Reporting Functions

High-Resolution Data

Rate:	8000 samples/second 4000 samples/second 2000 samples/second 1000 samples/second
-------	--

Output Format:	Binary COMTRADE
----------------	-----------------

Note: Per IEEE C37.111-1999 and IEEE C37.111-2013, *Common Format for Transient Data Exchange (COMTRADE) for Power Systems*.

Event Reports

Length:	0.25–24 seconds (depending on LER setting)
Volatile Memory:	3 seconds of back-to-back event reports sampled at 8 kHz
Nonvolatile Memory:	At least 4 event reports of a 3-second duration sampled at 8 kHz
Resolution:	4 and 12 samples/cycle

Event Summary

Storage:	100 summaries
----------	---------------

Sequential Events Recorder

Storage:	1000 entries
Trigger Elements:	250 relay elements

Resolution:	0.5 ms for contact inputs
Resolution:	1/12 cycle for all elements

Processing Specifications

AC Voltage and Current Inputs

8000 samples per second Full-cycle cosine filtering
--

Protection and Control Processing

12 times per power system cycle

Control Points

96 remote bits 64 local control bits 32 latch bits in protection logic 32 latch bits in automation logic

Relay Element Pickup Ranges and Accuracies

Differential Elements

Number of Zones:	6
Number of Check Zones:	3
Number of Terminals	
Three-Relay Application:	21
Single-Relay Application:	7
Pickup Range:	0.10–4.00 pu
Pickup Accuracy:	1 A nominal: $\pm 5\% \pm 0.02$ A 5 A nominal: $\pm 5\% \pm 0.10$ A
Slope 1	
Setting Range:	15%–90%
Slope 2	
Setting Range:	50%–90%

Supervising Differential Element

Quantity:	9 total, 1 per zone (6 standard zones, 3 check zones)
Setting Range:	0.05–3.00 pu
Accuracy:	$\pm 5\% \pm 0.02 \cdot I_{\text{NOM}}$

Incremental Restraint and Operating Threshold Current Supervision

Setting Range:	0.1–10.0 pu
Accuracy:	$\pm 5\% \pm 0.02 \cdot I_{\text{NOM}}$

Sensitive Differential Current Alarm

Quantity:	9 total, 1 per zone (6 standard zones, 3 check zones)
Setting Range:	0.05–1.00 pu
Accuracy:	$\pm 5\% \pm 0.02 \cdot I_{\text{NOM}}$
Timer Setting Range:	50–6000 cycles

Instantaneous/Definite-Time Overcurrent Elements

Phase Current Setting Range	
5 A Model:	OFF, 0.25–100.00 A secondary, 0.01 A steps
1 A Model:	OFF, 0.05–20.00 A secondary, 0.01 A steps
Accuracy (Steady State)	
5 A Model:	± 0.05 A, $\pm 3\%$ of setting
1 A Model:	± 0.01 A, $\pm 3\%$ of setting
Transient Overreach:	$< 5\%$ of setting
Timer Setting Range:	0.00–99999.00 cycles, 1/6-cycle steps
Timer Accuracy:	$\pm 0.1\%$ of settings $\pm 1/6$ cycle
Maximum Operating Time:	1.5 cycles

Time-Overcurrent Elements

Pickup Range	
5 A Model:	0.25–16.00 A secondary, 0.01 A steps
1 A Model:	0.05–3.20 A secondary, 0.01 A steps
Accuracy (Steady State)	
5 A Model:	± 0.05 A, $\pm 3\%$ of setting
1 A Model:	± 0.01 A, $\pm 3\%$ of setting
Time Dial Range	
US:	0.50–15.00, 0.01 steps
IEC:	0.05–1.00, 0.01 steps
Curve Timing Accuracy:	± 1.50 cycles, $\pm 4\%$ of curve time (for current between 2 and 30 multiples of pickup)
Reset:	1 power cycle or Electromechanical Reset Emulation time

Under- and Overvoltage Elements (27, 59)

Processing Rate:	1/6 cycle
Phase Under- and Overvoltage (2 Level/Phase)	
Setting Range:	2.00–300 V_{L-N} in 0.01 steps
Accuracy:	$\pm 3\%$ of setting, ± 0.5 V
Transient Overreach:	$< 5\%$ of pickup
Maximum Delay:	1.5 cycles
Zero- and Negative-Sequence Overvoltage Elements	
Setting Range:	2.00–300 V_{L-N} in 0.01 steps
Accuracy:	$\pm 5\%$ of setting, ± 1 V
Transient Overreach:	$< 5\%$ of setting
Maximum Delay:	1.5 cycles

Breaker Failure Instantaneous Overcurrent

Setting Range	
5 A Model:	0.50–50 A, 0.01 A steps
1 A Model:	0.10–10.0 A, 0.01 A steps
Accuracy	
5 A Model:	± 0.05 A, $\pm 3\%$ of setting
1 A Model:	± 0.01 A, $\pm 3\%$ of setting
Transient Overreach:	$< 5\%$ of setting
Maximum Pickup Time:	1.5 cycles
Maximum Reset Time:	< 1 cycle
Timers Setting Range:	0–6000 cycles, 1/12-cycle steps (BFPUnn, RTPUmn) 0–1000 cycles, 1/12-cycle steps (BFISPnn, BFIDOnn)
Time Delay Accuracy:	1/12 cycle, $\pm 0.1\%$ of setting

Disconnect Monitor

Number:	60
Timer Setting Range:	0–99999 cycles, 1 cycle step

Breaker Status

Number:	21
---------	----

Coupler Security Logic

Number:	4
Timer Setting Range:	0–1000 cycles, 1/12 cycle step

Control Input Timers

Setting Range	
Pickup:	0.00–30 ms
Dropout:	0.00–30 ms

Station DC Battery System Monitor Specifications

Rated Voltage:	24–250 Vdc
Operational Voltage Range:	0–300 Vdc
Sampling Rate:	2 kHz
Processing Rate:	1/8 cycle
Operating Time:	Less than 1.5 cycles (all elements except ac ripple) Less than 1.5 seconds (ac ripple element)

Setting Range

15–300 Vdc, 1 Vdc steps (all elements except ac ripple)
1–300 Vac, 1 Vac steps (ac ripple element)

Accuracy

Pickup Accuracy:	$\pm 3\% \pm 2$ Vdc (all elements except ac ripple) $\pm 10\% \pm 2$ Vac (ac ripple element)
------------------	---

Metering Accuracy

All metering accuracies are based on an ambient temperature of 20°C and nominal frequency.

Currents**Phase Current Magnitude**

5 A Model:	$\pm 0.2\%$ plus ± 4 mA (2.5–15 A sec)
1 A Model:	$\pm 0.2\%$ plus ± 0.8 mA (0.5–3.0 A sec)

Phase Current Angle

All Models:	$\pm 0.2^\circ$ in the current range (0.5–3.0) • I_{NOM}
-------------	---

Differential Currents per Zone (Steady State)

IOP, IRT:	$\pm 5.0\% \pm 0.02 \cdot I_{NOM}$
IOPCZ, IRTCA:	$\pm 5.0\% \pm 0.02 \cdot I_{NOM}$

Voltages**Phase Voltage Magnitude**

300 V Maximum Inputs:	$\pm 2.5\% \pm 1$ V (5–33.5 V) $\pm 0.1\%$ (33.5–300 V)
-----------------------	--

Phase Angle

300 V Maximum Inputs:	$\pm 1.0^\circ$ (5–33.5 V) $\pm 0.5^\circ$ (33.5–300 V)
-----------------------	--

Technical Support

We appreciate your interest in SEL products and services. If you have questions or comments, please contact us at:

Schweitzer Engineering Laboratories, Inc.
2350 NE Hopkins Court
Pullman, WA 99163-5603 U.S.A.
Tel: +1.509.338.3838
Fax: +1.509.332.7990
Internet: selinc.com/support
Email: info@selinc.com

© 2018-2024 by Schweitzer Engineering Laboratories, Inc.

Content subject to change without notice.

Unless otherwise agreed in writing, all SEL product sales are subject to SEL's terms and conditions located here: <https://selinc.com/company/termsandconditions/>.

SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court • Pullman, WA 99163-5603 U.S.A.
Tel: +1.509.332.1890 • Fax: +1.509.332.7990
selinc.com • info@selinc.com

