


# 2026 Product and Solution Guide



# **New and Upcoming Products**

SEL-9L Line Relay	19
LINAM® UGFI Underground Fault Indicator	39
SEL-T35 Time-Domain Power Monitor	43
SEL-2743 Ethernet Switch	52
SEL-2744 Ethernet Switch	52
SEL-3790 Low-Voltage Divider Module	67

# **Contents**

About SEL	2
SEL Innovations and Solutions	6
Generator Protection	8
Industrial and Commercial Protection	12
Transmission Line Protection and Fault Locating	16
Substation Protection	22
Distribution Protection and Control	28
Fault Indicators, Sensors, and CTs	34
Metering and Power Monitoring	38
Automation and Computing Platforms	42
SEL Network Communications Solutions	48
WAN and LAN Networks	50
Wireless Communications	54
Precise Time	56
Transceivers and Adapters	58
Cables	60
Remote I/O	62
Annunciation and Notification	63
Software	64
Accessories and Tools	67
Panels and Enclosures	68
Direct-Replacement Assemblies	69
SEL Services	70
Project and Program Management	71
Microgrids and Power Management	72
Cyber Services	73
Education and Training	74
Ordering and Customer Support	76
Index	78

#### SEL **About SEL**

## Our Mission: Making Electric Power Safer, More Reliable, and More **Economical**


SEL invents, designs, manufactures, and supports a complete line of products and services for the protection, monitoring, control, automation, and metering of electric power systems.

Our solutions range from comprehensive generator and transmission protection to distribution automation and control systems.

Our Engineering Services division partners with customers globally to create turnkey solutions and services that help protect and control critical electrical infrastructure worldwide. We also offer education and full product support.

SEL products are in more than 170 countries and support industries from petrochemical to transportation to electric utilities.







Looking Back, Moving Forward

SEL Founder and Chairman of the Board Dr. Edmund O. Schweitzer, III. invented the first microprocessor-based digital protective relay, the SEL-21, in 1982. The SEL-21 revolutionized the electric power industry by providing reliable transmission line protection with fault locating at a much lower cost than traditional electromechanical relays.

In the decades since, SEL has launched power industry innovations including the load-encroachment element in a transmission relay, synchrophasors as a standard feature in protective relays, and Mirrored Bits® relay-to-relay communications.

#### 2020

We added the SEL-T401L Ultra-High-Speed Line Relay to our family of protective relays, automation controllers, digital secondary system solutions, recloser controls, and more. The SEL-T401L is the first relay in the world to combine traveling-wave and incremental-quantity elements with phasor-based protection.

#### 2021

We released our newest overcurrent protective relay, the SEL-851 Feeder Protection Relay, as well as our operational technology (OT) application platform, Blueframe®, and its first application suite, SEL Data Management and Automation (DMA).

#### 2022

We introduced the SEL Axion® Bay Controller and SEL Fault Location, Isolation, and Service Restoration (FLISR), a wide-area control application that operates on our Blueframe application platform to locate and isolate faults and automatically restore power to healthy portions of affected lines or feeders.

#### 2023

We made major enhancements to our IEC 61850-based solutions, including a new gigabit Ethernet card for SEL-400 series relays and Parallel Redundancy Protocol (PRP) support for Sampled Values (SV)-based process bus applications.

Dr. Edmund O. Schweitzer, III Inventor of the world's-first digital protective relay—the SEL-21.

#### Industries We Serve

- Electric power generation
- Power transmission and distribution
- Oil, gas, and petrochemical
- Renewable energy
- Metals and mining
- Water and wastewater
- Pulp and paper
- Mission-critical power systems
- Government
- Education and healthcare
- Consumer product manufacturing
- Transportation
- Data centers
- Land mobile radio systems

# 2024

We released the SEL-TWFL Dual Traveling-Wave Fault Locator and 12-Channel MHz Recorder, which locates faults to within one tower span and monitors up to two transmission lines from a single substation.

#### 2025

We introduced the SEL-T35 Time-Domain Power Monitor, which continuously streams time-synchronized waveform oscillography and industry-exclusive energy packets. We also released the LINAM® UGFI Underground Fault Indicator, which streamlines underground fault locating and offers industry-leading adjacent-phase immunity.

## **Quality in Manufacturing**

We design and manufacture all our electronic devices in the U.S.A. This allows for direct collaboration and short feedback loops between our research and development and manufacturing divisions as well as world-class supply chain security. We manufacture our own critical components, like metal cabinets, printed circuit boards (PCBs), and magnetic devices, in our secure, SEL-owned and -operated facilities in Washington, Idaho, Illinois, and Indiana.

SEL exceeds industry quality standards, requirements, and customer expectations. We test our products thoroughly and verify that they will perform under demanding and harsh conditions.

Our quality practices include:

- Monitoring and controlling processes to exceed the ISO 9001:2015 Quality Management Systems Standard.
- Developing robust, repeatable, and scalable manufacturing processes to address process errors.
- Ensuring that our test and calibration laboratories use the latest equipment and follow National Institute of Standards and Technology (NIST) traceable standards for accuracy and maintenance.
- Partnering with our suppliers for the highest possible quality and value.



"As an engineering company, we work every day to invent, design, and support products that monitor, control, and protect power systems installed all over the world. Serving our industry is a tremendous privilege and responsibility that we take very seriously. Listening to our customers' requirements and needs, we strive to make our solutions innovative, reliable, easy to use, and secure. We invest in our people, tools, and facilities in order to produce designs that exceed our customers' requirements. Engineering is our middle name, and it's what we love to do."

Dave Whitehead President

#### Warranty, Service, and Support

We back our products with a tenyear warranty, no-charge diagnostic and repair services, local support, and a variety of test procedures and certifications.

Our dedicated support teams are located in regional offices around the globe and staffed with SEL application engineers who are experts in our products and in power system applications. We offer free, 24/7 emergency technical support for the life of your SEL products.

Many support questions may also be answered by visiting our video portal at video.selinc.com, where you'll find how-to and support videos ranging from product set up and configuration to report retrieval and resource management.

#### **Learn More**

Read more about our history, products, and practices at selinc.com/company/about.

# **SEL Innovations and Solutions**

# **Traveling-Wave and Time-Domain Technologies**

- Protection that isn't dependent on sources; great for areas with high inverter-based resource integration.
- Detects and issues trip commands in 1-2 ms, 5-10 times faster than traditional protection.
- The most accurate fault locator available; pinpoints faults to within one tower span.

#### **Software-Defined Networking**

- The only engineered network designed for reliable control system operations.
- Ensures traffic only flows between designated points and blocks all other traffic, eliminating the need for complex firewall rules.
- Redirects network traffic to alternate paths in under 100 µs when the network breaks.

#### SEL POWERMAX® Power Management and Microgrid **Control Solutions**

- Maximizes uptime by controlling generation, shedding loads, and automatically synchronizing microgrids.
- Scalable from oil refineries to solar and wind farms to managing an entire country's power system.
- Manages energy costs and determines the optimal generation dispatch based on operational conditions.

# SEL Arc Sense<sup>™</sup> Technology for Wildfire Mitigation

- Detects and isolates high-impedance downed conductors to reduce fire risk while keeping unaffected line sections energized.
- Alerts operators of a fallen conductor or instructs circuit breakers or recloser controls to isolate the affected circuit.
- Available in many devices already deployed in your distribution systems.

#### **Time-Domain Power Monitoring** With Energy Packet Technology

- Streams continuous waveform data to SEL Synchrowave® software, which captures, analyzes, and stores every disturbance.
- Accurately measures energy transfer every millisecond, regardless of the waveshape, frequency, or phase.
- Calculates energy in a simple method that is traceable to the fundamentals of physics and mathematics.

# SEL Time-Domain Link (TiDL®) **Technology**

- The simplest, most reliable, and lowest-cost digital secondary system available.
- Plug-and-operate configuration.
- Requires no network switches or clocks.

# SEL ICON® Virtual Synchronous **Networking**

- Packet transport with deterministic time-division multiplexing (TDM) and better than 1 ms latency.
- Enables TDM-based line current differential protection within IP core networks.
- Allows packet-based and TDM-based systems to work together, greatly reducing communications migration or upgrade costs.

#### **SEL Arc-Flash Solutions**

- Life-saving arc-flash protection operates in milliseconds to reduce arc fault energy.
- Combines light sensing with fast overcurrent protection to provide high-speed detection without operating for external faults.
- Works with low- and medium-voltage switchgear and easily coordinates with other devices in industrial- and commercial-scale facilities.

## **SEL-487E Centralized Protection** and Control

- Simplifies commissioning, testing, firmware management, and cybersecurity while reducing the total cost of ownership.
- Built on a proven relay platform.
- Offers flexible deployment solutions, including traditional I/O connections, SEL TiDL, or IEC 61850.

#### SEL-5702 Synchrowave **Operations Software**

- Wide-Area Situational Awareness (WASA) software that aggregates time-series data, including synchrophasor data, relay event reports, and high-resolution waveform streams.
- Equips transmission control centers with tools to transform time-synchronized data into detailed system insights that support decision making.
- Simple to use and customizable to maximize WASA.

#### Blueframe® Data Management and Automation (DMA)

- Automatically collects, stores, and manages device-specific information to simplify system-wide device management and compliance.
- Automates the collection of oscillography, Sequence of Events data, device settings, property information, and other data.
- Rotates passwords and streamlines device audits with summary reports that identify device changes.

#### Blueframe FLISR (Fault Location, Isolation, and Service Restoration)

- Enables you to create system configurations in minutes with no complex modeling required.
- Manages protection and switching devices at the grid edge, increasing the speed of service restoration.
- Manufacturer-agnostic recloser support through DNP3.

## High-Density Coordination™ **Solutions for Distribution Protection and Reclosing**

- Simplify recloser deployment in any feeder topology, overcoming the limitations of traditional timeovercurrent coordination.
- Coordinate the actions of any number of SEL-651R Advanced Recloser Controls, allowing all of them to operate quickly, securely, and dependably.
- Implement with your existing communications infrastructure or even without communications.

## **SEL-RPM Redundant Power Module**

- A reliable and simple multisource module to power your protection, monitoring, and control equipment.
- Combines as many as three ac sources and one dc source for dependable control power during normal operations and power disturbances.
- Keeps protection, automation, and SCADA running and increases device availability, even during station battery servicing and station power interruptions.

### **SEL Grid Configurator Software**

- Provides context-oriented configuration and commissioning tools for SEL power system devices.
- Facilitates device testing and commissioning through customized HMI dashboards.
- Simplifies settings evaluation with intuitive comparison interfaces.

#### **ACSELERATOR Architect®** SEL-5032 Software

- Provides powerful and simple IEC 61850 configuration.
- Efficiently supports a top-down engineering workflow in the role of the IED Configuration Tool (ICT).
- Innovative interoperability features include the ability to create a custom IED data model and the ability to use multiple IEC 61850 editions in the same system.

# **Generator Protection**

selinc.com/products/categories/protective-relays/#generator-protection

Modern generators and related equipment require advanced protection, automation, control, metering, and security. SEL products and solutions, including engineering services, address any nameplate rating from megawatt to kilowatt and range from wide-area protection systems down to utilityscale generation and microgrids.

#### **Applications**


- Hydropower
- Steam and thermal generation
- Combustion and combined-cycle generation
- Wind power
- Solar power
- Nuclear
- Power management (PowerMAX®)
- Microgrids
- Remedial action schemes/ special protection systems
- Electrical balance-of-plant




#### **Customer Story**

Belgium Integrates Offshore Wind Power Into European Grid

selinc.com/featured-stories/elia



**Example System Diagram** 



♣RTAC

Controller

#### Webinar

Protection Advancements to Benefit Generators of All Sizes and Types selinc.com/events/on-demandwebinar/130607

#### **Related Material**

POWERMAX Solutions

selinc.com/api/download/ blt1d488719cce3a781/?lang=en-us

#### **Technical Papers**

Fast Wind Farm Restoration Using Wireless Fault Sensors to Identify Faulted Segments selinc.com/api/download/130379

Leveraging Digital Relays for Protection of Pumped Storage Hydro


selinc.com/api/download/121666

Capability Curve-Based Generator Protection Minimizes Generator Stress and Maintains Power System Stability

selinc.com/api/download/124333

Stator Ground Protection for Multiple High-Impedance Grounded Generators Sharing a Common Bus selinc.com/api/download/124321

Upgrading PacifiCorp's Jim Bridger RAS to Include Wind Generation selinc.com/api/download/135500





# SEL-400G Advanced Generator **Protection System**

Combine generator, bus, and step-up transformer protection in one package, and achieve comprehensive protection and monitoring for generators of all types and sizes, including those used in pumped-storage applications.



# **SEL-700G Generator Protection Relay**

Provide generator or unit protection in utility, industrial, and renewable applications with the flexible I/O and functionality of the compact, economical SEL-700G.



#### **SEL-300G Generator Relay**

Implement primary and backup protection for utility and industrial generators.



# SEL-2664S Stator Ground **Protection Relay**

Protect high-impedance grounded generators from ground faults at standstill, during startup, and while running. All SEL-2664S relays are sold with the SEL-4664 Calibration Module.



#### SEL-2664 Field Ground Module

Combine the SEL-2664 with other SEL generator protective devices to continuously monitor field-toground resistance and protect critical components, including rotor and stator windings.



#### SEL-2600 RTD Module

Measure and transmit data from as many as 12 resistance temperature detector (RTD) inputs and one contact input over a single fiber-optic link.



#### **SEL-2414 Transformer Automation Controller**

Control load tap changers and transformer cooling stages with one device. The SEL-2414 offers comprehensive voltage regulation, transformer monitoring, and flexible I/O options to fit your application requirements.



# SEL-3555 Real-Time **Automation Controller (RTAC)**

The SEL-3555 provides powerful processing for large-scale automation projects.



#### SEL-2742 Ethernet Switch

The SEL-2742 is a 12-port, DINrail-mount switch for industrial environments. It combines with the SEL-5056 Network Management System (NMS) to simplify network engineering and improve LAN security.

Applications	SEL-400G	SEL-300G	SEL-700G	SEL-700GT	SEL-700GW
Generator Protection	•	•	•	+	■1
Unit/Overall (Generator + Generator Step-Up [GSU]) Differential Protection	•	+	•		
Independent GSU Transformer Protection	•				
Pumped-Storage Hydro Protection	-		•		
Integrated Synchronizer	+		+	+	
Breaker Failure Protection	-	f	-	-	•
Equipment Thermal Monitoring	•	+	+	+	+
Generator Intertie Protection					

#### Instrumentation and Control

instrumentation and Control					
SELogic® Control Equations/Remote Control Switches	•	•	•	•	•
Nonvolatile Latch Control Switches	•	•	•	•	•
Multiple Settings Groups	•	•	•	•	•
Station Battery Monitor	•	•			
Breaker Wear Monitor	•	•	•	•	•
Event Report (Multicycle Data)/Sequential Events Recorder	•	•	•	•	
Disturbance Recording up to 300 seconds	•				
Demand Meter	•	•	•	•	•
Load Profile Report	•		•	•	•
RTD Inputs	+	+	+	+	+
Ethernet	+		+	+	+
Built-In Web Server	+		+	+	+
EtherNet/IP			+	+	+
IEEE 1588 Precision Time Protocol (PTP)	+		+	+	+
IEC 61850 Edition 2	+		+	+	+
IEC 60870-5-103			+	+	+
Parallel Redundancy Protocol (PRP)	+		+	+	+
DNP3 Serial	•		+	+	+
DNP3 LAN/WAN	+		+	+	+
Simple Network Time Protocol (SNTP)	+		+	+	+
Rapid Spanning Tree Protocol (RSTP)			+	+	+
Modbus TCP	+		+	+	+
Modbus RTU		•	•	•	
IEEE C37.118 Synchrophasors (With Protocol Edition)	2011		2005	2005	2005
MIRRORED BITS® Communications	•		-	•	•

#### Miscellaneous

Dual Frequency Zones (Generator and System)	•				
Frequency Tracking Range	5- 120 Hz	20- 70 Hz	15– 70 Hz	15– 70 Hz	15- 70 Hz
Accepts Wye or Open-Delta Voltage Transformers		•	•	•	•
Connectorized® (Quick Disconnect) Available	+	+			

	SEL-400G	SEL-300G	SEL-700G	SEL-700GT	SEL-700GW
Protection	S	S	S	S	S
21C Compensator Distance		•	+		
21P Phase Mho Distance	•	•			
24 Overexcitation (Volts/Hertz)	•	•	•	+	
25 Synchronism Check	•	+	+	+	
27/59 Under-/Overvoltage	•	•	•	+	
271/59I Inverse-Time Undervoltage/ Overvoltage	•		•	•	
32 Directional Power	•	•	•	+	
40 Impedance-Based Loss of Field	•	•	•	+	
40 Capability-Based Loss of Field	•				
46 Current Unbalance	•	•	•	+	
46 Harmonic Current Unbalance					
49 Thermal Model	•	•	•	+	
49R Thermal Overload (RTD)	•		•	•	
50 (P,N,G) Overcurrent (Phase, Neutral, Ground)	•	•	•	•	•
50Q Negative-Sequence Overcurrent	•	+	•	-	•
51 (N,G) Time Overcurrent (Neutral, Ground)	•	-	-	-	•
51 (P,Q) Time Overcurrent (Phase, Neg. Seq.)	•	-		-	•
60 Loss of Potential	•	•	•	+	
60 Voltage Balance Loss of Potential					
60 (P,N) Independent Split-Phase (Phase, Neutral)	•				
64G 100 Percent Stator Ground	•	•	+		
64G Intermittent Ground Fault Detection					
64F Field Ground		•		•	
67 (N,G) Directional Overcurrent (Neutral, Ground)			•	+	
67Q Negative-Sequence Directional Overcurrent	•			•	
78 Out of Step	•	•	+		
78 Dual Zone (Generator and System) Out of Step With Pole Slip Counters	•				
78VS Vector Shift				-	
81 Over-/Underfrequency	•	•	•	•	
81A Accumulated Frequency	•				
81R Rate-of-Change of Frequency	•			-	
87 Stator Differential	•	+	+		
Transformer Differential					
REF Restricted Earth Fault				+	
Inadvertent Energization		•	•	+	
Flashover Protection		f	f		
Low-Energy Analog (LEA) Current and Voltage Sensors Support			+	+	+

■ Standard feature + Model option **f** May be created using settings

<sup>1</sup>Protects wind collector system apparatus during overcurrent events



# **Industrial and Commercial Protection**

selinc.com/solutions/industrial

SEL power management, protection, automation, and control solutions are hard at work in heavy industries and commercial-scale facilities around the world. These solutions protect lowand medium-voltage equipment and help improve system performance, availability, and process efficiency.

**Example System Diagram**Combine SEL low- and mediumvoltage protective relays with other SEL
automation, monitoring, and control

# **Applications**

- Asynchronous (induction) and synchronous motor protection
- Variable-frequency drive protection
- Motor bus transfer systems
- Motor control centers
- Arc-flash mitigation
- Power quality and revenue metering
- Power management and control systems (PowerMAX®)
- Microgrid control systems
- Wide-area protection and remedial action schemes



#### **Customer Story**

Mine Discovers Arc-Flash Detection Saves Lives and Equipment selinc.com/highlights/mining-arc-flash

#### products for a comprehensive solution. Motor Bus Transfer Relay Meter Source High-Impedance SEL-787Z SEL-700B SEL-73 Differential Relay SEL-2742 SEL-2742 SEL-787L Line Relay Feeder Relay SEL-751 Load Feeder SEL-700G Relay Transformer Relay Generator Relay Satellite-Synchronized Clock Motor SEL-2488 SFI -849 Relay SEL-851 Real-Time Feeder Relay Automation Controller :::::: SEL-2742 SEL-2741 SDN Switch SEL-2742 Motor SDN Switch Management Relay

#### Webinars

New Cable and Bus Differential Solutions for Data Center Medium-Voltage Power Systems

selinc.com/events/on-demand-webinar/

Effective Arc-Flash Mitigation Strategies

selinc.com/events/on-demand-webinar/

SEL POWERMAX Power Management and Control System for Industrial Applications (Part 1)

selinc.com/events/on-demand-webinar/132490

#### **Technical Papers**

Case Study: Deployment of 300 Smart Motor Control Centers selinc.com/api/download/124143

Advancement of Safety Features for Industrial Power System Operations and Control

selinc.com/api/download/140315

Making My Paper Mill Safer: An Arc-Flash Energy Reduction Story selinc.com/api/download/126387

Case Study: Adaptive Load Shedding in Critical Industrial Facilities selinc.com/api/download/130119

#### White Paper

Purpose-Engineered, Active-Defense Cybersecurity for Industrial Control Systems

selinc.com/api/download/121044

#### **Videos**

How a Data Center Achieves Utility-Grade Metering

video.selinc.com/detail/video/ 5747812817001/how-a-data-centerachieves-utility-grade-metering

Engineer a Better Network—It Starts With SDN

video.selinc.com/detail/videos/ software-defined-networking



# SEL-787L Line Current Differential Relay

The SEL-787L is an economical and dependable line current differential protection solution that offers arc-flash protection, fault locating, high-impedance fault detection, and more.



#### **SEL-751 Feeder Protection Relay**

The SEL-751 offers feeder protection, an intuitive color touchscreen, fast and secure arc-flash detection, flexible I/O, and advanced communications.



# **SEL-851 Feeder Protection Relay**

The SEL-851 is a compact relay that provides overcurrent, voltage, and arc-flash protection as well as versatile communications.



# SEL-700BT Motor Bus Transfer Relay

Ensure motor bus system process continuity by allowing the quick transfer of load to an auxiliary feeder during primary feeder line faults.



# SEL-710-5 Motor Protection Relay

Provide protection, including optional arc-flash detection, for a full range of medium-voltage, three-phase induction, and synchronous motors.



# SEL-849 Motor Management Relay

Provide current-, voltage-, and thermal-based protection; arc-flash detection; and power metering in low-voltage to medium-voltage motor protection applications.



# SEL-700G Generator **Protection Relay**

Provide standby, emergency, and co-generator protection with an autosynchronizer, flexible I/O, and advanced communications.



# SEL-787-2/-3/-4 Transformer **Protection Relay**

Apply advanced protection and monitoring with flexible communications to two-, three-, and four-terminal transformers.



# SEL-787Z High-Impedance Differential Relay and SEL-HZM **High-Impedance Module**

The SEL-787Z combines high-impedance protection principles with advanced numerical technologies to provide high-impedance differential protection. Apply the SEL-787Z and SEL-HZM High-Impedance Module for a comprehensive, single-zone bus-protection solution.



#### SEL-735 Power Quality and **Revenue Meter**

SEL meters offer bidirectional, full fourquadrant, and high-accuracy energy metering as well as precise and reliable power quality measurements.



#### SEL-2600 RTD Module

Measure and transmit data from as many as 12 resistance temperature detector (RTD) inputs and one contact input status over a single fiber-optic link.



#### SEL-2742 Ethernet Switch

The SEL-2742 is a 12-port, DIN-rail-mount switch for industrial environments. It combines with the SEL-5056 Network Management System (NMS) to simplify network engineering and improve LAN security.



# SEL-3555 Real-Time Automation Controller (RTAC)

The SEL-3555 provides powerful processing for large-scale automation projects.



## SEL-3350 Computing **Platform**

The SEL-3350 is ideal for limitedspace, dedicated embedded applications that require midlevel I/O and computation. It can be configured as a Real-Time Automation Controller (RTAC), as a computer, or with the SEL Blueframe® application platform.

Applications	SEL-787L	SEL-751	SEL-851	SEL-700BT	SEL-710-5	SEL-849	SEL-700G	SEL-787-2/-3/-4	SEL-787Z
Generator Protection		+					•		
Motor Protection					•	•			
Motor Bus Transfer Protection				•					
Feeder Protection	•	•	٠	•		•	+		
Transformer Protection								•	
Bus Differential Protection								•	•
Line Current Differential Protection	-								

Protection									
24 Overexcitation (Volts/Hertz)							•	+	
27/59 Under-/Overvoltage	+	+	+	•	•	+	•	+	•
32 Directional Power	+	+	+			+	•	+	
37 Underpower					•	•			
46 Current Unbalance					•	٠	•		
47 Phase Reversal					•	•			
49 Thermal	•	•			•	•	•		
49R Thermal Overload (RTD)	+	+		-	+		•	•	
50 Overcurrent	•	•	•	•	•	•	•	+	٠
51 Time Overcurrent	•	-	•	-	•	•	•	+	•
55 Power Factor	+	+	+		•	+	f		
60 Loss of Potential	+	+	+	-	•	+	•		
64F Field Ground							•		
67 (N,G) Directional Overcurrent (Neutral, Ground)	+	+	+				•		
81 Over-/Underfrequency	+	+	+	•	•		•	+	
87 Current Differential					+		+	•	
87L (P,G,Q) Line Differential	•								
87Z High-Impedance Differential									•
REF Restricted Earth Fault							•	+	
Arc-Flash Detection	+	+	+		+	-			+
Separate Neutral Overcurrent	•	-	-	-	-	-	•	+	
Broken Rotor Bar Detection					•				

Instrumentation and Control	SEL-787L	SEL-751	SEL-851	SEL-700BT	SEL-710-5	SEL-849	SEL-700G	SEL-787-2/-3/-4	SEL-787Z
Breaker Wear Monitoring	•	•		•	•		•	•	
RTD Inputs	+	+		+	+		+	+	
Low-Energy Analog (LEA) Current and Voltage Sensors Support	+	+		+	+		+	+	
IEC 61850 Edition 2			+	+	+		+	+	+
IEC 61850 Edition 2.1	+	+							
IEC 61869-9 SV Publishing			+						
Parallel Redundancy Protocol (PRP)	+	+	+	+	+	•	+	+	+
DNP3 Serial	+	+	+	+	+	+	+	+	+
DNP3 LAN/WAN	+	+	+	+	+	+	+	+	+
Simple Network Time Protocol (SNTP)	+	+	•	+	+	•	+	+	+
Built-In Web Server	+	+	•	+	+	•	+	+	+
IEEE 1588 Precision Time Protocol (PTP)	+	+	+	+	+		+	+	+
EtherNet/IP	+	+	+	+	+	+	+	+	+
Modbus TCP	+	+	•	+	+	+	+	+	+
Modbus RTU Outstation	•	•	•	•	•	•	•	•	•
Rapid Spanning Tree Protocol (RSTP)	+	+	+	+	+		+	+	+



# Transmission Line Protection and Fault Locating

selinc.com/products/categories/protective-relays/#line-protection | selinc.com/products/categories/fault-locating

SEL transmission line protective relays provide reliable subcycle line current differential and multizone distance protection. Their faultlocating capabilities allow you to efficiently dispatch line crews to quickly isolate line problems and restore service faster.

# **Applications**

- Time-domain line protection
- Differential protection
- Pilot protection: directional and distance
- Step distance protection
- Single-pole tripping
- Series-compensated lines
- Single- and dual-breaker terminals

#### **Technical Papers**


Modern Line Current Differential **Protection Solutions** selinc.com/api/download/6390

Transmission Line Protection System for Increasing Power System Requirements selinc.com/api/download/2603

A Fresh Look at Limits to the Sensitivity of Line Protection selinc.com/api/download/8505

Series Compensation, Power Swings, and Inverter-Based Sources and Their Impact on Line Current **Differential Protection** selinc.com/api/download/21474837052

Speed of Line Protection - Can We Break Free of Phasor Limitations? selinc.com/api/download/106193



#### **Real-World Event Reports**

Field Experiences With Traveling-Wave Protection and Fault Locating selinc.com/mktg/122973

#### Webinar

Detecting and Locating a Broken Conductor Before It Converts Into a Fault

selinc.com/events/on-demandwebinar/136022



# SEL-T401L Ultra-High-Speed Line Relay

Apply the SEL-T401L, which was built on the field experience of the SEL-T400L, for its unprecedented operating speed and complete suite of primary and backup line protection functions. The SEL-T401L can trip within 1 ms, records events with a 1 MHz sampling rate, locates faults to the nearest tower, and uses line monitoring to detect and locate incipient and recurring faults.



# SEL-411L Advanced Line Differential Protection, Automation, and Control System

Apply the SEL-411L for comprehensive line differential protection for up to four terminals; subcycle distance protection; and directional overcurrent protection. Use traveling-wave fault locating to pinpoint faults to the nearest tower span. Broken conductor detection logic can identify line breaks on overhead conductors.



# SEL-421 Protection, Automation, and Control System

Apply the SEL-421 for subcycle distance and directional overcurrent protection.



#### SEL-9L Line Relay COMINGSOON

Use the SEL-9L for comprehensive line protection on single- or dual-breaker subtransmission lines. Universal hardware, modern communications and cybersecurity, and flexible firmware options enable you to tailor the relay to your application.



# SEL-311L Line Current Differential Protection and Automation System

Use the SEL-311L for comprehensive, easy-to-apply line differential and four-zone distance protection.



# SEL-311C Transmission Protection System

Apply the SEL-311C-1 for three-pole distance protection, reclosing, monitoring, and control of breakers on transmission lines. Apply the SEL-311C-2/-3 for single-pole tripping.



## SEL-TWFL Dual Traveling-Wave Fault Locator and 12-Channel MHz Recorder

Use the SEL-TWFL alongside existing line protective relays to locate faults and monitor two line terminals at a substation.



# SEL-T4287 Traveling-Wave Test System

Test traveling-wave fault locators and line protective relays (e.g., the SEL-T401L and SEL-411L) using the SEL-T4287, a simple and compact secondary pulse injection test set.

Applications	SEL-T401L	SEL-411L	SEL-421	SEL-311C	SEL-311L	SEL-9L
Pilot Protection—Directional	•	•	•	•	•	+
Pilot Protection—Directional and Distance	•	•	•	•	•	+
Differential Protection	•	•			•	
Step Distance Protection	•	•	•	•	•	+
Single-Pole Tripping	•	•	•	•	•	+
Series-Compensated Lines	•	+	+			
Dual-Breaker Terminals		+				+

## **Major Protection Functions**

Major Protection Functions						
21P Phase Distance—Mho	4	5	5	4	4	4
21G Ground Distance—Mho	4	5	5	4	4	4
21P Phase Distance—Quadrilateral	4	5	5			4
21G Ground Distance—Quadrilateral	4	5	5	4	4	4
Subcycle Distance Operation	-	+	+	•		•
Nondirectional Distance Zone	1					1
Step Distance Timers	5	5	5	4	4	5
Incremental-Quantity Distance	-					
32 Directional	-	•	•	•	•	•
TD32 Incremental-Quantity Directional	•					
TW32 Traveling-Wave Directional	-					
POTT	•	٠	•	•	•	+
DCB	-	٠	•	•	•	+
DCUB	f	•	•	•	•	f
DTT	-	•	•	•	•	+
87L Line Current Differential		•			•	
TW87 Traveling-Wave Line Current Differential	-					
50 Instantaneous Overcurrent	4	4	4	4	4	6
51 Inverse-Time Overcurrent <sup>1</sup>	4	10	10	1	1	5
50 Definite-Time Overcurrent <sup>1</sup>	4	4	4	4	4	6
Switch Onto Fault	-	•	•	•	•	•
Breaker Failure		•	•	•	f	+
59 Overvoltage	-	•	•	•	•	•
27 Undervoltage	-	•	•	•	•	•
81 Frequency		•	•	•	•	•
49 Thermal		•	•			f
Out of Step	-	•	•	•	•	+

Instrumentation and Control	SEL-T401L	SEL-411L	SEL-421	SEL-311C	SEL-311L	SEL-9L
Loss of Potential	•	•	•	•	•	•
Load Encroachment	•	•	•	•	•	-
Power Swing Blocking	•	•	•	•	•	+
Synchronism Check		•	•	•	•	+
79 Automatic Reclosing		•	•	•	•	+
SELogic® Control Equations	•	•	•	•	•	-
Nonvolatile Latch Control Switches	•	•	•	•	•	-
SELogic Remote and Local Control Switches	•	•	•	•	•	-
Programmable Math Operations		•	•			-
Direct Fiber	•	•		•	•	-
SEL MIRRORED BITS®	•	•	•	•	•	-
IEEE C37.94	•	•			•	•

# Fault Locating, Monitoring, and Recording

Fault Locating—Single-Ended Impedance	•	•	•	•	•	•
Fault Locating—Multi-Ended Impedance	•	•				+
Fault Locating—Single-Ended Traveling Wave	•					
Fault Locating—Multi-Ended Traveling Wave	•	+				
Broken Conductor Detection		+				
Breaker Wear Monitor		•	•	•	•	
Substation Battery Monitor		•	•	•	•	•
Trip Coil Monitor		f	f	f	f	•
Advanced Trip Circuit Monitoring						•
Event Recorder (DFR)	•	•	•	•	•	•
Sequential Events Recorder (SER)	•	•	•	•	•	•
High-Resolution (1 MHz) Event Recorder	•					
Metering	-	•	•	-	•	-

■ Standard feature + Model option **f** May be created using settings <sup>1</sup>Phase, negative sequence, and zero sequence

SCADA/HMI Integration and Protocols	SEL-T401L	SEL-411L	SEL-421	SEL-311C	SEL-311L	SEL-9L
SEL ASCII, Fast Meter, and Fast SER		•	•	•	•	
DNP3 Serial		•	•	٠	•	
DNP3 LAN/WAN		•	•	•		•
Synchrophasors (IEEE C37.118)		•	•	•	•	
IEC 61850		+	+	+	+	+
Parallel Redundancy Protocol (PRP)		•	•	+		+
IEEE 1588 Precision Time Protocol Version 2 (PTPv2)		+	+			+
IEC 61850-9-2 Sampled Values		+	+			
IEC 61869-9 Sampled Values		+	+			+
Time-Domain Link (TiDL®)		+	+			
SEL Fast Time-Domain Values (1 MHz Sampling Rate Streaming)	•					


#### Miscellaneous


Trip-Rated High-Speed Outputs	•	•	•	•	•	•
Software-Invertible CT Polarities		•	•			•
Built-In Playback Test	•					
Display Points		•	٠	•	•	•
Configurable Targets		•	•	•		•
Front USB-C Port						•
Programmable Pushbuttons		12	12	10		10
Programmable Contact Inputs, 24–250 V						•
Programmable 1 A/5 A CTs						•
Printable Labels	•	•	•	•		•
Protection With Delta-Connected Voltages				•		
Color Touchscreen Display						-

<sup>■</sup> Standard feature + Model option

#### **Example System Diagram**

Combine SEL transmission protective relays with other SEL automation, monitoring, and control products for a comprehensive solution.







# **Substation Protection**

selinc.com/products/categories/protective-relays

SEL devices protect, monitor, and control critical assets located in all types of generation, transmission, and distribution substations.

#### **Applications**

- Transformer protection, monitoring, and control
- Bus protection
- Breaker failure protection
- Capacitor bank protection
- Digital secondary systems that use Time-Domain Link (TiDL®) or IEC 61850 technologies

#### Webinars

Protect Multiple Substation Assets Using One Relay: CPC Solutions With the SEL-487E

selinc.com/events/on-demand-webinar/ 139281

Innovation in IEC 61850 Digital Secondary Systems

selinc.com/events/on-demand-webinar/ 137779

#### **Technical Papers**

Considerations for Using High-Impedance or Low-Impedance Relays for Bus Differential Protection selinc.com/api/download/5562

Beyond the Nameplate—Selecting Transformer Compensation Settings for Secure Differential Protection selinc.com/api/download/114458

Beyond the Nameplate: Transformer Compensation Revisited—New Applications, Greater Simplicity selinc.com/api/download/138123

Performance of IEC 61850 Sampled Values Relays for a Real-World Fault selinc.com/api/download/137357

Redundant Bus Protection Using High-Impedance Differential Relays selinc.com/api/download/121745


Principles of Shunt Capacitor Bank Application and Protection selinc.com/api/download/6395



#### **Customer Story**

Creating a Better Future: Innovative Substation Modernization in the Philippines

selinc.com/highlights/davao-light





#### SEL-352 Breaker Failure Relay

Provide breaker failure protection and breaker control and monitoring with unparalleled flexibility. Pointon-wave opening and closing technology extends breaker life and reduces system transients and restrikes.



#### SEL-2414 Transformer **Automation Controller**

Control load tap changers and transformer cooling stages with one device. The SEL-2414 offers comprehensive voltage regulation, transformer monitoring, and flexible I/O options to fit your application requirements.



#### SEL-787-2/-3/-4 Transformer **Protection Relay**

Apply advanced protection and monitoring with flexible communications to two-, three-, and four-terminal transformers.



#### **SEL-TMU TiDL Merging Unit**

Employ the SEL-TMU for remote data acquisition in substations with Time-Domain Link (TiDL) technology systems. It can share data with up to four SEL-400 series TiDL relays.



# SEL-401 Protection, Automation, and Control Merging Unit

Apply merging units in substations with IEC 61850-9-2 Sampled Values (SV) systems. The SEL-401 is a standalone merging unit with phase overcurrent and breaker failure protection. Some SEL SV relays can be configured as merging units to provide local protection that also publishes SV data.



# SEL-787Z High-Impedance Differential Relay and SEL-HZM **High-Impedance Module**

The SEL-787Z combines highimpedance protection principles with advanced numerical technologies to provide high-impedance differential protection. Apply the SEL-787Z and SEL-HZM High-Impedance Module for a comprehensive, single-zone bus-protection solution.



#### SEL-487B Bus Differential and **Breaker Failure Relay**

Provide bus differential and breaker failure protection, automation, and control in applications with up to seven terminals per relay. Use multiple SEL-487B relays to expand up to 21 protected terminals for scalable protection and control.



# **SEL-487E Transformer Protection Relay**

Provide high-speed transformer differential protection as well as advanced monitoring, metering, automation, and control. With optional distance, second differential zone, and reclosing functionalities, use the SEL-487E for centralized protection and control applications.



# **SEL-487V Capacitor Protection and Control** System

Protect and control grounded and ungrounded, single- and doublewye capacitor bank configurations.

Transformer Protection and Monitoring  Applications	SEL-487E	SEL-387E	SEL-387	SEL-387A	SEL-787-2X/-21/-2E	SEL-787-3E/-3S/-4X	SEL-2414
Breaker Failure Protection	•	f	f	f	•	•	f
Percentage-Restrained Current Differential	-	•		•	•	•	
Number of Differential Zones	1 or 2+	1	1	1	1	1	
Underfrequency Load Shedding	•	f			+	+	
Undervoltage Load Shedding	•	f			+	+	
Three-Phase Current Inputs	6	3	4	2	2*	3 or 4	2*
Three-Phase Voltage Inputs	2	1			1*	1*	1*

Protection
21 Phase and

21 Phase and Ground Distance	+						
24 Overexcitation (Volts/Hertz)	•	•			+	+	
25 Synchronism Check	-					+	
27/59 Under-/Overvoltage	-	-			+	+	
32 Directional Power	-				+	+	
46 Current Unbalance	-						
49 Equipment Thermal Monitoring	•		+		•	•	
50FO Flashover Protection	f	f			f	f	
50 (N,G) Overcurrent (Neutral, Ground)	-	-	•	-	-	•	
50P Phase Overcurrent, 50Q Negative- Sequence Overcurrent	•	•	•	•	•	•	
51 (N,G) Time Overcurrent (Neutral, Ground)	•	•	•	•	•	•	
51P Phase Time Overcurrent	•	•	•	-	•	•	
51Q Negative-Sequence Time Overcurrent	•	•	•	•	•	•	
67 (P,G,Q) Directional Overcurrent (Phase, Ground, Negative Sequence)	•						
81 Under-/Overfrequency	•	•			+	+	
81R Rate-of-Change of Frequency	f						
87 Current Differential	•	•	•	•	•	•	
REF Restricted Earth Fault	•	•	•	+	+	•	

Instrumentation and Control	SEL-487E	SEL-387E	SEL-387	SEL-387A	SEL-787-2X/-21/-2E	SEL-787-3E/-3S/-4X	SEL-2414
SELogic® Control Equations	•	•	-	-	-	•	•
Voltage Check on Closing	f	f			f	f	
Transformer Cooling Fan Control	f				f	f	•
On-Load Tap Changer Control							+
Nonvolatile Latch Control Switches	•	•	-	-	•	•	•
SELogic Remote Control Switches	•	•	•	•	•	•	•
SELogic Local Control Switches	•	-	•	•	•	•	•
Display Points	•	•	•	•	•	•	•
Multiple Settings Groups	•	•	-	-	•	•	
Substation Battery Monitor	•	•	-	-	+	+	f
Breaker Wear Monitor	-	-	-	-	•	•	
Event Report (Multicycle Data)	-	-	-	-	•	•	•
Sequential Events Recorder	•	•	•	•	•	•	•
Instantaneous and Demand Meter	-	-	-	-	•	•	•
Load and Temperature Profile Report	-				•	•	•
Custom Recorder (Up to an Hour)							•
RTD (Resistance Temperature Detector) Inputs					+	+	+
Built-In Web Server	•	+			+	+	
Software-Invertible Polarities	-						
IEC 60255-Compliant Thermal Model	•						
IEEE C37.118 Synchrophasors	•				•	•	
IEC 61850	+	+			+	+	+
IEC 61850-9-2 Sampled Values Technology	+						
IEC 61869-9 Sampled Values	+						
Simple Network Time Protocol (SNTP)	•				+	+	•
Parallel Redundancy Protocol (PRP)	•				+	+	•
IEEE 1588 Precision Time Protocol Version 2 (PTPv2)	+				+	+	•
EtherNet/IP					+	+	
Time-Domain Link (TiDL) Technology	+						
Through-Fault Monitor	-	•	+	•	•	•	•
Thermal Model/SEL-2600 RTD Module Communications	•		+	•	+	+	•

<sup>■</sup> Standard feature + Model option

 ${\it f}$  May be created using relay elements, device word bits, analog quantities, and timers

## **Bus Protection**

Applications	SEL-487B	SEL-487E	SEL-787Z
Breaker Failure Protection	•	•	-
Bus Differential	•		•
Transformer and Machine Current Differential			
High-Impedance Bus Differential			•
Low-Impedance Bus Differential	•		
Three-Phase Current Inputs	7/10/21‡	6	4
Three-Phase Voltage Inputs	1	2	3

#### Protection

27/59 Under-/Overvoltage	•	•	•
46 Current Unbalance	f	•	
47 Voltage Unbalance		f	
50 (N,G) Overcurrent (Neutral, Ground)		•	•
50P Phase Overcurrent	•	•	•
50Q Negative-Sequence Overcurrent		•	•
51 (N,G) Time Overcurrent (Neutral, Ground)			•
51P Phase Time Overcurrent	•	•	•
51Q Negative-Sequence Time Overcurrent			•
87 Current Differential	•		
87Z High-Impedance Differential			•
Single-Pole Trip/Close	•		
Three-Phase Differential Bus Zones	2/3/6 <sup>‡</sup>	1 or 2+	1
Check Zones	3		

Instrumentation and Control	SEL-487B	SEL-487E	SEL-787Z
79 Automatic Reclosing	f	+	
Dynamic Zone Selection	•	•	
SELogic Control Equations	•	•	•
Nonvolatile Latch Control Switches	•	•	•
SELogic Remote/Local Control Switches	•	•	•
Display Points	•	•	•
Multiple Settings Groups	•	•	•
Substation Battery Monitor	•	•	
Breaker Wear Monitor		•	
Event Report (Multicycle Data)	•	•	•
Sequential Events Recorder	•	•	•
Instantaneous Meter	•	•	•
Demand Meter		•	
Through-Fault Monitor		•	
Software-Invertible Polarities		•	
IEC 60255-Compliant Thermal Model		•	
IEEE C37.118 Synchrophasors		•	
Synchrophasor Real-Time Control		•	
IEC 61850	+	+	+
IEC 61850-9-2 Sampled Values Technology	+	+	
IEC 61869-9 Sampled Values	+	+	
Built-In Web Server	•	•	+
Simple Network Time Protocol (SNTP)	•	•	+
MIRRORED BITS® Communications	•	•	•
Parallel Redundancy Protocol (PRP)	•	•	+
IEEE 1588 Precision Time Protocol Version 2 (PTPv2)	+	+	+
Time-Domain Link (TiDL) Technology	+	+	

#### Miscellaneous Features

Connectorized® (Quick Disconnect) Available	+	+	
Connectorized (Quick Disconnect) Available	т -	т	

■ Standard feature + Model option \*1/2/3 relay application  ${\it f}$  May be created using settings

# **Breaker Failure and Capacitor Bank Protection**

Applications	SEL-352	SEL-451	SEL-487B	SEL-487V
Breaker Failure Protection, Number of Three- Phase Breakers	1	2	7	1
Bus Differential			•	
Shunt Capacitor Bank Protection		f		•
Underfrequency Load Shedding		f		f
Undervoltage Load Shedding	f	f	f	f

#### Protection

25 Synchronism Check	•	•		
27/59 Under-/Overvoltage	•	•	•	•
32/37 Power Elements	•	•	f	•
46 Current Unbalance	•	f	f	•
47 Voltage Unbalance		f		f
49 Equipment Thermal Monitoring	+	•		f
50FO Flashover Protection	•	•		•
50 (N,G) Overcurrent (Neutral, Ground)	•	•		•
50P Phase Overcurrent	•	•	•	•
50Q Negative-Sequence Time Overcurrent		•		•
51 (N,G) Time Overcurrent (Neutral, Ground)		•	f	•
51P Phase Time Overcurrent		•	•	•
51Q Negative-Sequence Time Overcurrent		•		•
60 (N,P) Current Unbalance (Neutral, Phase)				•
67 Directional Overcurrent		•		•
81 Under-/Overfrequency		•		•
81R Rate-of-Change of Frequency				•
87 Current Differential			•	
87V Voltage Differential	•	f		•
Single-Pole Trip/Close	-		•	

Instrumentation and Control	SEL-352	SEL-451	SEL-487B	SEL-487V
Open-Pole Detection		-	f	•
Point-on-Wave (POW) Breaker Control				
79 Automatic Reclosing	f	-	f	f
SELOGIC Control Equations	•	-	•	•
Voltage Check on Closing		-		
Nonvolatile Latch Control Switches	•	•	•	•
SELogic Remote/Local Control Switches	•	•	•	•
Display Points	•	•	•	•
Multiple Settings Groups	-	-	•	•
Substation Battery Monitor	+	-	•	•
Breaker Wear Monitor	+	-		•
Voltage Sag, Swell, and Interruption (VSSI) Recording		•		•
Event Report (Multicycle Data)	•	•	•	
Sequential Events Recorder	•	-	•	•
Instantaneous Meter	•	•	•	•
Demand Meter		•		•
Harmonic Metering				•
Software-Invertible Polarities		•		
IEC 60255-Compliant Thermal Model		•		
IEEE C37.118 Synchrophasors		-		•
IEC 61850		+	+	+
IEC 61850-9-2 Sampled Values Technology		+	+	
IEC 61869-9 Sampled Values		+	+	
Built-In Web Server		-	•	
Simple Network Time Protocol (SNTP)		•	•	
Parallel Redundancy Protocol (PRP)		•	•	
IEEE 1588 Precision Time Protocol Version 2 (PTPv2)		+	+	
Time-Domain Link (TiDL) Technology		+	+	
SEL-2600 RTD Module Communications	+	-		•

#### Miscellaneous Features

Connectorized (Quick Disconnect) Available	+	+	+	+
Synchrophasor Real-Time Control				•

■ Standard feature + Model option

 ${\it f}$  May be created using relay elements and timers



# Distribution Protection and Control

selinc.com/products/categories/protective-relays | selinc.com/products/categories/controls

The complex demands of distributed generation, renewable resources, and an evolving customer base present challenges to distribution systems everywhere. From protection fundamentals to advanced automation, SEL offers the most reliable and efficient solutions for every section of a utility-, industrial-, or commercialscale distribution system.

**Applications** 

- Feeder protection
- Transformer protection
- Busbar protection
- Recloser control and protection
- Digital secondary systems
- Arc-flash protection
- Arc Sense<sup>™</sup> technology (AST) high-impedance fault detection
- Microgrid control systems (POWERMAX®)
- Distributed generation
- Power quality
- Distribution automation
- Substation automation



#### **Customer Story**

Mitigating Wildfire Risk in Southern California

selinc.com/highlights/fcp

#### **Videos**


SEL-651R—A Better Way to Connect DERs video.selinc.com/detail/video/ 6084720804001

Simplify and Improve Voltage Regulation in Any Distribution System

video.selinc.com/detail/videos/distributioncontrol/video/1827062609235342126

#### **Example System Diagram**

Combine SEL distribution protection and control products with other SEL automation, monitoring, and wireless communications products for a comprehensive solution.



#### Webinars

Wildfire Mitigation—SEL Solutions for Transmission and Distribution Systems selinc.com/events/on-demand-webinar/ 139282

The Next Evolution in FLISR Simplicity: Automatic Configuration With GIS Data selinc.com/events/on-demand-webinar/ 138534

Improving Voltage Regulation in Systems With DERs

selinc.com/events/on-demand-webinar/138448

SEL Capacitor Bank Controls: More Than Just an On/Off Switch

selinc.com/events/on-demand-webinar/139182

#### **Technical Papers**

Improving Distribution System Reliability With High-Density Coordination and Automatic System Restoration selinc.com/api/download/137363

Using Existing Distribution Protection and Control Capabilities for Integration of Distributed Energy Resources selinc.com/api/download/140366

A New Ground Fault Detection Method in Three-Wire Distribution Systems to Reduce Fire Hazards

selinc.com/api/download/140365

Detecting and Isolating Falling Conductors in Midair—First Field Implementation on Double-Phase Distribution Circuits

selinc.com/api/download/blt40d1b00cc2565c3c

#### White Papers


Wildfire Mitigation: Detecting and Isolating Falling Conductors in Midair Using 900 MHz Private LTE at Protection Speeds selinc.com/api/download/135957

Fire Mitigation for Distribution selinc.com/api/download/126445

Wireless Current Sensing for Improved Distribution Capacitor Bank Control selinc.com/api/download/130665

Securing the "Last Foot" in Distribution Automation

selinc.com/api/download/136842





# **SEL-851 Feeder Protection** Relay

A compact relay for utility and industrial applications that provides overcurrent, voltage, and arc-flash protection as well as versatile communications.



## **SEL-751 Feeder Protection Relay**

Ideal for industrial and utility feeder protection, offering an intuitive color touchscreen, fast and secure arc-flash detection, flexible I/O, and advanced communications.



# SEL-451 Protection, Automation, and Bay Control System

Flexible overcurrent protection with complete substation bay control.



#### **SEL-351 Protection System**

Transmission or distribution overcurrent protection, monitoring, and control.



# **SEL-351A Protection System**

An economical solution for distribution feeder protection.



#### **SEL-351S Protection System**

Comprehensive feeder and overcurrent protection perfect for industrial and utility feeder applications.



#### **SEL Wireless Protection System**

SEL-FT50 Fault Transmitter SEL-RP50 Fault Repeater SEL-FR12 Fault Receiver

Enhance distribution protection by enabling relays to block reclosing for underground faults, by enabling fast bus tripping, or by coordinating highdensity recloser trip blocking.

Applications	SEL-451	SEL-351	SEL-351A	SEL-351S	SEL-851	SEL-751	SEL-751A
Distribution Feeder Protection	-	-	-	-	•	•	•
Breaker Failure (BF) Protection	-	-	f	-	•	•	•
Generator Intertie Protection	•	•	•	•		+	+
Synchronism Check (25)	•	•	•	•		+	+
Underfrequency Load Shedding	f	•	•	•	+	•	•
Undervoltage Load Shedding	f	•	•	•	+	+	+

		on

27/59 Under-/Overvoltage	•	•	•	+	+	+	+
32 Directional Power Elements	•	+		+	+	+	+
49 IEC Line/Cable Thermal Overload	•					•	
50 (P,N,G,Q) Overcurrent Element (Phase, Neutral, Ground, Negative Sequence)		•	•	•	•	•	•
51 (P,N,G,Q) Time Overcurrent Element (Phase, Neutral, Ground, Negative Sequence)	•	•	•		-	•	•
67 (P,N,Q) Directional Overcurrent (Phase, Neutral, Negative Sequence)		•	•	•		+	
78VS Vector Shift						+	
81 Over-/Underfrequency	•	-	-	•	+	-	+
Separate Neutral Overcurrent	•	•	•	•	-	•	•
Load Encroachment Supervision	•	•	•	•		+	
Low-Energy Analog (LEA) Voltage Inputs	+					+	
Directional Sensitive Earth Fault Protection		+	+	+		+	
Pilot Protection Logic	•	•		•			
81R Rate-of-Change of Frequency (df/dt)	•	•	•	•		+	+
81RF Fast Rate-of-Change of Frequency	f					+	+
Harmonic Blocking	-	•	+	•	-	-	
Arc Sense <sup>™</sup> Technology (AST) High-Impedance Fault Detection	+					+	
Arc-Flash Detection					+	+	+
Phantom Phase Voltage		•	•	•			
Current/Voltage Channels	6/6	4/4	4/4	4/4	4/0 4/3 <sup>+</sup>	4/3 4/5 <sup>+</sup>	4/0 4/5 <sup>+</sup>
Complete Two-Breaker Control	•						

Instrumentation and Control	SEL-451	SEL-351	SEL-351A	SEL-351S	SEL-851	SEL-751	SEL-751A
79 Automatic Reclosing		•	•	•	•	+	+
Fault Locating	•	•	•	•		+	
SELogic® Control Equations With Remote Control Switches	•	•	•	•	•	•	•
SELogic Counters	•				•	•	-
Voltage Check on Closing	-	•	•	•		+	+
SELogic Nonvolatile Latch	•	•		•	•	•	•
Nonvolatile Local Control Switches	•	•	+	•	•	•	-
Substation Battery Monitor	•	•	•	•		+	+
Breaker/Recloser Wear Monitor	•	•	•	•		•	-
Trip Coil Monitor	f	f	f	f		f	f
Voltage Sag, Swell, and Interruption (VSSI)	•	+		+			
Load/Signal Profile Recorder	•	+		+	•	•	•
Sequential Events Recorder	•	•	•	•	•	•	•
Software-Invertible Polarities	•						
IEC 60255-Compliant Thermal Model	•						
DNP3 Level 2 Outstation	•	•	•	•	+	+	+
Parallel Redundancy Protocol (PRP)	+	•		•		+	
IEEE 1588 Precision Time Protocol Version 2 (PTPv2)	+					+	
Time-Domain Link (TiDL®) Technology	+						
IEEE C37.118 Synchrophasors	•	•	•	•		•	-
Bay Control	•					+	
Ethernet	+	•	•	•	•	+	+
EtherNet/IP						+	
Built-In Web Server	-				•	•	
IEC 61850	+	+	+	+	+	+	+
IEC 61850 Edition 2	+				+	+	
IEC 61850-9-2 Sampled Values Technology	+						
Firmware Option With MIRRORED BITS® Communications Available	•	•		•	•	•	•
Simple Network Time Protocol (SNTP)	•	•	•	•	•	+	+
Harmonic Metering		•	•	•	•		
RMS Metering	•	•	•	•	•	•	•

<sup>■</sup> Standard feature + Model option f May be created using settings



#### SEL-651R Advanced **Recloser Control**

The SEL-651R provides Automatic Network Reconfiguration and threeand single-phase tripping. It can be used at distributed energy resource (DER) interconnections, for detecting down conductors, and in other distribution automation applications. It is compatible with popular reclosers.



#### SEL-651RA Recloser Control

The SEL-651RA is a powerful, costeffective, and flexible recloser control for 14-pin reclosers used in threephase tripping applications. It can be used at DER interconnections, for detecting down conductors, and in other distribution automation applications. It is compatible with popular reclosers.



## SEL-351RS Kestrel® Single-**Phase Recloser Control**

The SEL-351RS provides integrated logic and communications and comprehensive protection for single-phase applications.



# SEL-734B Advanced Monitoring and Control System

The SEL-734B includes low-energy analog inputs and provides advanced monitoring and control capabilities for applications such as capacitor bank control and feeder monitoring.



## SEL-734W and LINAM® WCS **Capacitor Bank Control and** Wireless Current Sensor

This solution is a quick and simple way to provide accurate current, reactive power (VAR), or power factor control for capacitor bank installations and improve power quality.



# SEL-2431 Voltage **Regulator Control**

The SEL-2431 optimizes system voltages and facilitates DER integration by using directional voltage profiles and detailed tap change event reports.

Applications	SEL-351RS Kestrel®	SEL-651R	SEL-651RA	Instru
Distribution Feeder Protection	•	•		79 Auto
Breaker Failure Protection	f	f	f	Fault Lo
Generator Intertie Protection		•	•	SELogi
Recloser Control	•		•	SELogi
Synchronism Check		•	+	Voltage
Underfrequency Load Shedding	-		•	SELogi
Undervoltage Load Shedding	•	•	•	Nonvol
Protection				Display
25 (G,T) Generator/Intertie Synchronism Check		•	•	Trip Co
27/59 Under-/Overvoltage	•	•	•	IEEE 15
27I Inverse-Time Undervoltage		+		Ethern
32 Directional Power Elements	•		+	IEC 618
50 (P,N,G,Q) Overcurrent Element (Phase, Neutral, Ground, Negative Sequence)	•	•	•	Simple
51 (P,N,G,Q) Time Overcurrent Element (Phase, Neutral, Ground, Negative Sequence)	•	•	•	
51V/C Voltage-Restrained/Controlled Time Overcurrent		+		
59I Inverse-Time Overvoltage		+		
67 (P,N,Q) Directional Overcurrent (Phase, Neutral, Negative Sequence)		•	•	
78VS Vector Shift		•	•	Powe
81 Over-/Underfrequency	•	•	•	Voltage
81R Rate-of-Change of Frequency (df/dt)	•	•	•	(VSSI)
81RF Fast Rate-of-Change of Frequency (ROCOF)		•	•	Load/S
81W Frequency Window		+		Seque
Separate Neutral Overcurrent		•	•	DNP3 I
Load-Encroachment Supervision		•	•	IEEE C
Low-Energy Analog (LEA) Voltage Inputs		+	+	Harmo
Directional Sensitive Earth Fault Protection		•	•	RMS M
Pilot Protection Logic		f	f	■ Ctop
Harmonic Blocking	•	•	•	■ Stand <b>‡</b> Excep
Fast Islanding Detection		•	•	
Arc Sense Technology (AST) High-Impedance Fault Detection		+	+	
Phantom Phase Voltage	•	•	•	
Current/Voltage Channels	1/1	4/6	4/1 4/6*	

Instrumentation and Control	SEL-351RS Kestrel®	SEL-651R	SEL-651RA
79 Automatic Reclosing	•	•	-
Fault Locating	•	•	+
SELogic Control Equations With Remote Control Switches	•	•	-
SELogic Counters	•	•	-
Voltage Check on Closing	•	•	-
SELogic Nonvolatile Latch	•	•	-
Nonvolatile Local Control Switches	•	•	•
Display Points	•	•	-
Breaker/Recloser Wear Monitor	•	•	-
Trip Coil Monitor	f	f	f
IEEE 1547-2018		•	-
Ethernet	•	•	•
IEC 61850	+	+	+
Simple Time Network Protocol (SNTP)	•	•	•

Power Quality	SEL-351RS Kestrel®	SEL-651R	SEL-651RA	SEL-734B	SEL-734W	SEL-2431
Voltage Sag, Swell, and Interruption (VSSI)	•	•	•	•	•	f
Load/Signal Profile Recorder	•	•	•	•	•	•
Sequential Events Recorder	•	•		•		•
DNP3 Level 2 Outstation	•	•	•	•	•	•
IEEE C37.118 Synchrophasors	•	•	•	•	‡	•
Harmonic Metering	•	•			•	•
RMS Metering	•	•	•	•	•	•

- ndard feature ullet Model option  $m{f}$  May be created using settings
- ept phase currents



# Fault Indicators, Sensors, and CTs

selinc.com/products/categories/fault-locating/#fault-indicators | selinc.com/products/categories/measurement-streaming

SEL fault indicators and sensors improve reliability by indicating the fault path to speed up the fault-locating time and reduce the outage duration. Suitable for overhead and underground installations, SEL fault indicators and sensors work in a wide range of applications—from overcurrent fault detection to enhancing system protection.

# **Applications**

- Traditional fault locating for line crews
- Wireless fault locating
- Distribution protection and control enhancement


#### **Videos**

How to Install the AR360 AutoRANGER® Fault Indicator

video.selinc.com/detail/videos/ fault-indicators/video/2925549374001

Wireless Protection Communications— Innovating to Improve Reliability selinc.com/highlights/aes-ohio





## White Papers

Wireless Current Sensing for Improved Distribution Capacitor Bank Control

selinc.com/api/download/130665

Fire Mitigation for Distribution selinc.com/api/download/126445

#### Wireless Fault Indication

Advanced fault detection solutions optimize distribution reliability.

## **Technical Papers**

Emerging Communications and Sensor Technologies That Advance Distribution Automation

selinc.com/api/download/124511

Fast Wind Farm Restoration Using Wireless Fault Sensors to Identify Faulted Segments selinc.com/api/download/130379


#### Webinars


Introducing the LINAM® UGFI Underground Fault Indicator selinc.com/events/on-demand-webinar/ 140106

A Better Test Point Voltage Sensor for Switchgear

selinc.com/events/on-demand-webinar/ 135858

Enhance Distribution Protection With the SEL Wireless Protection System selinc.com/events/webinar/133828





#### Overhead



# SEL-FLT and SEL-FLR Fault and Load Transmitter and **Receiver System**

Improve overall distribution system reliability with the SEL-FLT and SEL-FLR system, which accurately indicates faults and monitors load. Speed up deployment in pole-mount applications with the system's enclosure.



# SEL-AR360 and SEL-AR **Overhead AutoRANGER Fault Indicators**

Locate momentary and permanent faults in overhead applications. The SEL-AR360 and SEL-AR automatically adjust their trip thresholds to coordinate with the load current in distribution systems.



## **SEL-ER Overhead Electrostatic Reset Fault Indicator**

Provide maintenance-free fault indication with a battery-free design and automatic voltage reset.



#### **SEL Wireless Protection System**

Enhance distribution protection by enabling relays to block reclosing for underground faults, by enabling fast bus tripping, or by coordinating high-density recloser trip blocking.



## **SEL-CRD Overhead Current Reset Fault Indicator**

Reduce fault detection time with the SEL-CRD, featuring load-currentpowered functionality, a 1 ms response time, and single-hot-stick installation.



## **SEL-MR Manual Reset Fault** Indicator

Troubleshoot overhead and underground applications up to 38 kV with this portable, fault-powered manual reset fault indicator.

# Underground



# LINAM UGFI Underground Fault Indicator NEW

Reduce outage durations and improve reliability with the LINAM UGFI, featuring line-powered functionality, adjacent phase immunity, and performance that exceeds IEEE 495 standards.



# RadioRANGER® Underground Wireless Fault Indication System

Reduce the need to access vaults or open pad-mounted enclosures to retrieve the fault indicator status. Decrease fault-locating time and improve safety.



# SEL-TPR Underground Test Point Reset Fault Indicator

Easily install the SEL-TPR on most brands of 200 A or 600 A elbows with capacitive test points. It is ideal for pad-mounted transformer and switchgear applications.



# SEL-3780 Test Point Voltage Sensor

Detect system voltage loss on distribution elbows with capacitive test points. The SEL-3780 is part of an economical solution for source transfer schemes.



# SEL-PILC Underground Paper-Insulated Lead-Covered Cable Fault Indicator

Apply the SEL-PILC on paperinsulated lead-covered cables. It features a rugged design and can be submerged in up to 15 feet of water.



# SEL-CT Split-Core Current Transformers

Economically add SEL CTs to existing wiring and electrical equipment without interrupting service.



# **Metering and Power Monitoring**

selinc.com/solutions/metering-solutions | selinc.com/services/protection-control/metering-demand-management

SEL metering products help operators identify power quality issues and improve energy usage in generation, interchange, transmission, distribution, industrial, and commercial applications.

# **Applications**

- Power quality monitoring and troubleshooting
- Usage reporting and billing management system integration
- Load profiling and monitoring
- Continuous waveform streaming and recording

# White Paper

Achieve Accurate Metering in Modern Nonsinusoidal Power System Conditions selinc.com/api/download/123140

#### Webinars

134511

Improve Your Power System Visibility selinc.com/events/on-demand-webinar/ 140676

Never Miss an Event: Introducing the SEL-T35 Time-Domain Power Monitor selinc.com/events/on-demand-webinar/ 139220

Solutions for Optimizing Energy Metering and Demand Management selinc.com/events/on-demand-webinar/




#### **Customer Stories**

SEL Meter Helps Data Center Supply High-Quality, Uninterrupted Power selinc.com/solutions/success-stories/ Vantage-Data

Minimize the Cost of Harmonic Mitigation With Continuous Waveform Recording selinc.com/CWStestimonial

#### **Example System Diagram**

Combine the SEL-735 Power Quality and Revenue Meter with other SEL devices and software for a comprehensive metering data management solution.





# SEL-735 Power Quality and Revenue Meter

SEL meters offer bidirectional, full four-quadrant, and high-accuracy energy metering as well as precise and reliable power quality measurements.

Capture every disturbance in your system with optional continuous waveform streaming at 3 ksps to SEL Synchrowave® software. Multiple mounting and enclosure options and accessories are available; visit selinc.com/products/735.

#### **SEL Synchrowave Software**

Automate data retrieval, quickly visualize data, and create custom reports with the enterprise data collection and reporting software bundle. Bundling software simplifies ordering and license management, eliminates base license fees, and allows incremental license purchases. View software bundling options below.

# **Software Bundling Options**

ACSELERATOR TEAM® SEL-5045 Software'	Meter Data Option	Power Quality Option	Energy and Power Monitoring Option
Event and SER collection		•	•
LDP and VSSI collection	•		•

SEL-5705 Synchrowave Reports	Meter Data Reports	<b>Power Quality Reports</b>	<b>Power Quality Reports</b>
Device Overview	•	•	•
SER	•	•	•
LDP	•	•	•
VSSI	•	•	•
Signals or WAGES	•	•	•
IEEE 519 Compliance Report		•	•

SEL-5703 Synchrowave Monitoring	Trending and Archiving Package	Power Monitoring Package
Phasor Measurement Unit (PMU)	•	•
Continuous Waveform Receiving	•	•
Time-Series Historian	•	•
Calculations	•	•
Software PMU	•	•
Virtual Metering	•	•
Visualization	•	•
Data Export	•	•
Notifications/Alarms		•
Oscillation Detection		•
Disturbance Detection		•
PT Failure Detection		•
Threshold Monitoring		

# Virtual Metering Expands **Power Monitoring Capabilities**


The Virtual Metering applications in SEL Synchrowave software allows users to generate signals similar to metering analogs using timestamped signal data as a source. The software automatically converts instantaneous waveforms sampled at 3 or 14.4 ksps into phasorbased quantities. The application calculates current, voltage, power, frequency, harmonics, symmetrical components, and power quality measurements, providing valuable reporting and monitoring data.

## **Power Management**

SEL Synchrowave software supports event detection and expedites rootcause analysis using streaming data from the SEL-735 meter and SEL-T35 power monitor.

#### **Related Material**

Capture every disturbance with continuous waveform recording. selinc.com/api/download/138703



# **Metering and Power Monitoring Applications**

		SEL-735		SEL-T35
Application	Basic	Intermediate	Advanced	All Models
Revenue Metering	Class 0.1	Class 0.1	Class 0.1	-
SCADA Metering	Yes	Yes	Yes	-
Onboard Storage	128 MB	256 MB	1 GB	-
Event Detection	Basic	Advanced	Advanced	Advanced, virtual metering
Waveform Recording	16 samples/cycle	128 samples/cycle	512 samples/cycle	Virtual metering, 14.4 ksps
SELogic® Control Equations	Yes	Yes	Yes	_
Harmonic Order	15th	63rd	63rd	Virtual metering, 100th
PQ Monitoring	-	Yes	Yes	Virtual metering
Subsynchronous Oscillation Detection	Option with Synchrowave Reports	Option with Synchrowave Reports	Option with Synchrowave Reports	Included
IEEE 519 Compliance Monitoring	_	-	Option with Synchrowave Reports	Included
Synchrowave Software License	Optional	Optional	Optional	Included



# SEL-T35 Time-Domain Power Monitor NEW


The SEL-T35 streams high-precision ac and dc voltage and current measurements at 14.4 kilosamples per second (ksps) to the included Synchrowave software for wide-area, real-time data analysis.

Energy packets calculated every millisecond provide energy measurements independent of frequency. An integrated ridethrough pack ensures that you never miss a disturbance during short-duration outages.

#### **SEL Synchrowave Software**

Calculate and monitor power quality values in real time using high-rate streaming data.

The Virtual Metering application in Synchrowave software enables system-wide power quality calculations, including harmonics, subsynchronous oscillations, rapid voltage changes, and flicker. Synchrowave can use the calculated harmonic values in IEEE 519 compliance reports.





# **Automation and Computing Platforms**

selinc.com/products/categories/automation-computing

Increase system reliability and operation efficiency using SEL automation and computing platforms, which offer scalable and modular solutions for the most demanding utility and industrial applications. SEL automation solutions allow you to implement a broad set of functionalities or choose a subset and add more capabilities over time.

# **Applications**

- Remote terminal unit (RTU)
- Digital fault recording systems
- Network device auditing
- Power management and control systems (POWERMAX®)
- Distributed energy resource (DER) management (SEL Real-Time Automation Controller [RTAC] Grid Connect)
- Automatic fault location, isolation, and service restoration
- Bay control
- Phasor measurement unit
- Continuous waveform recording and streaming
- Embedded computing systems



#### **Customer Stories**

Pend Oreille Utility Benefits From Innovative RTU Upgrade Strategy selinc.com/highlights/pud


A System of Robust Reliability for the Water and Wastewater Industry selinc.com/solutions/success-stories/brunswick

#### **Automation News**

selinc.com/products/automation/news

#### **Example System Diagram**

Combine SEL automation and computing platforms with SEL protective relays and software for a comprehensive solution.



#### Webinars

Innovating DFR Solutions—Continuous Oscillography, Asset Monitoring, and More

selinc.com/events/webinar/138498

RTAC and Axion® Advancements for RTU and Substation Gateway Applications selinc.com/events/on-demand-webinar/ 137925

Managing DERs With RTAC Grid Connect selinc.com/events/on-demand-webinar/

Software-Based Password Rotation With DMA Credential Management selinc.com/events/on-demand-webinar/ 137643

#### **Technical Papers**

Simplifying Compliance: An Integrated Approach to Meeting NERC PRC-002 and PRC-005 Requirements selinc.com/api/download/130034

New Advancements in Solar Grid Controllers selinc.com/api/download/130047

Wind Farm Volt/VAR Control Using a Real-Time Automation Controller selinc.com/api/download/99167

#### White Paper

Using Defense in Depth to Safely Present SCADA Data for Read-Only and Corporate Reporting selinc.com/api/download/120437

#### **Related Materials**

SEL Advanced Digital Fault Recorder (DFR) Solutions selinc.com/api/download/122510

POWERMAX Solutions selinc.com/api/download/106293

Capture Every Disturbance With Continuous Waveform Recording selinc.com/api/download/138703



#### **SEL-3350 Computing Platform**

The SEL-3350 is a cost-effective model ideal for applications that require midlevel I/O and computation. It can be deployed as an RTAC, an industrial computer running a Microsoft Windows or Linux OS, or a Blueframe® application platform.



#### **SEL-3355 Computing Platform**

The SEL-3355 is a server-class computing platform built to withstand harsh environments in utility substations and industrial control and automation systems. It can be deployed as an industrial computer running a Microsoft Windows or Linux OS or as a Blueframe application platform.



# SEL-3360S/3360E Compact Computing Platform

These models match the performance, ruggedness, and configuration flexibility of the SEL-3355 and are ideal for surface- or panel-mount applications. They can be deployed as industrial computers running a Microsoft Windows or Linux OS or as Blueframe application platforms.



#### SEL-3505/3505-3 RTAC

These RTACs offer powerful automation, reporting, and control for low-voltage, limited-space applications.



#### SEL-3555 RTAC

The SEL-3555 provides powerful processing for large-scale automation projects.



#### SEL-3560E/3560S RTAC

These RTACs offer powerful processing for large-scale automation projects in a compact form factor.





#### SEL-2240 Axion®

The Axion is a ruggedized, high I/O count, modular platform that supports multiple utility and industrial applications on a single device. Common applications include bay control, SCADA data concentration, digital fault recording, microgrid monitoring and control, power quality monitoring, and deployment as an RTU.



## SEL-2411 Programmable **Automation Controller**

The SEL-2411 provides flexible I/O for automatic control, SCADA, station integration, remote monitoring, and plant control systems.

#### **RTAC Automation Software**

#### ACSELERATOR RTAC® SEL-5033 Software

Included with an SEL RTAC purchase, AcSELERATOR RTAC is an intuitive, easy-touse application designed to configure the SEL RTAC family of products, including the Axion.

#### **RTAC HMI Builder**

Included with an SEL RTAC purchase, AcSELERATOR Diagram Builder™ SEL-5035 Software enables the creation and management of HMI visualization projects for the RTACs in your system.

#### ACSELERATOR® Bay Screen Builder SEL-5036 Software

Included with acSELerator QuickSet® SEL-5030 Software and acSELerator RTAC, Bay Screen Builder works with QuickSet and AcSELERATOR RTAC to enable the custom creation of bay screens for SEL devices with touchscreen displays.

#### **RTAC Extensions**

Simplify automation programming with RTAC extensions. These preconfigured logic suites support automation solutions such as digital fault recording, DER monitoring, and IEC 61850 device monitoring.

#### **SEL Blueframe**

#### **SEL Blueframe Application Platform**

Scalable and flexible, SEL Blueframe provides a secure operational technology (OT) platform for installing applications and for managing and exchanging data between supported applications.

## Distribution Management System (DMS) Application Suite

The DMS suite includes the Fault Location, Isolation, and Service Restoration (FLISR) application package, which reduces customer outages, improves reliability metrics, and provides rapid fault detection and system restoration.

#### Data Management and Automation (DMA) Application Suite

DMA applications automatically collect, store, and manage device-specific information to simplify day-to-day management of a system of devices and to support compliance.



## **SEL-2411P Pump Automation** Controller

The SEL-2411P is a standalone, SCADA-ready system for control and monitoring of water and wastewater pump applications.



#### **SEL-2414 Transformer Automation Controller**

Control load tap changers (LTCs) and transformer cooling stages with one device. The SEL-2414 offers comprehensive voltage regulation, transformer monitoring, and flexible I/O options to fit your application requirements.



## SEL-2440 Discrete Programmable **Automation Controller (DPAC)**

The SEL-2440 offers utility-grade I/O, powerful processing, flexible communications, and microsecond timing.

Applications	SEL-3355	SEL-3360E	SEL-3360S	SEL-3350	SEL-3555	SEL-3560E	SEL-3560S	SEL-3530-4	SEL-2240	SEL-3505/3505-3	SEL-3533	SEL-2411	SEL-2411P	SEL-2414	SEL-2440
Collect, Scale Meter Data	+/#	+/#	+/#	+/#							-			•	
Condition Monitoring	#	#	#	•							-			•	
Transformer Load Tap Changer Control														+	
IED Report/Event Collection	+	+	+	•		-	•			•	-				
Digital Fault Recording				+		-	•								
Collect Targets, Contact Input Status, Fault Location	#	#	#	+		-	•			•	-				
Enable Fiber-Optic Links	+	+		+	+	+			•	•	-	•	•	•	•
Control Through IED Outputs				•		-	•		•	•	•	•	•	•	•
IRIG-B Client Time Synchronization	•	•	•	•		-	•		•	•	+	•	•	•	•
IRIG-B Server Time Distribution	+	+		•	•	•	•	•	•	•	+				
IRIG-B Time Distribution and Network Time Protocol (NTP) Conversion	+	+		•	•	•	•	•	•	•	+				
Transparent "Port Switch"	#	#	#	+	•	•	•	•	•	•	•	•	•	•	•
Windows/Linux Applications in Harsh Environments	+/#	+/#	+/#	+/#											
Running Multiple Applications Simultaneously	-	-	•	•											
Installing Third-Party Software	+	+	+	+											
Security Appliance to Help Satisfy NERC CIP Requirements	#	#	#	+/#	•	•	•	•	•	•	-				
Network Monitoring and Intrusion Detection	#	#	#	#	+										
Virtualization Server	+/#	+/#	+/#												
Engineering Access Point	+/#	+/#	+/#	+/#	-	•	•	-	•	•	-				
Video Surveillance Control and Archiving/Physical Security Monitoring and Notification	#	#	#	#											
Concentrate Data for Distributed Control System (DCS)				+	-	-	•	-	•	-	-				
Concentrate Data for SCADA Master or Remote Terminal Unit (RTU)	#	#	#	+	-	-	•	-	•	-	-				
Remote Third-Party HMI	#	#	#	+	-	•	•	•	•	-	-				

## Features

Protocol Redundancy (DNP3 and IEC 60870-5-101/104 Server)				+	•	•	•	•	•	•	•				
Primary and Standby LAN Support	+/#	+/#	+/#	+	-	-	•	•	-	-	•	•	•	•	•
Optoisolated Inputs/Programmable Outputs				+	<b>■</b> ¹	<b>■</b> ¹	<b>■</b> ¹	•	+	+	<b>■</b> ¹	+	+	+	+
IEC 61131 Logic Engine				+	-	-	•	•	-	-	•				
Cybersecurity Management	#	#	#	+	-	-	•	•	-	-	•				
Real-Time Operating System				+	-	-	•	•	-	-	•	•	•	•	•
Web-Based HMI	#	#	#	+	+	+	+	+	+		+				
Touchscreen Display	+/#	+/#	+/#	+/#					+			+		+	
LCD												•	•	•	

<sup>■</sup> Standard feature + Model option #Third-party software required ¹Alarm contact only

	SEL-3355	SEL-3360E	SEL-3360S	SEL-3350	SEL-3555	SEL-3560E	SEL-3560S	SEL-3530-4	SEL-2240	SEL-3505/3505-3	SEL-3533	SEL-2411	SEL-2411P	SEL-2414	SEL-2440
Hardware Intel Xeon Quad-Core 64-Bit CPU	<i>σ</i>	<b>σ</b>	<b>σ</b>	S	<b>ω</b>	<b>ω</b>	S	S	S	S	S	S	S	S	ဟ
Intel Atom Quad-Core 64-Bit CPU		_	_		_	_	_								
Power PC Single-Core CPU				_					_						
Maximum Error-Correcting Code (ECC) RAM (GB)	64	64	64	8	64	64	64	1	4	0.5					
Supports Independent Displays With Digital Audio	•		•		•	•	•	·		0.0					
Analog Audio Ports: Line In, Line Out, Microphone															
Front USB Ports				•											
Rear USB Ports															
Front RJ45 Ethernet Ports		_	_	1	_	_	_		+						
Rear Ethernet Ports	2	2	2	4	2	2	2	2	3	2		2	2		2
Fiber-Optic Rear Ethernet Ports				+				+	+	+		+	+		+
Additional Ethernet Ports, Copper RJ45, or Fiber-Optic SFP	8	4		•	8	4		•	•						•
Dedicated Serial Ports	2	2	2		2	2	2								
Configurable Serial Ports				16	6	6		4	4	4/3					
Expansion Serial Ports	24	12		32	18	6		_	7	4/3					
IRIG-B Input	24	12	•	32	10	•							•		
IRIG-B Output	+	+	_	•	+	+	_					_	_	-	_
		T				Т.				•					
19" Rack Mount					•			•				+	+	+	+
Panel Mount	+		_	+	+	_		+	+			+	+	+	+
Wall Mount															
Conduction Cooled Wall Mount		+	+			+	+								
PCI/PCIe Expansion Slots	5	2			3	1									
SSDs (2.5" SATA, 32 GB-7.68 TB Drive Options)	4	2	2	2	4	2	2								
High-Voltage 125–250 Vdc, 120–240 Vac Power Supply	•	-	+	•	-	•	+	•	•			•	-	•	•
Medium-Voltage 48–125 Vdc, 120 Vac Power Supply				•				•				•	•	-	•
Low-Voltage 48 Vdc Power Supply	•	•	+		•	•	+								
Low-Voltage 24–48 Vdc Power Supply				•					+	+		+	+		+
12–24 Vdc Power Supply										•					
12 Vdc Power Supply			•				•								
Secondary Power Supply	+		+		+		+								
Hot-Swappable Power Supplies	•		•	+	•		•								
Alarm Contact, Alarm LED, Watchdog	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
Configurable Universal Control Input				•											
Programmable LEDs	3	3	3	4	3	3	3		2			23	15	23	19
Intel Active Management Technology (AMT) v11.8	•	•	•												
Infineon Trusted Platform Module (TPM) v2.0 (Hardware)	•	-	-	-	•	•	•		-						

<sup>■</sup> Standard feature + Model option

Supported Operating Systems and Hypervisors	SEL-3355	SEL-3360E	SEL-3360S	SEL-3350	SEL-3555	SEL-3560E	SEL-3560S	SEL-3530-4	SEL-2240	SEL-3505/3505-3	SEL-3533	SEL-2411	SEL-2411P	SEL-2414	SEL-2440
SEL Real-Time Automation Controller (RTAC)				+	•	•	•	•	+	•	•				
SEL Blueframe	+	+	+	+											
Linux (RHEL, SUSE, Ubuntu)	<b>‡</b>	‡	‡	‡											
Microsoft Windows IoT Enterprise LTSC	+	+	+	+											
Microsoft Windows Server Standard	+	+	+	+											
Linux KVM	<b>‡</b>	‡	‡	‡											
Microsoft Hyper-V	<b>‡</b>	‡	‡	‡											
VMware ESXi	<b>‡</b>	‡	‡												

# Supported Protocols


Supported Protocols															
SEL ASCII				+	•	•	•	•	٠	•	•				
SEL Fast Messages				+	•	•	•	•	•	•	•				
SEL MIRRORED BITS® Communications				•	•	•	•	•	•	•	•	•	•	•	•
CDC Type II				+	•	•	•	•	•	•	-				
CP 2179				+	•	•	•	•	•	•	-				
DNP3				+	•	•	•	•	•	•	-	+	•	+	+
DNP3 LAN/WAN				+	•	•	•	•	•	•	•	+	•	+	+
EtherCAT® (SEL-2240 Field Bus I/O Only)									•						
EtherNet/IP				+	•	•	•	•	•	•	•				
File Transfer Protocol (FTP)/Secure FTP (SFTP)				+	•	•	•	•	•	•	•	•	•	•	
IEC 60870-5-101				+	•	•	•	•	•	•	•				
IEC 60870-5-103				+	•	•	•	•	•	•	•				
IEC 60870-5-104				+	•	•	•	•	•	•	•				
IEC 61850 GOOSE				+	+	+	+	+	+	+	+	+		+	+
IEC 61850 Manufacturing Message Specification (MMS)				+	+	+	+	+	+	+	+	+		+	+
IEEE C37.118				+	•	•	•	•	•	•	•				
LG 8979				+	•	•	•	•	•	•	•				
Lightweight Directory Access Protocol (LDAP)				+	•	•	•	•	•	•	•				
Modbus RTU				+	•	•	•	•	•	•	•	•	•	•	•
Modbus TCP				+	•	•	•	•	•	•	•	•	•	•	•
MQTT				+	•	•	•	•	•	•	•				
Network Time Protocol (NTP)				+	•	•	•	•	•	•	•				
OPC Unified Architecture (UA)				+	+	+	+		+	+					
Parallel Redundancy Protocol (PRP)	+	+	+	+	•	•	•	•	•	•	•	•	•	•	•
Precision Time Protocol (PTP)				+	•	•	•	•	•	•	•	•		•	•
Secure Shell (SSH)				+			•	•		•	•				
SES-92				+	•		•	•		•	-				
Simple Mail Transfer Protocol (SMTP)/Email Notification				+	•	•	•	•	•	•	•				
Simple Network Management Protocol (SNMP)				+							-				
Simple Network Time Protocol (SNTP)				+			•	•				•	•	•	
Telnet				+			•				-	•	•	•	

lacktriangle Standard feature lacktriangle + Model option lacktriangle Supported for customer installation lacktriangle May be created using settings



# **SEL Network Communications Solutions**

selinc.com/products/categories/networking-communications



## Wide-Area Networks (WANs)


The SEL operational technology (OT) WAN circuit aggregation solution supports a variety of transport technologies, from DS1/E1 to packet transport, and helps preserve the performance characteristics of time-division multiplexing (TDM) for critical applications, regardless of the deployed technology. The SEL ICON® offers a rugged, flexible solution with a 20-year life cycle, extending the network's lifetime and improving its reliability.

#### Local-Area Networks (LANs)

SEL Ethernet switches and security gateways facilitate reliable, predictable, and secure connectivity between different devices for critical applications. Our rugged solutions are optimized for OT networking. They simplify network engineering, improve cybersecurity, ensure dependable performance, and support critical infrastructure with economical devices designed for 20 years of operation.

#### Field-Area Networks (FANs)

The SEL-3031 Serial Radio
Transceiver and SEL-3061 Cellular
Router provide robust wireless
communications for electric utilities
to achieve optimized situational
awareness. Our wireless solutions
can be seamlessly integrated with
SCADA applications, like recloser
controls, capacitor bank controls,
voltage regulator controls, fault
indicators, sensors, and other IEDs.





# **WAN and LAN Networks**

selinc.com/products/categories/networking-communications

SEL devices combine the connectivity, performance, cybersecurity, and ruggedness required for WAN and LAN applications.

#### **Solutions**

- Operational technology (OT) networking:
  - Programmable networks and software-defined networking
  - Managed networks and the Rapid Spanning Tree Protocol (RSTP)
- WAN circuit aggregation
- SONET/T1/E1 multiplexing

# **Applications**

- Teleprotection systems
- Analog leased-line service migration
- IT/OT convergence
- Engineering access
- SCADA and distributed control systems
- Network time synchronization
- IEC 61850 digital secondary systems
- Special protection systems
- Microgrids
- Distributed renewables
- Remedial action schemes
- Facility-related control systems
- NERC CIP
- Land mobile radio (LMR) systems

#### Video

OT Software-Defined Networking: Purpose-Engineered for Critical Infrastructure

video.selinc.com/detail/video/ 1726869976932833649

#### Webinars

Best Practices for Successful IT/OT Network Convergence

selinc.com/events/webinar/128773

Redefining Ethernet Performance With Software-Defined Networking selinc.com/events/webinar/130273

Lower Your Costs With SEL ICON®: Decades of WAN Transport Flexibility selinc.com/events/webinar/140867

Stay TDM or Move to Packet? Do Both With the SEL ICON selinc.com/events/on-demand-webinar/ 138942

Automate SDN Configuration With RTAC and IEC 61850 Files selinc.com/events/on-demandwebinar/137644

# **Technical Papers**

Using Software-Defined Networking to Build Modern, Secure IEC 61850-Based Substation Automation Systems

selinc.com/api/download/130126

**Deterministic Communications for** Protection Applications Over Packet-Based Wide-Area Networks selinc.com/api/download/121072

Taking Full Control of Your Process Bus LAN Using New Ethernet Packet Transport Technologies selinc.com/api/download/119756

#### SDN News

selinc.com/products/sdn/news

#### **ICON News**

selinc.com/products/icon/news



#### **Customer Stories**

Belgium Integrates Offshore Wind Power Into European Grid selinc.com/featured-stories/elia

EPR Modernizes Their Multinational Transmission System selinc.com/highlights/epr-siepacmodernization

**Defending Critical Substation** Communications in Slovenia selinc.com/highlights/eles

Creating a Better Future: Innovative Substation Modernization in the Philippines selinc.com/highlights/davao-light

# White Papers


Software-Defined Networking Changes the Paradigm for Mission-Critical Operational Technology Networks selinc.com/api/download/118416

Leveraging SEL Ecosystem for NERC CIP-015 Compliance selinc.com/api/download/140729

#### **Related Materials**

OT SDN

selinc.com/solutions/ot-sdn



#### **Example System Diagram**

Combine SEL LAN and WAN devices with other SEL protection, automation, and control products for a comprehensive solution.



# **SEL ICON Integrated Communications Optical** Network

The ICON is a WAN multiplexing and circuit aggregation solution optimized for industrial and utility applications. By combining time-division multiplexing (TDM) and Ethernet transport options with a comprehensive range of data interfaces, the ICON makes it easy to migrate legacy network technologies to a packet-based solution.



#### SEL-2731 Ethernet Switch

The SEL-2731 is an OT SDN and Rapid Spanning Tree Protocol (RSTP) managed Ethernet switch that is optimized for OT environments, supporting critical infrastructure applications.



#### SEL-2741 Ethernet Switch

The SEL-2741 is a 24-port, multilayer LAN Ethernet switch that supports deny-by-default, zero-trust OT SDN and RSTP. It is designed to perform reliably in the harshest environments found in critical infrastructure.



## SEL-2740S Software-Defined **Network Switch**

The SEL-2740S is the industry's first field-hardened SDN-enabled switch and improves cybersecurity and Ethernet performance in missioncritical applications.



#### SEL-2742 Ethernet Switch

The SEL-2742 is a 12-port, DIN-rail mount SDN switch for industrial environments. It combines with SEL-5056 Network Management System (NMS) software to simplify network engineering and improve LAN security.



# SEL-2743 Ethernet Switch NEW

The SEL-2743 is an 8-port OT SDN and RSTP managed Ethernet switch. Combining powerful performance, a small form factor, Power over Ethernet Plus (PoE+), and an economical price, it's ideal for OT networks for most industrial and electric utility communications applications.



#### SEL-2744 Ethernet Switch NEW

The SEL-2744 is a 10-port OT SDN and RSTP aggregation Ethernet switch. With two 10 Gbps ports, dual power supplies, and PoE+, it's well suited for IT/OT convergence at electric utilities.



# SEL-3620 Ethernet Security Gateway or SEL-3622 Security Gateway

The gateways each function as a router, VPN endpoint, and firewall device. They can provide secure and proxy user access for serial- and Ethernet-based IEDs.



# SEL-2725 Five-Port **Ethernet Switch**

The SEL-2725 allows you to easily connect devices to Ethernet networks.

Applications	SEL ICON	SEL-3620	SEL-3622	SEL-2725	SEL-2731	SEL-2740S	SEL-2741	SEL-2742	SEL-2743	SEL-2744
SONET and Ethernet WAN	•									
Ethernet LAN	•	•	•	•			•			•
E1 and T1 Transport	•									
Precise Time Distribution	•	•	•		•	•	•	•	-	•
Engineering Access Control		•	•		<b>■</b> ¹	<b>■</b> ¹	■1	■¹	<b>■</b> ¹	<b>■</b> ¹
Connect Multiple Wired-Ethernet Devices to Network	•			•	•	•	•	•	•	•
Convert Wired 10/100BASE-T Ethernet to Fiber-Optic 100BASE-FX Ethernet	•	•	•	•	•		•	•	•	•
Convert Serial Links to Ethernet Links		•	•							

#### **Features**

reactives									
Cryptography (Encryption and Authentication)		•	•						
User-Based Accounts	•	•	•	<b>■</b> ²	<b>■</b> <sup>2</sup>				
Centralized Authentication Via Lightweight Directory Access Protocol (LDAP)	■3	•	•	■2	<b>■</b> <sup>2</sup>				
Centralized Authentication Via Remote Authentication Dial-In User Service (RADIUS)		•	•						
Single Sign On (SSO)	■3								
Deny-by-Default Firewall		•	•	■4	■4	■4	■4	■4	■4
Import/Export Configuration Files	•	•	•	■2	<b>■</b> <sup>2</sup>				
VPN		•	•						
Syslog Logging	•	•	•	•	•	•	•	•	•
Network Management System (NMS) Software	•			•	•	-	•	-	-
GPS Receiver	•								
Power over Ethernet Plus (PoE+)							-	•	•
Real-Time Latency Monitor	•								
Spanning Tree Protocol (STP)	•	•	•	•		-		-	•
Rapid Spanning Tree Protocol (RSTP)	•			•		-		-	•
Multiple Spanning Tree Protocol (MSTP)	•								
VLANs	•	•	•	•	-	•	•	•	•
Ethernet Class of Service (CoS)	•			•	-	•	•	-	•

⊏uner	net Por	ts, con	mector

ua		

Copper 10/100BASE, RJ45	0-85	3	3	3 or 4	0-24	0-20	0-24	2-8	0-8	0–8
Fiber-Optic 100BASE, LC	0-85	2	2	1 or 2	0-24	0-20	0-24	0-6	0-8	0–8
Copper 1000BASE, RJ45	0-85				0-8	0-4	0-24	0-4	0-8	0–10
Fiber-Optic 1000BASE, LC	4 <sup>6</sup> /0-8 <sup>7</sup>				0-8	0-4	0-24	0-4	0-8	0–10
Fiber-Optic 10GE, LC										0-2
Small Form-Factor Pluggable (SFP) Cages	4 <sup>6</sup> /0-8 <sup>7,8</sup>				0-24		0-24		0-8	0–10
Sindii Futiti-ractui Fiugyabie (SFF) Cayes	4 /0-8				0-24		0-24		0-8	0-1

<sup>&</sup>lt;sup>1</sup>Communication management for engineering access.

<sup>2</sup>SEL-5056 NMS software, when using SDN technology, provides centralized authentication, user-based accounts, and import/export configuration files.

<sup>&</sup>lt;sup>3</sup>SEL-5052 Server NMS Software provides LDAP centralized authentication and SSO for the ICON.

<sup>&</sup>lt;sup>4</sup>Deny-by-default network access control.

SEL ICON has the option to support 8 copper and 8 SFP ports across two Ethernet Bridging Access Modules (EBAMs).

<sup>&</sup>lt;sup>6</sup>SEL-8022-01 Enhanced Protected Line Module supports 2 fiber-optic Gigabit interfaces.

<sup>&</sup>lt;sup>7</sup>SEL-8036-01 Ethernet Bridging Access Module supports 4 fiber-optic 100BASE-FX/Gigabit interfaces.

<sup>\*</sup>SEL ICON uses SFP cages for SONET and GigE fiber-optic interfaces.



# Wireless Communications

selinc.com/products/categories/networking-communications/#wireless-communications

Wireless communications extend networks in areas where wired communications networks are not available or are cost-prohibitive. SEL wireless devices use radio signals to communicate and send data over the air, eliminating the need for traditional cabling.



#### SEL-3061 Cellular Router

The SEL-3061 provides secure, remote access for devices using public cellular radio networks. It supports 4G LTE.

#### **Example System Diagram**

Substation

Improve operation efficiency with advanced network architectures.

Network Switch

## **Applications**

- Cellular router for remote connectivity
- Serial radio for protection schemes

#### **Technical Papers**

Expanding Protection and Control Communications Networks With Wireless Radio Links selinc.com/api/download/121073

Overcoming the Challenges of License-Free Radio Communications With Secure Cellular Radios selinc.com/api/download/140452

#### Webinar

Improve System Visibility and Reliability With SEL's Wireless Fault Indication System

selinc.com/events/on-demand-webinar/134158



# **Customer Story**

SCADA System Sheds Light on Texas Utility's Power System


selinc.com/solutions/success-stories/ scada-in-texas

#### Video

Communication Made Easy Over Difficult Terrain

video.selinc.com/detail/video/767833630001







Communications




# SEL-3031 Serial Radio Transceiver

The SEL-3031 is a 900 MHz ISM serial data radio that supports point-to-point (P2P) and point-to-multipoint (P2MP) operational modes. In P2P mode, the SEL-3031 supports three serial data ports in one radio channel. It can protect critical data from malicious attacks with the optional encryption card.

#### **Example System Diagram**

Economical communications solutions for remote locations and controls



Applications	SEL-3031	SEL-3061
Wireless Communications for SCADA	•	•
High-Speed Teleprotection	•	
Distribution Automation	•	•
Wireless Communications for Synchrophasor Data	•	•
Substation-to-Substation Communications Link		•
Wireless Communications for Distributed Generation	•	•
Permanent Wireless Cable Replacement	•	
Remote Engineering Access	•	
Short-Range Engineering Access	•	
LAN Extension		•
Wireless Backhaul Communications for Fault and Load Transmitters		•

Setup Method		
USB Port	•	
Secure Web Interface Via Ethernet Port		•
Wireless Configuration	•	•
Simple Network Management Protocol (SNMP)		•

	SEL-3031	SEL-3061
Features	SEI	SEI
915 MHz ISM Band (License-Free)	•	
Serial Communication	•	•
Ethernet Communication		-
Low Latency for Teleprotection	•	
Compatible With SEL MIRRORED BITS® Communications	•	
Compatible With Modbus	•	•
Compatible With DNP3 and Typical Byte-Oriented Protocols	•	•
Encryption	f	•
Point-to-Multipoint Capability	•	
Cellular Capability		•
EIA-232 Port (Quantity)	3	1
Wired EIA-485 Port	+	
High Maximum Throughput (1 Mbps or Greater)		•
Device Status LEDs	•	•
Visible Link Quality Indicator		•

■ Standard feature + Model option

f With SEL-3044 Encryption Card option



selinc.com/products/categories/precise-time

SEL precise-time products keep critical infrastructure devices synchronized to the microsecond. They offer resilience and security that meet the rigorous demands of critical infrastructure while supporting a range of industry protocols. With tough solid-state hardware, SEL precise-time products are engineered for reliability. Backed by our worldclass sales and customer service team, these products provide a low cost of ownership and minimize the risk of disruption.

## **Applications**

- Utility and industrial facilities
- Manufacturing
- Military bases
- Transportation systems
- Land mobile radio (LMR) systems
- Emergency services

# **Customer Story**

Emergency Radio—A Community **Effort** 

selinc.com/highlights/whitmancounty-emergency-communications

#### **Technical Papers**

Understanding the Impact of Time Inaccuracy on Synchrophasors, Traveling-Wave Fault Locating, and Line Current **Differential Protection** 

selinc.com/api/download/138657

It's About Time—Considerations and Requirements for DSS and Line Current Differential Applications

selinc.com/api/download/138274

Using Wide-Area Precise Time Distribution to Increase Dependability and Security of Substation Time Synchronization selinc.com/api/download/136425



# SEL-2488 Satellite-**Synchronized Network Clock**

The SEL-2488 receives multiple time signals and distributes precise frequency and time via 10 MHz, IRIG-B, NTP, and PTP outputs with ±40 ns accuracy.



## SEL-2407® Satellite-**Synchronized Clock**

The SEL-2407 is a half-rack satellite clock with a time display that provides IRIG-B outputs with ±100 ns accuracy.



# SEL-2401 Satellite-Synchronized Clock

The SEL-2401 is a compact satellite clock that provides an IRIG-B output with ±100 ns accuracy.



# SEL-3400 IRIG-B **Distribution Module**

The SEL-3400 verifies two IRIG-B inputs and distributes demodulated IRIG-B output for up to 240 devices.



## SEL-3405 High-Accuracy IRIG-B Fiber-Optic Transceiver

SEL-3405 transceivers send delay-compensated demodulated IRIG-B signals up to 4 km (2.5 mi).



#### SEL-9524 GNSS Antenna

The SEL-9524 is a rugged and reliable antenna for GNSS devices in critical infrastructure applications.



#### SEL-3401 Digital Clock

The SEL-3401 provides a highly visible time display for use anywhere there are time-critical functions set by IRIG-B synchronization signals.



# SEL-9929 Satellite-Synchronized Clock Display Kit

The SEL-9929 kit includes a satellitesynchronized clock, a large digital clock display, and all accessories.



# SEL ICON® Integrated **Communications Optical Network**

The ICON provides precise time distribution over WANs, with an accuracy of 1 µs with a variety of input and output protocols.

Applications	SEL-2401	SEL-2407®	SEL-3400	SEL-3401	SEL ICON®	SEL-2488
Time Source for Substation and Industrial Applications	•	•	-		•	•
Time Source for Land Mobile Radio (LMR) Systems and Public Safety Answering Points (PSAPs)						•
Digital Secondary Systems (Sampled Values)					•	•
Time Source for Phasor Measurement Unit (IEEE C37.118.1-2011 Synchrophasors)		•				
Time Source for Recloser						
Time Source for Line Current Differential Protection, Traveling-Wave Fault Locating, and Time-Synchronized Event Reporting	•	•	•		•	•
Network Time Synchronization Applications Using the Network Time Protocol (NTP)						•

# **Time Sources and Time Distribution**

Demodulated IRIG-B Outputs (Quantity)	1	6	12	4*	4	9
Modulated IRIG-B Outputs (Quantity)		1				up to 4
Optional 10 MHz Frequency Outputs (Quantity)						6
GPS Satellite Tracking	•				•	•
GLONASS Satellite Tracking (Verification Only)						•
Demodulated IRIG-B Input			•	•	•	
Synchronized Pulse Output	•				•	•
NTP Server						-
IEEE 1588-2008 Precision Time Protocol (PTP) Input (With ITU-T G.8275.1 Telecom Profile)					+	+
IEEE 1588-2008 PTP Output (With IEEE C37.238-2011/2017 Power System and IEC/IEEE 61850-9-3:2016 Power Utility Automation Profiles)					+	+

## **Features**

			•		
	•	•			•
	•	•	+	+	•
	•	+	•	+	+
	•	•			
				•	•
					•
					•
•	•				
				•	•
•	•			•	•
					+
		•		•	<b>■</b> ¹
•	•	-	•	•	•
	•				

#### Accuracy

Average Accuracy (ns)	±100	±100			±40	
Peak Accuracy (ns)	±500	±500		±1,000	±100	

<sup>■</sup> Standard feature + Model option/accessory 'SEL-2488 includes antenna cable delay compensation

# 

# **Transceivers and Adapters**

selinc.com/products/categories/cables-accessories

Many SEL devices come with standard or optional fiber-optic communications ports. Transceivers convert between copper and fiber optics or between other communications interface standards.

# **Applications**

- Single- or multimode fiber
- Distances ranging from 1 m (3.28 ft) to 110 km (68.35 mi)

#### **Related Material**

Fiber-Optic Products and Applications selinc.com/api/download/2848

Connector and Wavelength	SEL-2800	SEL-2810	SEL-2812	SEL-9220	SEL-2814	SEL-2815	SEL-2820	SEL-2824	SEL-2829	SEL-2830	SEL-2831	SEL-2894
V-Pin, 650 nm	-	•					•					
ST, 850 nm			-	-	•	•		-				•
ST, 1,300 nm									-	•		
ST, 1,550 nm											•	

#### **Fiber Compatibility**

200 µm Core Multimode Fiber (SEL-C805)	•	•	•	•	•	•	-	•			
50 or 62.5 μm Core Multimode Fiber (SEL-C807, SEL-C808)			•	•	•	•		•			-
9 μm Core Single-Mode Fiber (SEL-C809)									•	•	

## **Electrical Features**

EIA-232 Asynchronous Serial Data	•	•	•		-	-			•	•		•
EIA-485 Asynchronous Serial Data				•			•	•				
DTE/DCE Switch					•	•			•	•	•	
IRIG-B Transfer With Data		•	•	•								
Hardware Flow Control Lines With Data					-			•				
Power From Electrical Port Pins	•	•	•	•	•	•				•		•
External Power Jack or Terminals					•		•	•				

#### **Distances**

Minimum (metric)	1 m	1 m	1 m	1 m	1 m	2 km	1 m	1 m	1 m	16 km	16 km	1 m
Minimum (U.S.)	3.28 ft	1.24 mi	3.28 ft	3.28 ft	3.28 ft	9.94 mi	9.94 mi	3.28 ft				
Maximum (metric)	500 m	500 m	4 km	4 km	4 km	15 km	500 m	4 km	23 km	80 km	110 km	2 km
Maximum (U.S.)	0.3 mi	0.3 mi	2.48 mi	2.48 mi	2.48 mi	9.3 mi	0.3 mi	2.48 mi	14.3 mi	49.7 mi	68.3 mi	1.2 mi

■ Standard feature





# SEL-2800/2815 Fiber-Optic Transceivers

Improve safety, signal integrity, and reliability of EIA-232 communications by using multimode SEL-2800 or SEL-2815 transceivers instead of wire.



# SEL-2810/2812/2814 Fiber-Optic Transceivers

Use EIA-232 multimode fiber-optic transceivers instead of wire. The SEL-2810 and SEL-2812 support IRIG-B time signals, while the SEL-2814 works with hardware flow control signals.





# SEL-2829/2830/2831 Single-Mode Fiber-Optic Transceivers/Modems

Apply the SEL-2829, SEL-2830, or SEL-2831 to use two optical fibers instead of wire to transfer bidirectional serial data.



# SEL-2820/2824 Multimode Fiber-Optic EIA-485 Transceivers

Apply an SEL-2820 or SEL-2824 to safely add isolated segments to multidrop and point-to-point EIA-485 networks.





## SEL-2890 Ethernet Transceiver

Add Ethernet connectivity to an SEL device using its EIA-232 serial port with the SEL-2890.



# SEL-9220 Fiber-Optic Adapter for SEL-300 Series Relays

Convert the EIA-485 port of an SEL-300 series relay to a point-to-point fiber-optic port with the SEL-9220.





#### SEL-2894 Interface Converter

Apply the SEL-2894 to transfer SEL MIRRORED BITS® communications via an IEEE C37.94 fiber-optic link through a communications multiplexer.





# SEL-2886 EIA-232 to EIA-485 Interface Converter

Connect EIA-232 devices to an EIA-485 network with SEL-2886 converters.



# SEL-2902 RJ45 to DB-9 Adapter Panel

Easily retrofit RJ45 ports to DB-9 connectors using the SEL-2902 adapter panel. The SEL-2902 allows you to retain existing serial cables and transceivers when upgrading from an SEL-3530 Real-Time Automation Controller (RTAC) or SEL-2020/2030/2032 Communications Processor to an SEL-3300 series computing platform.



# Cables

selinc.com/products/categories/cables-accessories

SEL manufactures high-quality cables for connecting a variety of devices. Each cable is qualitytested to ensure reliability and proper operation. Choose the cable types and lengths to match your applications using the SEL-5801 Cable Selector program.

## **Applications**

- GPS and radio antenna connections and IRIG-B time distribution
- Serial communications over long distances without risk of electromagnetic interference
- Adaption and connection to **USB** ports

#### **Related Material**

SEL-5801 Cable Selector selinc.com/5801-selector



## SEL-C804 Multimode Arc-Flash **Detection Fiber-Optic Cable**

Use SEL-C804 cables with SEL-751 and SEL-851 Feeder Protection Relays and with SEL-710-5 Motor Protection Relays.



# SEL-C805 200 µm Multimode Fiber-Optic Cable

Connect V-pin or ST ports with SEL-C805 cable assemblies.



## SEL-C807 62.5/200 µm Multimode Fiber-Optic Cable

Use SEL-C807 cable assemblies to connect ST or LC ports.



# SEL-C808 62.5/125 µm Multimode Fiber-Optic Cable

Connect ST, SC, or LC ports with SEL-C808 cable assemblies.



# SEL-C809 9 µm Single-Mode Fiber-Optic Cables

Use SEL-C809 cable assemblies to connect ST, SC, or LC ports.



# Category 5e Ethernet

Apply high-quality, shielded twisted-pair (STP) Category 5e Ethernet cables for copper Ethernet connections.



#### **Coaxial Cables**

Use SEL Coaxial Cables for GPS and radio antenna connections and IRIG-B time distribution.



#### **USB Serial Cables**

Add a 1.8 m (6 ft) or 4.6 m (15 ft) EIA-232 serial port cable to a PC USB port to communicate with SEL relays and other devices with EIA-232 serial ports.



# **Electrical Data Cables**

Apply SEL Electrical Data Cables to reliably connect SEL products and other devices, including relays, information processors, computers, I/O modules, meters, clocks, and modems.

Connector	SEL-C804	SEL-C805Z	SEL-C805D	SEL-C805G	SEL-C807Z	SEL-C807G	SEL-C808Z	SEL-C808P	SEL-C808G	SEL-C809Z	SEL-C809P	SEL-C809G
V-Pin	•	•	٠	•								
ST	•	•	٠	•	•	•	•	٠	•	•	•	-
LC					•	•	•	٠	•	•	•	•
SC							•	•	•	•	•	•

Jacket Material	SEL-C804	SEL-C805Z	SEL-C805D	SEL-C805G	SEL-C807Z	SEL-C807G	SEL-C808Z	SEL-C808P	SEL-C808G	SEL-C809Z	SEL-C809P	SEL-C809G
Polyvinyl Chloride (PVC)		•	٠		٠		٠	٠	•	٠	٠	•
Polyethylene (PE)	•			•		•						

# Fiber Diameter (Core/Outer)

1,000 µm	•											
200 μm		•	٠	•								
62.5/200 μm					•	•						
62.5/125 μm							•	٠	•			
9/125 μm										•	•	•

ination	

V-Pin Termination Kit	•	•	•	•								
ST Termination Kit	•	•	•	•	•	•						
LC, ST, and SC Termination Kit							•	•	•	•	•	•

# Wavelength

650 nm (Multimode)	•	•	•								
850 nm (Multimode)	٠	•	•	•	•	•	٠	•			
1,300 nm (Multimode)				•	•	•	٠	•			
1,300–1,550 nm (Single-Mode)									•	•	•

# **Options**

Bulk (No Connectors)	•	•	•	•	•	•	•	•	•	•	•	•
Pulling Loop						•			•			

Fiber Count												
Simplex (1 Fiber)	•	•			•		•	•		•	•	
Duplex (2 Fibers)	•	•	•	•	•	•	•	•	•	•	•	•
Quad (4 Fibers)			-	-		-			-			

# Fiber-Optic Compatibility

SEL-2800/2810/2820		•	•	•								
SEL-2812/2814/2815/ 2824/3405/9220		•	•	•	•	•	•	•	•			
SEL-2829/2830/2831										•	•	•
SEL-751/751A/710-5 Arc-Flash Detection	•											
Multimode Fiber-Optic Ethernet					•	•	•	•	•			
Single-Mode Fiber-Optic Ethernet										•	•	•

#### **Cable Ratings**

Riser-Rated (OFNR)	•	•		•		•		•	•		•
Plenum-Rated (OFNP)							•			•	
Water-Blocked		٠									
Waterproof			•		•			٠			•

#### ■ Standard feature



selinc.com/products/categories/measurement-streaming/#remote-i-o

Remote I/O modules transfer data from remote locations over fiber and expand the I/O of SEL relays, automation controllers, and other devices without modification to the control panel face.

#### **Applications**

- Provide additional I/O for SEL protective relays and information processors
- Save wiring via I/O multiplexing
- Implement teleprotection
- Improve safety with optical fiber

#### Case Study

Remote I/O Modules Enable DC Substation Transfer Trip for Expanding Denver Light Rail System selinc.com/api/download/2723

Number of I/O Channels	SEL-2440	SEL-2505	SEL-2506	SEL-2507	SEL-2515	SEL-2516	SEL-2595
Digital Inputs (DI) Base	32	8	8	8	8	8	8
DI Maximum	48	8	8	8	8	8	8
Digital Outputs (DO) Base	16	8	8		8	8	8
High-Speed DO Base	10			8			
DO Maximum	32	8	8	8	8	8	8

# **Supported Protocols**

SEL Fast Messaging					-	-	
SEL MIRRORED BITS Communications	•	•	-	-			
DNP3	+						
DNP3 LAN/WAN	+						
File Transfer Protocol (FTP)/Secure FTP (SFTP)	•						
IEC 61850 GOOSE	+						
IEC 61850 MMS	+						
IEEE C37.94							
Modbus	•						
Parallel Redundancy Protocol (PRP)	•						
Precision Time Protocol (PTP)	•						
Simple Network Time Protocol (SNTP)	•						
Telnet	•						

■ Standard feature + Model option



# **SEL-2595 Teleprotection Terminal**

Use the SEL-2595 to securely transfer teleprotection signals through a highspeed IEEE C37.94 optical-fiber interface.



#### SEL-2505/2506/2507 Remote I/O Module

Connect a remote I/O module to a fiberoptic port or transceiver on a protective relay to add digital I/O. Or, wire the module I/O to relay I/O to add SEL Mirrored Bits® teleprotection.



#### SEL-2515/2516 Remote I/O Module

Connect these remote I/O modules, which are suitable for use in automation systems, to SEL information processors to easily expand inputs and outputs.



# SEL-2440 Discrete Programmable **Automation Controller (DPAC)**

The SEL-2440 offers utility-grade I/O, powerful processing, flexible communications, and microsecond timing.



# **Annunciation and Notification**

selinc.com/products/categories/hmi-annunciators

Annunciation and notification devices provide local and remote notification to improve situational awareness, efficiency, and safety. They display alarm conditions, and their communications ports enable integration with protection and automation systems.

Applications	SEL-2522	SEL-2523	SEL-2533	SEL-2240
Local Visual Indication	•	•	•	+
Remote Visual Indication		•	•	+
Local Audible Indication	•	•	•	
Remote Audible Indication	•	•	•	
Telephone Dial-Out Messages		•	•	
Local SELogic® Control Equations and Time Tagging		•	•	
IEC 61131 Logic Programming				•

#### Mounting and Labeling

3 3				
Rack Mount	+	+		•
Panel Mount	+	+	•	+
User-Defined Slide-In Labels	•	•	•	
Color LCD Software-Defined Labels				+

#### Inputs, Outputs, HMI, and Protocols

Digital Inputs	36	42	14 <sup>+</sup>	1,728
Acknowledge, Reset, and Test Digital Inputs	3	6	4 <sup>+</sup>	
Digital Outputs	1	11	14⁺	864
Alarm Digital Output	1	1	1	1
General Display LEDs/Windows	36	36	10	625
Programmable LED				19
LCD Touchscreen				+
Pushbuttons	3	4	4	6
Base Serial Ports		1	1	4
Copper or Fiber-Optic Ethernet Ports				3
Optional Multimode Fiber-Optic Serial Port		1	1	
Optional Additional EIA-232 or EIA-485 Port		1	1	
IRIG-B Time Input		1	1	1
ISA Annunciation Alarm Sequence Choices	2	8	8	
Number of Supported Protocols		5	5	31

■ Standard feature + Model option



#### SEL-2522 Alarm Panel

Apply the SEL-2522 with up to 36 inputs to easily view the status of alarms and operating events.



#### **SEL-2523 Annunciator Panel**

Provide local and remote notifications with the SEL-2523, which includes programmable logic and up to four communications ports.



#### **SEL-2533 Annunciator**

Use the compact, ten-window SEL-2533 to provide local and remote annunciation.



#### SEL-2240 Axion®

The Axion is a comprehensive control and monitoring solution that includes a full-color 7-inch touchscreen, allowing you to interact with up to 25 customizable alarm panels.



selinc.com/products/categories/software

SEL software products help automate and control power systems, optimize device configuration, configure secure operational technology (OT) networks, and collect and visualize power system data.

SEL Compass® keeps software applications and relay configuration drivers up to date and includes SEL instruction manuals, application guides, hardware drivers, and more.

#### Webinars

Streamline Data Collection and Fleet Management With DMA on Blueframe® selinc.com/events/on-demand-webinar/ 138573

The Next Evolution in FLISR Simplicity: Automatic Configuration With GIS Data selinc.com/events/on-demand-webinar/ 138534

Preventing PT Failures and Locating Generation Loss With Synchrowave® Operations

selinc.com/events/on-demand-webinar/ 136575

Improve Your Power System Visibility selinc.com/events/on-demand-webinar/ 140676

Automate SDN Configuration With RTAC and IEC 61850 Files

selinc.com/events/on-demand-webinar/ 137644

Collect and Visualize Metering Data With Next-Generation Software selinc.com/events/on-demand-webinar/ 138791

#### Case Study

Real-Time Operational Use Cases for Time-Synchronized Measurements With Synchrowave Operations selinc.com/api/download/134864

Software Product	Configuration	Automation	Visualization and Analysis
ACSELERATOR QuickSet® SEL-5030 Software	•		- 10
SEL Grid Configurator	•		
AcSELerator Architect® SEL-5032 Software			
acSELerator RTAC® SEL-5033 Software	•		
acSELerator Diagram Builder™ SEL-5035 Software	•		
ACSELERATOR® Bay Screen Builder SEL-5036 Software	•		
SEL-5051/5052 Client/Server Network Management System (NMS) Software	•	•	•
SEL-5056 Network Management System (NMS)	•	•	•
SEL-5057 SDN Application Suite—Flow Auditor			•
SEL Blueframe Data Management and Automation (DMA) Solution		•	
SEL Blueframe Distribution Management System (DMS) Solution		•	
SEL-5231 Configuration API	•		
SEL-5073 SYNCHROWAVE Phasor Data Concentrator (PDC) Software		•	
SEL-5601-2 Synchrowave Event Software			•
SEL-5702 Synchrowave Operations			•
SEL-5703 Synchrowave Monitoring			•
SEL-5705 Synchrowave Reports			•

#### ACSELERATOR QuickSet

Included with supported products

QuickSet is a tool to configure, commission, and manage devices for power system protection, control, metering, and monitoring.

#### **SEL Grid Configurator**

Included with supported products

Grid Configurator makes it more efficient to configure and commission SEL power system devices using its spreadsheet-style editor, protection visualization, intuitive HMI, custom filters, and multiple-device settings management.

#### ACSELERATOR Architect

Included with supported products

Architect streamlines the configuration and documentation of IEC 61850 messages, controls, and reports.

#### ACSELERATOR RTAC

Included with SEL RTAC purchase

acSELERATOR RTAC is an intuitive, easy-to-use application designed to configure the SEL Real-Time Automation Controller (RTAC) family of products, including the SEL-2240 Axion®.

#### **ACSELERATOR Diagram Builder**

Included with RTAC HMI purchase

Diagram Builder enables the creation and management of HMI visualization projects for the SEL RTACs in your system.

#### ACSELERATOR Bay Screen Builder

Included with QuickSet and AcSELERATOR RTAC

Bay Screen Builder, which works with QuickSet and AcSELERATOR RTAC, enables the custom creation of bay screens for SEL devices with touchscreen displays.

## **SDN Application Suite**

The SDN Application Suite includes Flow Auditor, which operates with SEL-5056 to provide safe, nondisruptive audits and documentation of conversations between hosts on your critical infrastructure network.

# LAN Network Management System (NMS)

Included with SEL software-defined networking (SDN) switch purchase


SEL-5056 NMS Software is the central controller for the configuration, monitoring, and management of SEL SDN-enabled switches.

# WAN Client/Server NMS

SEL-5051/5052 Client/Server NMS Software helps maintain a secure, reliable, and efficient communications infrastructure.

#### **Example System Diagram**

Use SEL software solutions to optimize the configuration and management of SEL devices and networks, provide advanced automation and data collection capabilities, and offer robust tools for data visualization and analysis.



## **SEL Blueframe Application Platform**

Blueframe is a secure application platform that can be deployed on an SEL computing platform or virtualized. It is purpose-built for managing large fleets of devices, visualizing and analyzing their data, and implementing automation and control solutions. SEL offers several power system solutions hosted on Blueframe.

# **SEL Data Management and** Automation (DMA) Blueframe **Application Suite**

The Blueframe DMA solution automatically collects, stores, and manages device specific information to simplify day-to-day management of a system of devices and to support compliance efforts.

# **SEL Distribution Management** System (DMS) Blueframe **Application Suite**

The Blueframe DMS solution includes a Fault Location, Isolation, and Service Restoration (FLISR) application package, which reduces customer outages, improves reliability metrics, and provides rapid fault detection and system restoration.

# **SEL Configuration API**

This API provides an integrated approach to managing SEL device configuration data, offering read/ write access to device identification information, connection parameters. passwords, and settings stored in the AcSELERATOR Database.

## Synchrowave Reports

Synchrowave Reports simplifies metering and power quality data reporting by analyzing stored voltage sag, swell, and interruption (VSSI) and load profile (LDP) data, and automatically delivering scheduled reports by email.

#### **Synchrowave Event**

Synchrowave Event provides a platform to display and analyze recorded power system data from SEL relay event records, motor start reports, synchrophasor data, COMTRADE files, and more.

#### **Synchrowave Operations**

Synchrowave Operations increases grid safety and reliability through situational awareness with highresolution time-series data, real-time analytics, and geographical information system (GIS) location information.

#### Synchrowave Monitoring

Synchrowave Monitoring brings synchrophasor data, streaming waveform data, and relay event reports together into one place so engineers can analyze both the high-level system impact of an event and the detailed oscillography data.

#### **SEL RTAC HMI**

The SEL RTAC HMI offers an easy way to visualize data to monitor and control your system.

# SYNCHROWAVE PDC

SYNCHROWAVE PDC provides synchrophasor aggregation and time alignment for downstream applications and inter-entity data sharing.



# **Accessories and Tools**

selinc.com/products/categories/cables-accessories



# SEL-3790 Low-Voltage Divider Module NEW

Apply the compact, lightweight SEL-3790 as a low-power voltage transformer in switchgear and other space-limited applications. This module takes in voltages between 120 Vac and 480 Vac and produces a voltage suitable for SEL relays with low-power inputs.



#### SEL-RPM Redundant Power Module

Use the SEL-RPM to combine as many as three ac sources and one dc source to provide a single reliable dc output (unregulated 125 Vdc). Large energy storage capacitors provide ride-through capability when all input sources are lost.





# SEL-9321 Low-Voltage DC Power Supply or SEL-9322 15 Vdc Power Supply

Provide low-voltage dc power from station battery or ac sources for communications devices and accessories with SEL-9321 and SEL-9322 power supplies.



# SEL-9501 or SEL-9502 Contact Arc Suppressor

Decrease maintenance costs, increase contact reliability, and reduce destructive dc circuit overvoltages with the self-powered SEL-9501/9502 arc suppressors.



#### SEL-4520 Arc-Flash Test Module

Use the SEL-4520 to conveniently test the operation of arc-flash detection relays installed in metal-clad and metal-enclosed switchgear.



#### SEL-4388 MIRRORED BITS® Tester

Accelerate commissioning and bench testing of SEL MIRRORED BITS links and improve training, maintenance, and cable identification with the SEL-4388.



# SEL-9510 Control Switch Module

Use the SEL-9510 where independent local control is needed. High-visibility status indication and arc-suppressed contacts are ideal for breaker control.



# SEL-2126 Fiber-Optic Transfer Switch

Apply the SEL-2126 to simply reroute any communications protocol carried on the IEEE C37.94 fiber-optic interface standard without moving fiber connectors and without changing communications equipment programming.



#### SEL-2652 Trip Coil Monitor

Verify circuit breaker or lockout relay trip coil and trip circuit continuity with the SEL-2652.



# Panels and Enclosures

selinc.com/services/panels-enclosures

SEL designs, manufactures, tests, and delivers custom protection, control, and metering panels, control cabinets, retrofit doors, and enclosures. We integrate multiple pieces of equipment (from SEL and other manufacturers) into a single assembly or kit, enabling onestop shopping for assemblies and labor with a quick turnaround time. Our experts will work with you to understand your requirements and challenges and provide innovative, economical solutions built to the highest quality standard.

#### **Customer Stories**

Partnership and Panels Improve Infrastructure selinc.com/highlights/rayburn-electric

Distribution Modernization in Kentucky selinc.com/highlights/lge-ku



## Complete Panel and **Enclosure Solutions**

SEL custom panel and enclosure solutions come with the following options and services:

- · Consulting, engineering design, and field services.
- Panel and assembly manufacturing tested in our in-house UL 508Acertified panel factories.
- Protection, automation, and control equipment manufacturing.
- Easily extractable assemblies for all SEL-700 and SEL-2400 series products.
- Cabinet designs for both indoor and outdoor applications, including stainless steel, mild steel, aluminum, fiberglass, and polycarbonate enclosures.
- Enclosures, racks, bezels, plates, portables, swing panels, doors, and retrofits.
- Assemblies that meet Seismic. NEMA, and UL 508A rating and certification requirements.



## Complete Design, Manufacturing, Testing, and Commissioning

To exactly meet your needs, we offer complete panel and enclosure solutions, from design through commissioning. We test the final implementation of every product or system before it ships, reducing your overall project costs and engineering time. This testing makes commissioning easier and faster.

#### **Field Services**

SEL provides complete installation services during any project phase, from demolition and wiring to testing and commissioning. SEL teams have extensive safety training and provide the same level of quality customers have come to expect from SEL manufacturing and other services.

Available field services include:

- Site investigation and surveying.
- Demolition and site development.
- Construction management.
- New relay panel installation, integration, and wiring.
- Automation and control system installation.
- SCADA installation.
- Arc-flash solutions.
- Testing and commissioning.
- Life cycle support.



# **Direct-Replacement Assemblies**

selinc.com/products/categories/panels-enclosures/#direct-replacements-retrofits

Streamline retrofit projects with SEL direct-replacement assemblies for motor, generator, transformer, bus, feeder, and metering applications.

These complete, factory-tested, preassembled retrofit kits are designed to closely match the features, form-factor, and terminal blocks of specific legacy digital and electromechanical relays. Direct-replacement assemblies combine field-proven SEL relays with specialized mounting plates, interposing terminal blocks, and other hardware to ensure quick, seamless, and cost-effective upgrades.



# Simplify Installation and Configuration

Direct-replacement assemblies deliver an installation experience that is easy, fast, and error-free. The physical installation work for most digital direct-replacement assemblies can typically be completed within an hour. Assemblies fit the existing panel opening and mounting holes. Terminal block arrangements and wiring designations closely match legacy products, and SEL provides wiring labels with all retrofit kits.

Electromechanical direct-replacement assemblies are designed to replace sets of three or four electromechanical relays aligned horizontally on the same panel with a digital relay and test switch(es). Installation can typically be completed within just a few hours with the removal of the panel dividers between the old relays and the addition of power supply connections.



## Minimize Engineering Work

Eliminate time-intensive and costly engineering tasks, such as revising drawings and diagrams. All assembly kits include wiring diagrams, so existing documentation for your system is not required for installation.

# Partner With SEL on a Turnkey Solution

We offer complete design, installation, and commissioning services for retrofit projects, saving you time and reducing costs.

Manufacturers we offer directreplacement assemblies for include:

- GF
- Westinghouse
- Cutler-Hammer
- Eaton
- Square D
- ABB
- Siemens
- Schneider Electric

SEL Engineering Services engineers and staff approach every project with a spirit of quality, innovation, and service. We offer a broad range of expertise and support to the utility, industrial, commercial, and governmental sectors. From planning and implementation through ongoing maintenance and support, we deliver a solution tailored to your needs.



# **Featured Services** and Solutions

# Transmission, Distribution, and Substation Engineering

From design through construction, our multidisciplinary SEL Engineering Services teams help ensure the cost effectiveness, quality, and overall success of your transmission, distribution, or substation project. We provide development, modernization, and maintenance solutions to ensure your power systems are safe, reliable, and economical.

#### **Protection and Control**

SEL Engineering Services optimizes your power system protection and control. We specify, design, implement, test, and commission power solutions. Our solutions safeguard valuable equipment, mitigate cyber threats, minimize outages, and meet safety and security compliance standards.

#### Microgrids and Power Management

SEL Engineering Services engineers are experts at designing microgrid control systems and power management solutions for all your project needs. Our solutions include comprehensive generation and load management using relays, logic, and control systems. See page 72 for more information.

#### **Field Services**

Whether you're upgrading, expanding, or implementing an entirely new system, SEL Engineering Services technicians can handle all phases of your project—from surveying, demolition, and wiring to installing, testing, and commissioning.

#### System Studies and Modeling

SEL Engineering Services uses a wide array of power system analysis tools, such as phasor domain modeling and electromagnetic transients program modeling, to perform non-real-time analysis and real-time hardware-inthe-loop studies to simulate "what if" scenarios.

#### **Cyber Services**

SEL Cyber Services designs endto-end operational technology (OT) security solutions to uniquely support your needs. Our full suite of security services strengthens your defenses, streamlines maintenance, and helps ensure compliance. See page 73 for more information.

#### **Panels and Enclosures**

SEL designs, manufactures, tests, and delivers custom protection, automation, control, and metering panels, control cabinets, and retrofit doors. SEL also helps you streamline your retrofit projects with direct-replacement assemblies that cause minimal impact on panels, wiring, and drawing sets.

#### **Project and Program Management**

As your complete substation solutions partner, SEL offers a single point of accountability—one trusted partner from concept to completion. Our comprehensive approach includes system and site planning, civil and structural engineering, equipment procurement, contractor management, testing, and commissioning. See page 71 for more information.

#### **Government Services**

SEL provides infrastructure protection, monitoring, and control systems to United States government agencies and their contractors—supporting mission-critical applications where reliability, cybersecurity, and supply chain assurance are essential.

# **Project and Program Management**

selinc.com/services/project-program-management

SEL provides solutions for substation engineering capital projects, programmatic equipment replacement, and unscheduled maintenance equipment replacement or upgrades. We ensure that power system solutions meet both industry standards and your own project-specific requirements.

#### **Engineering**

We provide electrical, civil, and structural engineering services for substation projects of any size and voltage, from targeted upgrades and retrofits to electrical and civil design packages for complete substations.

#### **Procurement**

We can partner with your preferred suppliers or bring on our team of prequalified subcontractors. We assist with procuring turnkey components and work closely with you to maximize value by reducing lifecycle costs.

#### **Construction Management**

As your construction management partner, SEL ensures the successful execution and completion of the project with an unwavering commitment to safety and quality.

We also provide planning, program management, project management, owner's engineering, and staff augmentation services as part of a master services agreement, engineer-of-choice designation, or individual contract.

#### **Planning**

SEL Engineering Services discusses with you the feasibility and broad goals of your program or project. We advise which projects to pursue, in what order, and help you determine which emerging technologies apply to your current and future needs.

# **Owner's Engineering**

Put our deep technical knowledge and industry expertise to work for you with SEL owner's engineering services. As an owner's engineer, we will work in your interests to help maximize safety, reliability, and profitability, both shortand long-term, for your project or program.

#### **Program Management**

SEL Engineering Services program management supports your large initiatives to help you align project goals and allocate resources. As projects progress, our program managers help coordinate the different components of the program to meet deadlines and budgets.



# Customer Story Distribution Modernization in Kentucky selinc.com/highlights/lge-ku

# Microgrids and Power Management

selinc.com/services/microgrids-power-management

SEL Engineering Services personnel are experts at designing solutions for a variety of applications, including industrial power management systems, microgrid control systems (MCSs), remedial action schemes (RASs), and wide-area monitoring, protection, and control (WAMPAC).

## **Industrial Power Management**

POWERMAX® Power Management and Control Systems intelligently balance generation and load at subcycle speeds to maintain grid stability, help mitigate widespread outages, reduce operating expenses, and meet everchanging system demands.

POWERMAX is a scalable, fast, and secure system composed of relay and control hardware, software, and logic processing, all designed by our expert power engineers. Benefits include:

- Advanced high-speed protection and control technology—such as islanding detection and decoupling, high-speed load shedding, generation shedding, and generator runback—to keep your critical processes running.
- Total system awareness with timesynchronized condition monitoring that tracks equipment status, electrical metering, cyber attacks, network traffic, and more.
- Point of common coupling management with power factor control, power export and import management, and single-click synchronization.
- Improved human safety and reduced equipment damage with adaptive protection, advanced protection systems, and arc-flash mitigation.

## **Microgrid Control Solutions**

Microgrids enhance energy reliability, resilience, and sustainability. They operate with the grid or islanded, integrating distributed energy resources for local power generation, energy storage, grid independence, and cost savings.

We apply our POWERMAX control logic to your microgrid to create a system that seamlessly meets your control, protection, and monitoring requirements. Our power system engineers work closely with microgrid owners and integrators to design, engineer, and implement the optimal MCS for your operational requirements.

#### **Remedial Action Schemes**

SEL POWERMAX provides the foundation for an RAS to integrate large geographic regions of interconnected generation sources, transmission lines, and loads. We incorporate a POWERMAX RAS with your existing relays, meters, and communications systems to reduce overall project costs.

Key applications for a POWERMAX RAS include:

- The addition of large renewable sources, such as wind power stations and photovoltaic arrays, with transmission systems.
- High-speed generation and/or load shedding to maintain grid stability.
- Synchrophasor monitoring and control.
- Fast decoupling solutions.
- Distributed computing and communications for smart transmission grid management.



#### **WAMPAC Systems**

WAMPAC systems allow operators to achieve comprehensive situational awareness over large geographical areas. WAMPAC and POWERMAX complement each other to provide visualization, analysis, notification, and archiving of time-series data, including synchrophasor data, relay event reports, point-on-wave data, and geographic information system (GIS) geospatial data. WAMPAC informs or triggers coordinated responses to correct system issues and maintain grid reliability.

#### **Customer Stories**

Microgrid Solution Plays Big on Campus selinc.com/highlights/msu

Innovation, Persistence, and a New Beginning selinc.com/highlights/gse-short

POWERMAX Prevents Blackouts at Motor Oil Hellas Refinery selinc.com/highlights/motor-oil-hellas

# **Cyber Services**

selinc.com/services/cyber-services

No matter your stage of the cyber lifecycle, our Cyber Services engineers build OT security solutions that are secure down to their very architecture. We use a front-end engineering methodology to design systems that uniquely support both your mission and your operational needs. From system assessment and baselining to cyber-defense solution development and ongoing system management, our full suite of security services strengthens your defenses, streamlines maintenance, and helps ensure compliance.

# Assessments, Governance, and Compliance

We provide services and solutions that streamline the demanding, potentially time-consuming tasks of maintaining compliance and keeping your infrastructure secure. We assist in determining high-value assets and threat vectors to identify next steps and solutions while helping define procedures and draft documentation to assist with system and process audits.

#### Security Resilience and Design

We ensure network resilience and security through a secure-by-default approach to system design. Integrating layered defenses, secure networking, and robust perimeter protection safeguards the integrity and availability of critical infrastructure. This forms a resilient, defense-in-depth architecture to defend against evolving threats. With remote access solutions and SEL security professionals augmenting your staff, you gain both the flexibility and the expertise to intelligently manage and protect your systems.

## **Monitoring and Detection**

Accredited cybersecurity engineers help you understand regulatory standards for internal network security monitoring (INSM) and assess your existing system. We collaborate with world-class cybersecurity vendors to leverage the best tools available and deliver an INSM solution that leverages any compatible devices you already own.

#### Life Cycle Support

We offer readiness and response for cyber incidents, monitoring, and maintenance.

 Readiness and Response
 We deliver proactive services, such as penetration testing, cybersecurity maturity assessments, employee training, and architecture reviews, to strengthen your security posture.

#### Maintenance

We provide ongoing support through patch, firmware, and software update management; security alert reviews; and alignment with future project needs.

#### Monitoring

We monitor SEL-designed or thirdparty-installed networks for threats and suspicious activity to ensure continuous situational awareness.

#### **Cybersecurity Center**

Our ICS and OT Cybersecurity Center provides the latest SEL industrial control system (ICS) and OT updates and a space to communicate with experts, analyze challenges, and share ideas.



#### **Customer Stories**

Defending Critical Substation Communications in Slovenia selinc.com/highlights/eles

Remote Engineering Access Solution Delivers Cybersecurity and Convenience selinc.com/highlights/gvea



# **Education and Training**

selinc com/education

#### Online Technical Resources

Get access to secure product information, configure and order products, and register for trainings with an SEL account. Visit selinc.com and select "Login" at the top right corner of your screen. You'll be able to:

- Access secure product information, like application guides and instruction manuals.
- Watch recorded webinars.
- View on-demand virtual presentations.
- Register for seminars, SEL University courses, and other educational offerings.



#### Schweitzer Drive Podcast

Our "Schweitzer Drive" podcast explores what goes on between the generation of electricity and the light switch. In each episode, SEL President Dave Whitehead talks with the entrepreneurs, innovators, and experts who are inventing the future of electric power. Visit selinc.com/schweitzerdrive to listen.

#### **SEL University**

Learn about power system fundamentals, the physics of power system protection, and advanced product applications with courses from SEL University. Gain Professional Development Hours (PDHs) and the confidence to install and commission SEL protection, automation, cybersecurity, and control products. Our training formats include eLearning courses as well as in-person and virtual courses that are taught by the same engineers who design SEL equipment and solutions, support customers, and author industry publications. Our power system experts have trained tens of thousands of industry professionals worldwide to help them meet the technical challenges of integrating digital technologies into their expanding power system infrastructure.

SEL University covers topics such as:

- Introduction to SEL relays.
- Cybersecurity and securing operational technologies (OT) networks.
- SEL Real-Time Automation Controller (RTAC) applications.
- Protecting power systems for engineers.

See available courses and register at selinc.com/selu.

# Technical Papers, Webinars, and Videos

SEL power system experts have authored more than 1,000 technical papers, hosted hundreds of webinars, and developed dozens of support videos. They are dedicated to teaching about how our technologies solve complex power system challenges and about how we partner with our customers to solve tough problems. Visit selinc.com to access our library of educational material, including these trending and top five downloaded technical papers:

#### **Trending Technical Papers**

Beyond the Nameplate: Transformer Compensation Revisited—New Applications, Greater Simplicity selinc.com/api/download/138123

Zero-Setting Broken Conductor Detection Method Using Local Measurements Only selinc.com/api/download/138742

Solving Complex Feeder Protection Challenges and Reducing Wildfire Risks With Remote Measurements selinc.com/api/download/138149

Case Study: Implementing a Zero-Touch Deployment Methodology Using SDN to Improve the Security, Reliability, and Engineering of Substation Automation Systems in Slovenia selinc.com/api/download/138803

Case Study: A Subtransmission-Level Fault Location, Isolation, and Service Restoration (FLISR) Scheme selinc.com/api/download/140447

# Top Five Downloaded Technical Papers of 2025

Introduction to Symmetrical Components selinc.com/api/download/2470

Review of Ground Fault Protection Methods for Grounded, Ungrounded, and Compensated Distribution Systems selinc.com/api/download/2604

Current Transformer Accuracy Ratings selinc.com/api/download/3684

Considerations for Using High-Impedance or Low-Impedance Relays for Bus Differential Protection selinc.com/api/download/5562

Understanding Generator Stator Ground Faults and Their Protection Schemes

selinc.com/api/download/111667

#### **Bookstore**

Visit the SEL bookstore at selinc.com/bookstore for textbooks and focused technical paper anthologies, like the following:

- Modern Solutions for Protection, Control, and Monitoring of Electric Power Systems
- Synchronous Generator Protection and Control
- Line Current Differential Protection
- Locating Faults and Protecting Lines at the Speed of Light

Modern Solutions for Protection, Control, and Monitoring of Electric Power Systems offers a comprehensive reflection of technologies developed by SEL engineers and spans topics of interest to people working in protection, control, communications, regulation, education, and design.

Online you'll also find these books written by Stanley E. Zocholl, an SEL Distinguished Engineer and IEEE Life Fellow:

- Analyzing and Applying Current Transformers
- AC Motor Protection





# **Ordering and Customer Support**

selinc.com/support | +1.509.338.3838

# **Online Configuration** and Ordering

Configure products to meet your exact application needs and order them online with an SEL account. Once logged in, select "Configure and Order" on a product webpage to choose from available model options, including items like power supply voltages, inputs and outputs, communications ports and protocols, and conformal coating. Save individual products to your cart, create projects to house specific product orders, and request a quote—all online. For products that do not require configuration or have been identified as common product configurations, select "Popular Models" on a product webpage to quickly and easily find the model you want.

## **Ordering Support**

Our sales representatives and customer service teams are always happy to answer questions and help configure the right SEL solution for your application. Visit selinc.com/support for regional sales contact information.

#### **Popular Models**

The Popular Models program makes selecting and ordering SEL products simple, fast, and convenient. SEL popular models are products preconfigured for popular applications and available for many SEL devices. Specific popular models may ship from stock. When available, the popular model configurations are displayed on the related SEL product webpage, where you can also view their technical details and popular applications. You can order these models directly from SEL or through your SEL sales representative.


# Local Support. **Global Expertise.**

Whether it's grid modernization in the Philippines or an ambitious offshore wind integration project in Belgium, our global engineering experts have helped projects in regions like yours succeed. And with local support from technical staff in your region, you can count on us to help your successes continue.

# Scan to find a customer support representative in your area.

selinc.com/support





# Index

9L Line Relay COMING SOON	17
300G Generator Relay	10
311C Transmission Protection System	17
311L Line Current Differential Protection and Automation System	17
351 Protection System	30
351A Protection System	30
351RS Kestrel® Single-Phase Recloser Control	32
351S Protection System	30
352 Breaker Failure Relay	24
400G Advanced Generator Protection System	10
401 Protection, Automation, and Control Merging Unit	24
411L Advanced Line Differential Protection, Automation, and Control System	17
421 Protection, Automation, and Control System	17
451 Protection, Automation, and Bay Control System	30
487B Bus Differential and Breaker Failure Relay	24
487E Transformer Protection Relay	24
487V Capacitor Protection and Control System	24
651R Advanced Recloser Control	32
651RA Recloser Control	32
700BT Motor Bus Transfer Relay	13
700G Generator Protection Relay	10,14
710-5 Motor Protection Relay	13
734B Advanced Monitoring and Control System	32
734W Capacitor Bank Control	32
735 Power Quality and Revenue Meter	14,39
751 Feeder Protection Relay	13,30
787-2/-3/-4 Transformer Protection Relay	14,24
787L Line Current Differential Relay	13
787Z High-Impedance Differential Relay and SEL-HZM High-Impedance Module	14,24

849 Motor Management Relay	13
851 Feeder Protection Relay	13,30
2126 Fiber-Optic Transfer Switch	67
2240 Axion®	44,63
2401 Satellite-Synchronized Clock	56
2407® Satellite-Synchronized Clock	56
2411 Programmable Automation Controller	44
2411P Pump Automation Controller	44
2414 Transformer Automation Controller	10,24,44
2431 Voltage Regulator Control	32
2440 Discrete Programmable Automation Controller (DPAC)	44,62
2488 Satellite-Synchronized Network Clock	56
2505 Remote I/O Module	62
2506 Rack-Mount Remote I/O Module	62
2507 High-Speed Remote I/O Module	62
2515 Remote I/O Module	62
2516 Rack-Mount Remote I/O Module	62
2522 Alarm Panel	63
2523 Annunciator Panel	63
2533 Annunciator	63
2595 Teleprotection Terminal	62
2600 RTD Module	10,14
2652 Trip Coil Monitor	67
2664 Field Ground Module	10
2664S Stator Ground Protection Relay	10
2725 Five-Port Ethernet Switch	52
2731 Ethernet Switch	52
2740S Software-Defined Network Switch	52
2741 Ethernet Switch	52
2742 Ethernet Switch	10,14,52
2743 Ethernet Switch NEW	52
2744 Ethernet Switch NEW	52
2800 Fiber-Optic Transceiver	59
2810 Fiber-Optic Transceiver With IRIG-B	59

2812 Fiber-Optic Transceiver With IRIG-B	59
2814 Fiber-Optic Transceiver With Hardware Flow Control	59
2815 Fiber-Optic Transceiver/Modem	59
2820 Multimode Fiber-Optic EIA-485 Transceiver	59
2824 Multimode Fiber-Optic EIA-485 Transceiver	59
2829 Single-Mode Fiber-Optic Transceiver/Modem	59
2830 Single-Mode Fiber-Optic Transceiver/Modem	59
2831 Single-Mode Fiber-Optic Transceiver/Modem	59
2886 EIA-232 to EIA-485 Interface Converter	59
2890 Ethernet Transceiver	59
2894 Interface Converter	59
2902 RJ45 to DB-9 Adapter Panel	59
3031 Serial Radio Transceiver	55
3061 Cellular Router	54
3350 Computing Platform	14,43
3355 Computing Platform	43
3360S Compact Computing Platform	43
3360E Compact Computing Platform	43
3400 IRIG-B Distribution Module	56
3401 Digital Clock	56
3405 High-Accuracy IRIG-B Fiber-Optic Transceiver	56
3505 Real-Time Automation Controller (RTAC)	43
3505-3 RTAC	43
3555 RTAC	10,14,43
3560E RTAC	43
3560S RTAC	43
3620 Ethernet Security Gateway	52
3622 Security Gateway	52
3780 Test Point Voltage Sensor	37
3790 Low-Voltage Divider Module NEW	67

5030 ACSELERATOR QuickSet® Software	67
	65
5032 ACSELERATOR Architect® Software	65
5033 AcSELerator RTAC® Software	44,65
5035 ACSELERATOR Diagram Builder™ Software	44,65
5036 ACSELERATOR® Bay Screen Builder Software	44,65
5037 Grid Configurator Software	65
5051/5052 Client/Server Network Management System (NMS) Software	65
5056 Network Management System (NMS) Software	65
5057 SDN Application Suite	65
5073 SYNCHROWAVE® PDC Software	66
5231 SEL Configuration API	66
5601-2 Synchrowave® Event Software	66
5705 Synchrowave® Reports	66
9220 Fiber-Optic Adapter for SEL-300 Series Relays	59
9321 Low-Voltage DC Power Supply	67
9322 15 VDC Power Supply	67
9501 Contact Arc Suppressor	67
9502 Contact Arc Suppressor	67
9510 Control Switch Module	67
9524 GNSS Antenna	56
9929 Satellite-Synchronized Clock Display Kit	56
AR Overhead AutoRANGER Fault Indicators	36
AR360 Overhead AutoRANGER Fault Indicators	36
Blueframe® Application Platform	44,66
Blueframe® Data Management and	44,66
Automation (DMA) Application Suite	
_	44,66
Automation (DMA) Application Suite  Blueframe® Distribution Management	44,66

C807 62.5/200 µm Multimode Fiber- Optic Cable	60
C808 62.5/125 µm Multimode Fiber- Optic Cable	60
C809 9 µm Single-Mode Fiber-Optic Cables	60
Cables—Coaxial, Electrical Data, Ethernet, and USB	60
CRD Overhead Current Reset Fault Indicator	36
CT Split-Core Current Transformers	37
Direct-Replacement Assemblies	69
ER Overhead Electrostatic Reset Fault Indicator	36
FLR Fault and Load Receiver	36
FLT Fault and Load Transmitter	36
FR12 Fault Receiver	30
FT50 Fault Transmitter	30
ICON® Integrated Communications Optical Network	52,56
LINAM® UGFI Underground Fault Indicator NEW	37
LINAM® WCS Wireless Current Sensor	32
MR Manual Reset Fault Indicator	36
Panels and Enclosures	68
PILC Underground Paper-Insulated Lead-Covered Cable Fault Indicator	37
RadioRANGER® Underground Wireless Fault Indication System	37
RP50 Fault Repeater	30
RPM Redundant Power Module	67
RTAC HMI	66
Services—Complete Design, Manufacturing, Testing, and Commissioning	68
Services—Cyber Services	73
Services—Microgrids and Power Management	72
Services—Project and Program Management	71
Synchrowave® Software	39,41
T35 Time-Domain Power Monitor NEW	41

T401L Ultra-High-Speed Line Relay	17
T4287 Traveling-Wave Test System	17
TMU TiDL® Merging Unit	24
TPR Underground Test Point Reset Fault Indicator	37
TWFL Dual Traveling-Wave Fault Locator and 12-Channel MHz Recorder	17
Wireless Protection System	30,36

The information in this document is furnished for informational use only and is subject to change without notice. Drawings are for illustrative purposes only; they are not for construction. Schweitzer Engineering Laboratories, Inc., is also referred to in this catalog as Schweitzer Engineering Laboratories. All brand or product names appearing in this document are the  $\,$ trademark or registered trademark of their respective holders in the U.S. and other countries. No SEL trademarks may be used without written permission. SEL products appearing in this document may be covered by U.S. and Foreign patents.

EtherCAT® is a registered trademark and patented technology, licensed by Beckhoff Automation GmbH, Germany.

© 2025 by Schweitzer Engineering Laboratories, Inc. All rights reserved.



2350 NE Hopkins Court, Pullman, WA 99163 USA

+1.509.332.1890

info@selinc.com

selinc.com